

# EXL1V0503

## High current molded inductor



### Product features

- High current carrying capacity
- Low DCR, high efficiency
- Magnetically shielded, low EMI
- Soft saturation
- Inductance range from 0.15  $\mu$ H to 4.7  $\mu$ H
- Current range from 5.9 A to 32.5 A
- 6.2 mm x 5.9 mm footprint surface mount package in a 3.1 mm height
- Alloy powder core material
- Moisture Sensitivity Level (MSL) 1

### Applications

- Voltage Regulator Module (VRM)
- Multi-phase regulators
- Point-of-load (POL) converters
- Desktop and server VRMs and EVRDs
- Base station equipment
- Laptop and notebook regulators
- Tablets and e-readers
- Battery power systems
- Graphics cards
- Data networking and storage system

### Environmental compliance and general specifications

- Storage temperature range (Component): -40 °C to +125 °C
- Operating temperature range: -40 °C to +125 °C (ambient plus self-temperature rise)
- Solder reflow temperature: J-STD-020 (latest revision) compliant



## Product specifications

Part number <sup>5</sup>	OCL <sup>1</sup> ( $\mu$ H) $\pm$ 20%	FLL <sup>2</sup> ( $\mu$ H) minimum	$I_{rms}$ <sup>3</sup> (A) typical		$I_{sat}$ <sup>4</sup> (A)	DCR (m $\Omega$ ) typical @ +25 °C	DCR (m $\Omega$ ) maximum @ +25 °C	SRF (MHz) typical
EXL1V0503-R15-R	0.15	0.08	14.3	22.2	32.5	2.1	2.31	140
EXL1V0503-R16-R	0.16	0.08	14.2	22.2	32	2.12	2.33	140
EXL1V0503-R28-R	0.28	0.15	14	19	28	3.0	3.3	120
EXL1V0503-R33-R	0.33	0.18	13.8	19.2	26	3.2	3.52	110
EXL1V0503-R47-R	0.47	0.26	13.7	18.4	24	3.75	4.13	95
EXL1V0503-R56-R	0.56	0.31	13.6	17.7	20.2	4.05	4.52	73
EXL1V0503-R60-R	0.6	0.33	13.6	17.7	20	4.11	4.52	68
EXL1V0503-R80-R	0.8	0.44	10.1	13.1	18	5.14	5.65	57
EXL1V0503-R82-R	0.82	0.45	9.9	12.9	17.6	5.25	5.78	54
EXL1V0503-1R0-R	1	0.56	9.0	12.2	14.3	6.9	7.6	50
EXL1V0503-1R2-R	1.2	0.67	8.5	11	13.5	8.8	9.7	43
EXL1V0503-1R5-R	1.5	0.84	8.0	10.5	12.5	10.1	11.2	38
EXL1V0503-1R8-R	1.8	1.00	7.6	10.1	11.3	11.5	12.7	36
EXL1V0503-2R2-R	2.2	1.23	7.2	9.7	9.0	13.2	14.5	33
EXL1V0503-3R3-R	3.3	1.84	5.9	8.1	8.7	21	23.1	25
EXL1V0503-4R7-R	4.7	2.63	4.3	5.9	7	33	36.3	21

1. Open circuit inductance (OCL) Test parameters: 100 kHz, 0.1 V<sub>rms</sub>, 0.0 Adc, +25 °C

2. Full load inductance (FLL) Test parameters: 100 kHz, 0.1 V<sub>rms</sub>,  $I_{sat}$ , +25 °C

3.  $I_{rms}$ : Heat rated current ( $I_{rms}$ ) will cause the part temperature rise approximately  $\Delta T$  of 40 °C. Circuit design, component, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application. The part temperature (ambient + temperature rise) should not exceed +125 °C under worst case operating conditions.

4.  $I_{sat}$ : Peak current for approximately 30% rolloff @ +25 °C

5. Part Number Definition: EXL1V0503-xxx-R

EXL1V0503 = Product code and size


xxx= inductance value in  $\mu$ H, R= decimal point,

If no R is present then third digit equals the number of zeros


-R suffix = RoHS compliant

6. Rated operating voltage: 40 V typical

## Mechanical parameters, schematic, pad layout (mm)



### Recommended pad layout



### Schematic




Figure 1. DCR test

Part number	A	B	C	D	E	F
EXL1V0503-xxx-R	6.0 $\pm$ 0.2	5.7 $\pm$ 0.2	2.9 $\pm$ 0.2	4.3 $\pm$ 0.3	1.1 $\pm$ 0.2	2.3 $\pm$ 0.25

Part marking: 0503, xxx= inductance value in  $\mu$ H (R= decimal point, If no R is present last digit equals number of zeros), yyyy= lot code

All soldering surfaces to be coplanar within 0.1 millimeters

Tolerances are  $\pm$  0.3 millimeters unless stated otherwise

Dimensions of recommended PCB layout are reference only.

Pad layout tolerances are  $\pm$  0.1 millimeters unless stated otherwise


Four terminal kelvin-clip recommended for DCR testing as shown in Figure 1.

Traces or vias underneath the inductor is not recommended.

## Packaging information (mm)

Drawing not to scale

Supplied in tape and reel packaging, 2000 parts per 13" diameter reel (EIA-481 compliant)









W ± 0.30	16
F ± 0.1	7.5
E1 ± 0.1	1.75
P0 ± 0.1	4.0
P1 ± 0.1	8.0
P2 ± 0.1	2.0
D0 + 0.1/-0	1.5
D1 + 0.1/-0	1.5
A0 ± 0.1	6.4
B0 ± 0.1	6.1
K0 ± 0.1	3.3
T ± 0.05	0.35
P0 X 10 ± 0.2	40







## Qualification testing

No.	Test item	Reference standards	Test condition	Acceptable value/range
1	Life	MIL-STD-202 Method 108	+125 °C + I <sub>rms</sub> for 1000 hours	a. Appearance b. ΔL/L<±10% d. ΔR/R<±15%
2	Load humidity	MIL-STD-202 Method 103	+85 °C/85% RH + I <sub>rms</sub> for 1000 hours	a. Appearance b. ΔL/L<±10% d. ΔR/R<±15%
3	Moisture resistance	MIL-STD-202 Method 106	7a & 7b included	a. Appearance b. ΔL/L<±10% d. ΔR/R<±15%
4	Thermal shock	MIL-STD-202 Method 107	Step 1: -40 ± 2 °C 30 ± 5 minutes Step 2: 25 ± 2 °C ≤ 0.5 minutes Step 3: 125 ± 2 °C 30 ± 5 minutes Number of cycles: 500	a. Appearance b. ΔL/L<±10% d. ΔR/R<±15%
5	Vibration	MIL-STD-202 Method 204	10 g, 12 hours (10 Hz ~ 2 kHz ~ 10 Hz for 20 minutes, 12 cycles each of 3 orientations)	a. Appearance b. ΔL/L<±10% d. ΔR/R<±15%
6	Shock	MIL-STD-202 Method 213	Half-sine 50 g's, 11 ms	a. Appearance b. ΔL/L<±10% d. ΔR/R<±15%
7	Bending	IEC 68-2-21	1.2 mm for 10 s	a. Appearance b. ΔL/L<±10% d. ΔR/R<±15%
8	Solderability	J-STD-002D Method B	Preheat: +150 °C, 60 sec. 245 ± 5, Dip time: 4 ± 1 sec. Depth: completely cover the termination	≥ 95% of the terminal covered with solder
9	Resistance to soldering heat	MIL-STD-202 Method 210	+260 ± 5 °C; 10 ± 1 s	a. Appearance b. ΔL/L<±10% d. ΔR/R<±15%
10	Terminal strength	AEC-Q200-006	1 kg for 60 + 1 s	a. Appearance b. ΔL/L<±10% d. ΔR/R<±15%




# Inductance and temperature rise vs. current









Inductance and temperature rise vs. current, continued



Inductance and temperature rise vs. current, continued









Inductance and impedance vs. frequency curve









Inductance and impedance vs. frequency curve, continued






Inductance and impedance vs. frequency curve, continued



## Solder reflow profile



**Table 1 - Standard SnPb solder ( $T_c$ )**

Package thickness	Volume mm <sup>3</sup> <350	Volume mm <sup>3</sup> ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

**Table 2 - Lead (Pb) free solder ( $T_c$ )**

Package thickness	Volume mm <sup>3</sup> <350	Volume mm <sup>3</sup> 350 - 2000	Volume mm <sup>3</sup> >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 – 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

## Reference J-STD-020

Profile feature	Standard SnPb solder	Lead (Pb) free solder
Preheat and soak		
• Temperature min. ( $T_{smin}$ )	100 °C	150 °C
• Temperature max. ( $T_{smax}$ )	150 °C	200 °C
• Time ( $T_{smin}$ to $T_{smax}$ ) ( $t_s$ )	60-120 seconds	60-120 seconds
Ramp up rate $T_L$ to $T_p$	3 °C/ second max.	3 °C/ second max.
Liquidous temperature ( $T_L$ )	183 °C	217 °C
Time ( $t_L$ ) maintained above $T_L$	60-150 seconds	60-150 seconds
Peak package body temperature ( $T_p$ )*	Table 1	Table 2
Time ( $t_p$ )* within 5 °C of the specified classification temperature ( $T_c$ )	20 seconds*	30 seconds*
Ramp-down rate ( $T_p$ to $T_L$ )	6 °C/ second max.	6 °C/ second max.
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.

\* Tolerance for peak profile temperature ( $T_p$ ) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

**Eaton**  
**Electronics Division**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
Eaton.com/electronics

© 2020 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. 11188 BU-MC20165  
November 2020

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

[EXL1V0503-1R0-R](#) [EXL1V0503-1R2-R](#) [EXL1V0503-1R5-R](#) [EXL1V0503-1R8-R](#) [EXL1V0503-2R2-R](#) [EXL1V0503-3R3-R](#) [EXL1V0503-R56-R](#) [EXL1V0503-R60-R](#) [EXL1V0503-R80-R](#) [EXL1V0503-R82-R](#) [EXL1V0503-4R7-R](#)  
[EXL1V0503-R15-R](#) [EXL1V0503-R16-R](#) [EXL1V0503-R28-R](#) [EXL1V0503-R33-R](#) [EXL1V0503-R47-R](#)