





Electrical Testing  
per Tusonix standard  
test plans and Mil-Std-202  
Test Methods.

**MARKETING SALES DRAWING**  
**DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING**



NOTE:  
1. SUPPLIED WITH SILVER PLATED  
HEX NUT AND INTERNAL TOOTH  
LOCK WASHER.

TUSONIX PART NUMBER	2425-734-X7U0-152Z
CAP. VALUE	1500 pF
CAP. TOL.	+80, -20 %
TEMP. COEF.	X7U
VOLT. RATING	100 VDC +125°C
OPERATING TEMP. RANGE	-55 TO +125°C
TESTED TO TUSONIX EQUIVALENT TO MIL-C39014 FOR GROUP A INSPECTION INCLUDING SUMMARY TEST DATA	

X-2015 Rev-0	REVISION RECORD	Original Release C.O. 20000216-2-01		--TOLERANCES-- Unless Otherwise Specified		Title <b>HI-RELIABILITY COMMERCIAL REPLACEMENT FOR M39014/18 (CKR76) FEED-THRU CAPACITOR</b>			
				DECIMAL ±	.015	Drawn S.M. 02-17-00		Scale 4 X	
				ANGLES ±		Approved T.C. 02-17-00		<b>A</b>	<b>2425-734-X7UO-152Z</b>
				<b>TUSONIX</b> TUCSON, ARIZONA					

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[2425-734-X7U0-152Z](#)