




This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.

**Electrical Testing  
per Tusonix standard  
test plans and Mil-Std-202  
Test Methods.**

# **MARKETING SALES DRAWING** **DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING** **DIMENSIONS IN METRIC - [   ]**




## **NOTES:**

1. SUPPLIED WITH SILVER PLATED HEX NUT AND INTERNAL TOOTH LOCK WASHER.
2. MOUNTING TORQUE NOT TO EXCEED 5 lb - in. MAX. [565 N-m]
3. TUSONIX STANDARD PART NUMBER: 2430-008-X5F0-102M. TUSONIX RoHS COMPLIANT PART NUMBER: 2430-008-X5F0-102M LF. CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
4. PART MARKING: STANDARD: BLACK INK FOR TRADEMARK AND CAP. CODE. RoHS PART: GREEN FOR TRADEMARK AND CAP. CODE.
5. LEAD: STANDARD PART, 60/40 SOLDER PLATED. RoHS PART, SILVER PLATED.

## **SPECIFICATIONS**

TUSONIX STYLE:	2430-008
Capacitance:	1000 pF
Capacitance Tolerance:	±20 %
Temp. Coef:	X5F
Rating:	200 VDC
Operating Range:	-55°C TO 85°C
I.R. MIN. @ 100 (VDC)	10 G Ω
DWV	600 VDC

<div>REVISION RECORD</div> <div>Original Release C.O. 19990106-2-01 ADDED NOTES, IR, DWV &amp; METRIC. S.M. 06-09-06</div> <div>20060602-2-03</div>					
		--TOLERANCES-- Unless Otherwise Specified		Title <b>MINIATURE BUSHING FEED-THRU CAPACITOR</b>	
		DECIMAL ± .031 [0.79]			
		ANGLES ± 		Drawn Title S.M. 01-08-99	
		<b>TUSONIX</b> TUCSON, ARIZONA		Scale 5 X	
				Approved J.Mc. 01-08-99	
				A	2430-008-X5F0-102M

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[2430-008-X5F0-102MLF](#)