MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - [ ]

Electrical Testing per Tusonix standard test plans and Mil-Std-202 Test Methods.







Notes:
1. Tusonix Standard part number: 4101-008.
   Tusonix RoHS compliant part number: 4101-008 LF.
   Customer must specify Standard or RoHS part number when ordering.
2. Lead finish: Standard Part No.: 60/40 solder plated. RoHS Part No. Silver Plated.
   Eyelet finish Standard Part No.: 60/40 solder plated. RoHS Part No. Silver Plated.
3. Part Marking: Standard has no marking. RoHS part: Green Dot.

MIN. CAP (pF)	WORKING VOLTAGE (WVDC)		CURRENT Idc	I.R. MIN. @ 100 (VDC.)	DWV 25 SEC. (VDC)	MINIMUM NO-LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220			
	85°C	125°C				10 MHz	100 MHz	1 GHz	10 GHz
5500	200 VDC	100 VDC	10A	10 G Ω	400	14	55	70	70

REVISION RECORD	
0	Original Release C.O.
1	CHANGED TOL. +.005, -.010 WAS ±.010, 200 VDC WAS 140 & 70. E.C. 11-05-87
2	WAS SK6848-000-S ADDED .060 TYP DIM. E.C. 11-23-87 3643 DWG. # WAS 4101-008-000-S. E.C. 01-21-88
3	4301 RDN TO COMP FMT. & ADDED METRIC. DIM .143 WAS .156 & DIM .237 WAS .250. DELETED S. WASHERS. S.M. 01-19-00
4	20000120-1-01 TOL. ±.010 WAS +.005 -.010. 100VDC WAS 200. ADDED TINNED COPPER.S.M. 07-14-03
5	20030711-1-02 ADDED NOTES, IR & DWV. S.M. 09-14-05
6	20050829-1-06

X-2015 Rev-0

--TOLERANCES--
Unless Otherwise Specified
DECIMAL ± .031 [.79]
ANGLES ±

TUSONIX
TUCSON, ARIZONA

Title
EYELET STYLE EMI FILTER

Drawn S.M. 01-19-00
Scale 4 X
Approved T.C. 01-19-00

A **4101-008**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Tusonix / CTS:
4101-008LF