




MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []


Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



NOTES:

1. TUSONIX STANDARD PART NUMBER: 4253-001.
TUSONIX RoHS COMPLIANT PART NUMBER: 4253-001 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
2. LEAD FINISH: STANDARD PART #: 60/40 SOLDER PLATED. RoHS PART #: SILVER PLATED.
3. PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.

MIN. Cx	WORKING VOLTAGE 125°C	CURRENT VDC	MINIMUM NO LOAD INSERTION LOSS @ 25°C (dB) PER MIL-STD-220			
			10 MHz	100 MHz	1 GHz	10 GHz
25,000 pF	100 VDC	10 A	30	65	70	70

X-2015 Rev-0	REVISION RECORD			--TOLERANCES-- Unless Otherwise Specified		Title MULTILAYER BUSHING STYLE EMI FILTER	
	Original Release C.O.	0 6611	DIM'S. REV. TITLE CHGD. E.C. 5-26-92	DECIMAL ±		Drawn S.M. 07-17-01	Scale 3 X
		1 6667	DIM'S. REV. TITLE CHGD. E.C. 5-26-92	ANGLES ±	.031[0.79]	Approved T.C. 07-17-01	
		2 20010713-2-03	ADDED NOTES 1-3. S.M. 06-15-05	TUSONIX TUCSON, ARIZONA		A	4253-001
		3 20050607-2-02					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[4253-001LF](#)