


SMFE

Automotive grade 400 W Transient voltage suppressor



Product features

- Automotive grade (AEC-Q101 qualified)
- Low profile SOD-123FL package
- Excellent clamping capability
- High reliability application
- 400 W peak pulse power capability at 10/1000 μ s waveform
- Typical I_R less than 1 μ A above 10 V
- Fast response time: typically less than 1.0 ps from 0 V to V_{BR} minimum
- Plastic package meets UL 94 V-0 flammability rating
- Meets moisture sensitivity level (MSL) level 1
- Terminal: tin plated, solderable per J-STD-002

Applications

- Automotive chassis and safety systems
- Advanced driver assistance systems (ADAS)
- Communication and infotainment systems
- Network systems and body electronics
- Power Train controls
- xEV and battery systems

Environmental compliance and general specifications



- AEC-Q101 qualified



Ordering part number

	SMFE	5-0	C	A	L	H
Family name	_____	_____	_____	_____	_____	_____
V_R voltage (“-” indicates decimal point)	_____	_____	_____	_____	_____	_____
Bi-/Uni-Directional (Blank=Uni, C=Bi)	_____	_____	_____	_____	_____	_____
Voltage tolerance	_____	_____	_____	_____	_____	_____
P_{PP} (400 W version)	_____	_____	_____	_____	_____	_____
High reliability application	_____	_____	_____	_____	_____	_____

PIN configuration




Absolute maximum ratings

(+25 °C, RH=45%-75%, unless otherwise noted)


Parameter	Symbol	Value	Unit
Storage operating junction temperature range	T_{STG}/T_J	-55 to +150	°C
Peak pulse power dissipation on 10/1000 μ s waveform	P_{PP}	400	W
Maximum instantaneous forward voltage at 20 A for unidirectional	V_F	5.0	V
Typical thermal resistance junction to lead	$R_{\theta JL}$	100	°C/W
Typical thermal resistance junction to ambient	$R_{\theta JA}$	220	°C/W

Mechanical parameters, pad layout- mm/inches



Dimension	Millimeters		Inches	
	Minimum	Maximum	Minimum	Maximum
A	2.60	3.00	0.102	0.118
B	1.60	2.00	0.063	0.079
C	3.45	3.95	0.136	0.156
D	0.10	0.25	0.004	0.010
E	0.30	0.90	0.012	0.035
F	0.80	1.20	0.031	0.047
G	0.95	1.35	0.037	0.053
J	1.30	-	0.051	-
K	-	1.70	-	0.067
L	1.30	-	0.051	-

Part marking



Cathode band (uni-polar only)


Part marking:

yyyy= Placeholder- refer to "Marking" listed in Electrical characteristics table for actual marking

Packaging information - mm/inches

Drawing not to scale.

Supplied in tape and reel packaging, 3,000 parts per 7" diameter reel (EIA-481 compliant)




Dimensions	Millimeters	Inches
A0	1.95 ± 0.3	0.077 ± 0.012
B0	3.95 ± 0.3	0.156 ± 0.012
C	178.0	7.0
D0	1.55 ± 0.1	0.061 ± 0.004
E	1.75 ± 0.2	0.069 ± 0.008
E1	13.3 ± 0.3	0.524 ± 0.012
F	3.50 ± 0.2	0.138 ± 0.008
P0	4.00 ± 0.2	0.157 ± 0.008
P1	4.00 ± 0.2	0.157 ± 0.008
P2	2.00 ± 0.2	0.079 ± 0.008
W	8.0 ± 0.2	0.315 ± 0.008
W1	11.5 ± 1.0	0.453 ± 0.039

Electrical specifications (+25 °C)


Part number		Marking		V_R	$I_R @ V_R$	$V_{BR} @ I_T$	I_T	$V_C @ I_{PP}$	I_{PP}
Uni-polar	Bi-polar	Uni	Bi	(V)	max (μA)	min (V)	max (V)	max (V)	(A)
SMFE5-0ALH	/	AEH	/	5	40	6.4	7	9.2	40.1
SMFE6-0ALH	/	AGH	/	6	40	6.67	7.37	10.3	35.9
SMFE6-5ALH	/	AKH	/	6.5	30	7.22	7.98	11.2	33.1
SMFE7-0ALH	/	AMH	/	7	30	7.78	8.6	12	30.9
SMFE7-5ALH	/	APH	/	7.5	30	8.33	9.21	12.9	28.7
SMFE8-0ALH	/	ARH	/	8	20	8.89	9.83	13.6	27.2
SMFE9-0ALH	/	AVH	/	9	5	10	11.1	15.4	24.1
SMFE10ALH	SMFE10CALH	AXH	10CLH	10	2	11.1	12.3	17	23.5
SMFE11ALH	SMFE11CALH	AZH	11CLH	11	1	12.2	13.5	18.2	22
SMFE12ALH	SMFE12CALH	BEH	12CLH	12	1	13.3	14.7	19.9	20.1
SMFE13ALH	SMFE13CALH	BGH	13CLH	13	1	14.4	15.9	21.5	18.6
SMFE14ALH	SMFE14CALH	BKH	14CLH	14	1	15.6	17.2	23.2	17.2
SMFE15ALH	SMFE15CALH	BMH	15CLH	15	1	16.7	18.5	24.4	16.4
SMFE17ALH	/	BRH	/	17	1	18.9	20.9	27.6	14.5
SMFE18ALH	SMFE18CALH	BTH	18CLH	18	1	20	22.1	29.2	13.7
SMFE20ALH	SMFE20CALH	BVH	20CLH	20	1	22.2	24.5	32.4	12.3
SMFE22ALH	SMFE22CALH	BXH	22CLH	22	1	24.4	26.9	35.5	11.3
SMFE24ALH	SMFE24CALH	BZH	24CLH	24	1	26.7	29.5	38.9	10.3
SMFE26ALH	SMFE26CALH	CEH	26CLH	26	1	28.9	31.9	42.1	9.5
SMFE28ALH	SMFE28CALH	CGH	28CLH	28	1	31.1	34.4	45.4	8.8
SMFE30ALH	SMFE30CALH	CKH	30CLH	30	1	33.3	36.8	48.4	8.3
SMFE33ALH	SMFE33CALH	CMH	33CLH	33	1	36.7	40.6	53.3	7.5
SMFE36ALH	SMFE36CALH	CPH	36CLH	36	1	40	44.2	58.1	6.9
SMFE40ALH	SMFE40CALH	CRH	40CLH	40	1	44.4	49.1	64.5	6.2
SMFE43ALH	SMFE43CALH	CTH	43CLH	43	1	47.8	52.8	69.4	5.8
SMFE45ALH	SMFE45CALH	CVH	45CLH	45	1	50	55.3	72.7	5.5
SMFE48ALH	SMFE48CALH	CXH	48CLH	48	1	53.3	58.9	77.4	5.2
SMFE51ALH	/	CZH	/	51	1	56.7	62.7	82.4	4.9
SMFE58ALH	/	DEH	/	58	1	64.4	71.2	93.6	4.3
SMFE60ALH	/	DGH	/	60	1	66.7	73.7	96.8	4.1
SMFE64ALH	/	DMH	/	64	1	71.1	78.6	103	3.9
SMFE70ALH	/	DPH	/	70	1	77.8	86	113	3.5
SMFE75ALH	/	DRH	/	75	1	83.3	92.1	121	3.3
SMFE78ALH	/	DTH	/	78	1	86.7	95.8	126	3.2
SMFE85ALH	/	DVH	/	85	1	94.4	104	137	2.9

Ratings and V-I characteristic curves (+25 °C unless otherwise noted)

V- I curve characteristics (Uni-directional)



V- I curve characteristics (Bi-directional)



Surge waveform: 10/1000 μ s

V_R : Stand-off voltage – Maximum voltage that can be applied

V_{BR} : Breakdown voltage


V_C : Clamping voltage – Peak voltage measured across the suppressor at a specified I_{PP}

I_R : Reverse leakage current


I_T : Test current

V_F : Forward voltage drop for Uni-directional

Pulse waveform



Pulse derating curve



Solder reflow profile




Table 1 - Standard SnPb solder (T_C)

Package thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2 - Lead (Pb) free solder (T_C)

Package thickness	Volume mm ³ <350	Volume mm ³ 350 - 2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 – 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Reference J-STD-020

Profile feature	Standard SnPb solder	Lead (Pb) free solder
Preheat and soak		
• Temperature min. (T_{smin})	100 °C	150 °C
• Temperature max. (T_{smax})	150 °C	200 °C
• Time (T_{smin} to T_{smax}) (t_s)	60-120 seconds	60 - 180 seconds
Ramp up rate T_L to T_p	3 °C/ second max.	3 °C/ second max.
Liquidous temperature (T_L)	183 °C	217 °C
Time (t_L) maintained above T_L	60-150 seconds	60-150 seconds
Peak package body temperature (T_p)*	Table 1	Table 2 (+0, -5 °C)
Time (t_p)* within 5 °C of the specified classification temperature (T_C)	20 seconds*	40 seconds*
Ramp-down rate (T_p to T_L)	6 °C/ second max.	6 °C/ second max.
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.

* Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com/electronics

© 2021 Eaton
All Rights Reserved
Printed in USA
Publication No. ELX1067 BU-ELX21067
June 2021

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

[SMFE15ALH](#) [SMFE28ALH](#) [SMFE64ALH](#) [SMFE40CALH](#) [SMFE13ALH](#) [SMFE18ALH](#) [SMFE33CALH](#) [SMFE8-0ALH](#)
[SMFE28CALH](#) [SMFE40ALH](#) [SMFE13CALH](#) [SMFE18CALH](#) [SMFE33ALH](#) [SMFE78ALH](#) [SMFE11ALH](#)
[SMFE22ALH](#) [SMFE43CALH](#) [SMFE45ALH](#) [SMFE11CALH](#) [SMFE20CALH](#) [SMFE14CALH](#) [SMFE30ALH](#)
[SMFE85ALH](#) [SMFE14ALH](#) [SMFE30CALH](#) [SMFE58ALH](#) [SMFE12CALH](#) [SMFE36CALH](#) [SMFE5-0ALH](#)
[SMFE24CALH](#) [SMFE9-0ALH](#) [SMFE15CALH](#) [SMFE26CALH](#) [SMFE36ALH](#) [SMFE20ALH](#) [SMFE26ALH](#) [SMFE10ALH](#)
[SMFE10CALH](#) [SMFE24ALH](#) [SMFE45CALH](#) [SMFE48ALH](#) [SMFE51ALH](#) [SMFE17ALH](#) [SMFE22CALH](#)
[SMFE43ALH](#) [SMFE12ALH](#) [SMFE48CALH](#) [SMFE6-5ALH](#) [SMFE60ALH](#) [SMFE70ALH](#) [SMFE75ALH](#) [SMFE6.0ALH](#)
[SMFE7.0ALH](#) [SMFE7.5ALH](#)