


SMTJ

3500 A Transient voltage suppressor



Product features

- Low slope resistance
- Very low clamping voltage
- Excellent clamping capability
- Sharp breakdown voltage
- Glass passivated junction
- Snapback technology for superior clamping factor
- High temperature reflow soldering: +260 °C /40 s at terminal
- Plastic package meets UL 94 V-0 flammability rating
- UL 1449 recognized.
File No. : E340782 Guide VZCA2


Applications

- Consumer electronics
- Telecommunications
- Computing and servers
- Ethernet protection
- Industrial automation
- Networking Equipment


Environmental compliance and general specifications



Ordering part number



PIN configuration



SMT-4




Absolute maximum ratings

(+25 °C, RH=45%-75%, unless otherwise noted)

Parameter	Symbol	Value	Unit
Operating junction temperature range	T_J	-55 to +150	°C
Peak pulse current @ 8/20 μ s	I_{PP}	3500	A
Storage temperature range	T_{STG}	-55 to +150	°C
Typical thermal resistance junction to lead	$R_{\theta JL}$	15	°C/W
Typical thermal resistance junction to ambient	$R_{\theta JA}$	65	°C/W

Mechanical parameters, pad layout- mm



Dimension	Millimeters		Inches	
	Minimum	Maximum	Minimum	Maximum
l	10.10	10.70	0.398	0.421
w	7.70	8.30	0.303	0.327
h	4.20	5.00	0.165	0.197
d	1.20	1.80	0.047	0.071
e	0	0.30	0	0.012
f	6.20	6.60	0.244	0.260
g	2.40	2.60	0.094	0.102
A		2.00		0.079
B	2.00		0.079	
C		7.00		0.276
D	2.50		0.098	

Part marking




Part marking: xxxx = Date code
yyyyyy- Refer to marking designer code listed in Electrical Characteristics table

Packaging information (mm)

Drawing not to scale.

Supplied in tape and reel packaging, 1,000 parts per 13" diameter reel (EIA-481 compliant)




Dimensions	Millimeters	Inches
A0	8.50 ± 0.3	0.335 ± 0.012
B0	10.80 ± 0.3	0.425 ± 0.012
C	330.0	13.0
D0	1.50 ± 0.1	0.059 ± 0.004
D1	1.50 ± 0.1	0.059 ± 0.004
E	1.75 ± 0.2	0.069 ± 0.008
E1	13.3 ± 0.3	0.524 ± 0.012
F	11.50 ± 0.2	0.453 ± 0.008
K0	5.10 ± 0.1	0.201 ± 0.004
P0	4.00 ± 0.2	0.157 ± 0.008
P1	12.00 ± 0.2	0.472 ± 0.008
P2	2.00 ± 0.2	0.079 ± 0.008
T	0.30 ± 0.05	0.012 ± 0.002
W	24.0 ± 0.3	0.945 ± 0.012
W1	28.5 ± 2.0	1.122 ± 0.079

Electrical characteristics (+25 °C)


Part number Bi-polar	Marking Bi	V_R (V)	$V_{BR} @ I_T$		I_T (mA)	$I_R @ V_R$ (μ A)	$V_C @ 8/20\mu s$	$V_C @ 8/20\mu s$	C_o typ (pf)
			min(V)	max(V)			3000 A (V)	3500 A (V)	
SMTJ58CAT	TJ58CA	58	64	70	10	5	110	120	3000
SMTJ66CAT	TJ66CA	66	72	80	10	5	120	130	2500
SMTJ76CAT	TJ76CA	76	85	95	10	5	140	150	2200
SMTJ86CAT	TJ86CA	86	95	105	10	5	157	170	1900

Ratings and V-I characteristic curves (+25 °C unless otherwise noted)

**V-I curve characteristics
(Bi-directional with negative resistance)**



Typical V_{BR} vs. junction temperature



Surge waveform: 8/20 μs

V_R: Stand-off voltage – Maximum voltage that can be applied

V_{BR}: Breakdown voltage


V_C: Clamping voltage – Peak voltage measured across the suppressor at a specified I_{PP}

I_R: Reverse leakage current


I_T: Test current

V_F: Forward voltage drop for Uni-directional TVS diode


Pulse waveform



Pulse derating curve



Peak pulse power rating curve



Solder reflow profile




Table 1 - Standard SnPb solder (T_C)

Package thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2 - Lead (Pb) free solder (T_C)

Package thickness	Volume mm ³ <350	Volume mm ³ 350 - 2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 – 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Reference J-STD-020

Profile feature	Standard SnPb solder	Lead (Pb) free solder
Preheat and soak	<ul style="list-style-type: none"> Temperature min. (T_{smin}) Temperature max. (T_{smax}) Time (T_{smin} to T_{smax}) (t_s) 	<ul style="list-style-type: none"> 100 °C 150 °C 60-120 seconds
Ramp up rate T_L to T_p	3 °C/ second max.	3 °C/ second max.
Liquidous temperature (T_L) Time (t_L) maintained above T_L	<ul style="list-style-type: none"> 183 °C 60-150 seconds 	<ul style="list-style-type: none"> 217 °C 60-150 seconds
Peak package body temperature (T_p)*	Table 1	Table 2
Time (t_p)* within 5 °C of the specified classification temperature (T_C)	20 seconds*	40 seconds*
Ramp-down rate (T_p to T_L)	6 °C/ second max.	6 °C/ second max.
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.

* Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com/electronics

© 2020 Eaton
All Rights Reserved
Printed in USA
Publication No. 11219 BU-MC20197
November 2020

Eaton is a registered trademark.
All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

[SMTJ58CAT](#) [SMTJ66CAT](#) [SMTJ76CAT](#) [SMTJ86CAT](#)