

MIN. CAP (UF)		DWV (VDC)	I.R. MIN. @ 100 (VDC.)	WORKING VOLTAGE D.C.		CURRENT DC (AMPS).	MIN. NO LOAD INSERTION LOSS (dB) @ 25°C PER MIL-STD-220						TEMP. CHARAC.
				85°C	125°C		30 KHz	100 KHz	300 KHz	1 MHz	10 MHz	1 GHz	
1.4		300	10 G Ω	100	70	15	15	25	34	44	60	70	X7W

REVISION RECORD Original Release C.O. 6769 METRIC DIMS & NOTES ADDED. E.C. 7-17-92 6789 WVDC REVISED 100 & 70 WERE 80 & 50. L.E. 10-26-92 6992 RDN TO COMP FMT. S.M. 02-14-02 20020213-4-04 WORKING VOLTAGE REV'D 100, 70 WERE 80, 50 & TEMP. CHARAC. ADDED 20020903-1-01 ADDED AND REVISED NOTES. S.M. 09-06-06 20060905-3-01	--TOLERANCES-- Unless Otherwise Specified		Title COAXIAL BROADBAND - "C"					
	DECIMAL ± 							
	ANGLES ± 		Drawn		S.M. 02-14-02		Scale	2 X
	TUSONIX TUCSON, ARIZONA		Approved		T.C. 02-14-02			
			A	4600-000				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[4600-000LF](#)