


STN254033UL33 and STN254033UL50

TVS Diode array ESD suppressor



Product features

- Solid-state silicon-avalanche technology
- Up to four I/O lines of protection
- Low operating and clamping voltage
- Ultra low capacitance
- Low leakage current
- Moisture sensitivity level (MSL): 3
- Molding compound flammability rating: UL 94V-0
- Termination finish: Ni/Pd/Au

Applications

- Serial ATA
- PCI express
- Desktops, servers and notebooks
- MDDI ports
- USB 2.0, 3.0 and 3.1
- Display ports
- HDMI 1.3, 1.4 and 2.0
- Digital visual interfaces (DVI)

Environmental compliance and general specifications



- IEC61000-4-2 (ESD)
 - Up to ± 15 kV (air)
 - Up to ± 15 kV (contact)
- IEC61000-4-5 (Lightning) Up to 7 A (8/20 μ s)



Ordering part number

	ST	N25	4	033	U	L33
Family	_____	_____	_____	_____	_____	_____
Package (N25- DFN2510)	_____	_____	_____	_____	_____	_____
Number of channels (4- 4)	_____	_____	_____	_____	_____	_____
Operating voltage (033- 3.3 V)	_____	_____	_____	_____	_____	_____
Bi/Uni directional (U- Uni)	_____	_____	_____	_____	_____	_____
Capacitance (L33- 0.33 pF)	_____	_____	_____	_____	_____	_____

Pin out/functional diagram



Absolute maximum ratings

(+25 °C, RH=45%-75%, unless otherwise noted)

Parameter	Symbol	Value		Unit
		STN254033UL33	STN254033UL50	
Peak pulse power dissipation on 8/20 μ s waveform	P _{pp}	30	70	W
ESD per IEC 61000-4-2 (Air)	V _{ESD}	+/-15	+/-15	kV
ESD per IEC 61000-4-2 (Contact)		+/-8	+/-15	
Lead soldering temperature	T _L	+260 (10 seconds)	+260 (10 seconds)	°C
Operating junction temperature range	T _J	-55 to +125	-55 to +125	°C
Storage temperature range	T _{STG}	-55 to +150	-55 to +150	°C

Electrical characteristics

(+25 °C)


STN254033UL33

Parameter	Test condition	Minimum	Typical	Maximum	Symbol (Units)
Reverse working voltage	I/O to GND	-	-	3.3	V _{RWM} (V)
Reverse leakage current	I/O to GND V _{RWM} = 3.3 V	-	0.1	1.0	I _R (μ A)
Reverse triggering voltage	I/O to GND I _{ti} = 1 μ A	3.8		-	V _{ti} (V)
Reverse holding voltage	I/O to GND I _{hi} = 50 mA	3.5	5.5	-	V _h (V)
Clamping voltage	I _{pp} = 1 A, t _p = 8/20 μ s	-	8	9	V _C (V)
	I _{pp} = 3 A, t _p = 8/20 μ s	-	10	11	V _C (V)
Junction capacitance	V _{RWM} = 3.3 V, f = 1 MHz I/O pin to GND	-	0.33	0.39	C _J (pF)
	V _{RWM} = 3.3 V, f = 1 MHz Between I/O pins	-	0.2	0.3	C _J (pF)

STN254033UL50

Parameter	Test condition	Minimum	Typical	Maximum	Symbol (Units)
Reverse working voltage	I/O to GND	-	-	3.3	V _{RWM} (V)
Reverse leakage current	I/O to GND V _{RWM} = 3.3 V	0.1	-	-	I _R (μ A)
Reverse breakdown voltage	I/O to GND I _t = 1 mA	4.0		10	V _{BR} (V)
Clamping voltage	I _{pp} = 1 A, t _p = 8/20 μ s	-	5.5	6.5	V _C (V)
	I _{pp} = 5.0 A, t _p = 8/20 μ s	-	7.5	8.5	V _C (V)
	I _{pp} = 7.0 A, t _p = 8/20 μ s	-	9	10.5	V _C (V)
Junction capacitance	V _{RWM} = 0 V, f = 1 MHz I/O pin to GND	-	0.5	0.6	C _J (pF)
	V _{RWM} = 0 V, f = 1 MHz Between I/O pins	-	0.25	0.35	C _J (pF)

Mechanical parameters, pad layout- mm




Dimension	Millimeters			Inches		
	Minimum	Typical	Maximum	Minimum	Typical	Maximum
A	0.45	-	0.65	0.018	-	0.026
A1	0.00	-	0.05	0.000	-	0.002
A2		0.15 REF			0.006 REF	
b	0.15	0.20	0.25	0.006	0.008	0.010
b1	0.35	0.40	0.45	0.014	0.016	0.018
D	2.45	2.50	2.55	0.096	0.098	0.100
E	0.95	1.00	1.05	0.037	0.039	0.041
E1	0.30	0.455	0.61	0.012	0.018	0.024
e		0.50 BSC			0.020 BSC	
L	0.33	-	0.45	0.013	-	0.018

Supplied in tape and reel packaging, 3,000 parts per 7" diameter reel (EIA-481 compliant)


Symbol	Dimensions	
	Millimeters	Inches
A0	1.15±0.05	0.045±0.002
B0	2.70±0.05	0.106±0.002
K0	0.59±0.05	0.023±0.002
P0	4.00±0.10	0.157±0.004
P1	4.00±0.10	0.157±0.004
P2	2.00±0.05	0.079±0.002
T	0.20±0.02	0.008±0.001
E	1.75±0.10	0.069±0.004
F	3.50±0.05	0.138±0.002
D0	1.55±0.05	0.061±0.002
D1	0.60±0.10	0.024±0.004
W	8.0±0.10	0.315±0.004
B	2.0±0.5	0.079±0.020
H	4.0±0.5	0.157±0.020
C	13.0±0.5	0.512±0.020
G	8.4±1.5	0.331±0.059
T1	14.9(max)	0.587(max)
N	60	2.362
D	178±2.0	7±0.079

Ratings and V-I characteristic curves (+25 °C unless otherwise noted)


V- I curve characteristics (Uni-directional)
STN254033UL33




V- I curve characteristics (Uni-directional)
STN254033UL50




Pulse waveform (8/20 μ s)



Pulse derating curve



ESD waveform



Solder reflow profile




Table 1 - Standard SnPb solder (T_C)

Package thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2 - Lead (Pb) free solder (T_C)

Package thickness	Volume mm ³ <350	Volume mm ³ 350 - 2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 – 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Reference J-STD-020

Profile feature	Standard SnPb solder	Lead (Pb) free solder
Preheat and soak		
• Temperature min. (T_{smin})	100 °C	150 °C
• Temperature max. (T_{smax})	150 °C	200 °C
• Time (T_{smin} to T_{smax}) (t_s)	60-120 seconds	60-120 seconds
Ramp up rate T_L to T_p	3 °C/ second max.	3 °C/ second max.
Liquidous temperature (T_L)	183 °C	217 °C
Time (t_L) maintained above T_L	60-150 seconds	60-150 seconds
Peak package body temperature (T_p)*	Table 1	Table 2
Time (t_p)* within 5 °C of the specified classification temperature (T_C)	20 seconds*	30 seconds*
Ramp-down rate (T_p to T_L)	6 °C/ second max.	6 °C/ second max.
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.

* Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com/electronics

© 2020 Eaton
All Rights Reserved
Printed in USA
Publication No. 11136 BU-MC20118
September 2020

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

[STN254033UL33](#) [STN254033UL50](#)