




This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



SPECIFICATIONS

TUSONIX STYLE.	2499-003
Capacitance Value:	1000 pF
Capacitance Tolerance:	-0% +100%
Temp. Characteristics:	X7R
Rating:	250 WVDC @ 125 °C
Current (A):	20
IR Min @ 100 vdc	10 GΩ
DWV	1500 VDC
Operating Range:	-55° TO + 125°C

NOTES:

- SUPPLIED WITH SILVER PLATED HEX NUT AND INTERNAL TOOTH LOCK WASHER.
- TUSONIX STANDARD PART
NUMBER: 2499-003-X7R0-102P.
TUSONIX R.o.H.S. COMPLIANT PART
NUMBER: 2499-003-X7R0-102P LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
- PART MARKING: TRADEMARK, CAPACITANCE CODE AND TOLERANCE CODE STAMPED ON BUSHING HEX FLATS:
STANDARD PART: BLACK MARKING.
RoHS COMPLIANT PART: GREEN MARKING.

X-2015 Rev-0

REVISION RECORD Original Release ECO-2602	A		--TOLERANCES-- Unless Otherwise Specified		Title BUSHING TYPE FEED-THRU CAPACITOR	
			DECIMAL ± .015 [0.38]		Drawn L.E. 01-17-12 Scale 3X	
			ANGLES ±		Approved R.L. 01-17-12	
			TUSONIX TUCSON, ARIZONA		A 2499-003-X7R0-102P	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[2499-003-X7R0-102PLF](#)