

P4SMA

400 W Transient voltage suppressor



Product features

- Low profile SMA package
- Excellent clamping capability
- 400 W peak pulse power capability at 10/1000 μ s waveform
- Typical I_R less than 1 μ A above 12 V
- Fast response time: typically less than 1.0 ps from 0 V to V_{BR} minimum
- High temperature reflow soldering: +260 °C /40 s at terminal
- Plastic package meets UL 94 V-0 flammability rating
- Meets moisture sensitivity level (MSL) level 1
- Terminal: Solder plated leads, solderable per J-STD-002
- For surface mounted applications in order to optimize board space
- UL 497B recognized.
File No. : E198449 Guide QVGQ2

Applications

- Consumer electronics
- Telecommunications
- Computing and servers
- Appliances
- Industrial automation
- Mobile and wearables

Environmental compliance and general specifications





Ordering part number

P4SMA 6-8 C A

Family name _____
 V_R voltage _____
 ("." indicates decimal point) _____
 Bi-/Uni-Directional _____
 (Blank=Uni, C=Bi)
 Voltage tolerance _____

PIN configuration




Absolute maximum ratings

(+25 °C, RH=45%-75%, unless otherwise noted)

Parameter	Symbol	Value	Unit
Storage operating junction temperature range	T_{STG}/T_J	-55 to +150	°C
Steady state power dissipation at $T_L = +75$ °C	$P_{M(AV)}$	3.3	W
Peak pulse power dissipation on 10/1000 μ s waveform	P_{PP}	400	W
Maximum instantaneous forward voltage at 100 A for unidirectional	V_F	5.0	V
Peak forward surge current, 8.3 ms single half sine wave ¹	I_{FSM}	60	A
Typical thermal resistance junction to lead	$R_{\theta JL}$	30	°C/W
Typical thermal resistance junction to ambient	$R_{\theta JA}$	120	°C/W

1. Measured on 8.3 ms single half sine wave or equivalent square wave for unidirectional device only, duty cycle = 4 per minute maximum

Mechanical parameters, pad layout- mm



Dimension	Millimeters		Inches	
	Minimum	Maximum	Minimum	Maximum
A	2.60	3.00	0.102	0.118
B	4.15	4.65	0.163	0.183
C	1.25	1.65	0.049	0.065
D	0.95	1.52	0.037	0.060
E	4.90	5.30	0.193	0.209
F	0.051	0.203	0.002	0.008
G	0.15	0.31	0.006	0.012
H	2.00	2.44	0.079	0.096
J	2.00		0.079	
K		2.30		0.091
L	1.80		0.071	

Part marking




Cathode band (Uni-polar only)

Part marking: xxxx = Date code
yyyy- Refer to marking designator listed in Electrical Characteristics table

Packaging information (mm)

Drawing not to scale.

Supplied in tape and reel packaging, 5,000 parts per 13" diameter reel (EIA-481 compliant)




Dimensions	Millimeters	Inches
A0	2.79 ± 0.3	0.110 ± 0.012
B0	5.33 ± 0.3	0.210 ± 0.012
C	330.0	13.0
D0	1.55 ± 0.1	0.061 ± 0.004
E	1.75 ± 0.2	0.069 ± 0.008
E1	13.3 ± 0.3	0.524 ± 0.012
F	5.50 ± 0.2	0.217 ± 0.008
P0	4.00 ± 0.2	0.157 ± 0.008
P1	4.00 ± 0.2	0.157 ± 0.008
P2	2.00 ± 0.2	0.079 ± 0.008
W	12.0 ± 0.2	0.479 ± 0.008
W1	15.7 ± 2.0	0.618 ± 0.079

Electrical characteristics (+25 °C)


Part number		Marking		V_R	$I_R @ V_R$	$V_{BR} @ I_T$		I_T	$V_C @ I_{PP}$	I_{PP}
Uni-polar	Bi-polar	Uni	Bi	(V)	(μ A)	min (V)	max (V)	(mA)	max (V)	(A)
P4SMA6-8A	P4SMA6-8CA	6V8A	6V8C	5.8	120	6.45	7.14	10	10.5	39
P4SMA7-5A	P4SMA7-5CA	7V5A	7V5C	6.4	80	7.13	7.88	10	11.3	36.3
P4SMA8-2A	P4SMA8-2CA	8V2A	8V2C	7.02	50	7.79	8.61	10	12.1	33.9
P4SMA9-1A	P4SMA9-1CA	9V1A	9V1C	7.78	20	8.65	9.55	1	13.4	30.6
P4SMA10A	P4SMA10CA	10A	10C	8.55	10	9.5	10.5	1	14.5	28.3
P4SMA11A	P4SMA11CA	11A	11C	9.4	5	10.5	11.6	1	15.6	26.3
P4SMA12A	P4SMA12CA	12A	12C	10.2	2	11.4	12.6	1	16.7	24.6
P4SMA13A	P4SMA13CA	13A	13C	11.1	1	12.4	13.7	1	18.2	22.5
P4SMA15A	P4SMA15CA	15A	15C	12.8	1	14.3	15.8	1	21.2	19.3
P4SMA16A	P4SMA16CA	16A	16C	13.6	1	15.2	16.8	1	22.5	18.2
P4SMA18A	P4SMA18CA	18A	18C	15.3	1	17.1	18.9	1	25.2	16.1
P4SMA20A	P4SMA20CA	20A	20C	17.1	1	19	21	1	27.7	14.8
P4SMA22A	P4SMA22CA	22A	22C	18.8	1	20.9	23.1	1	30.6	13.4
P4SMA24A	P4SMA24CA	24A	24C	20.5	1	22.8	25.2	1	33.2	12.3
P4SMA27A	P4SMA27CA	27A	27C	23.1	1	25.7	28.4	1	37.5	10.9
P4SMA30A	P4SMA30CA	30A	30C	25.6	1	28.5	31.5	1	41.4	9.9
P4SMA33A	P4SMA33CA	33A	33C	28.2	1	31.4	34.7	1	45.7	9
P4SMA36A	P4SMA36CA	36A	36C	30.8	1	34.2	37.8	1	49.9	8.2
P4SMA39A	P4SMA39CA	39A	39C	33.3	1	37.1	41	1	53.9	7.6
P4SMA43A	P4SMA43CA	43A	43C	36.8	1	40.9	45.2	1	59.3	6.9
P4SMA47A	P4SMA47CA	47A	47C	40.2	1	44.7	49.4	1	64.8	6.3
P4SMA51A	P4SMA51CA	51A	51C	43.6	1	48.5	53.6	1	70.1	5.8
P4SMA56A	P4SMA56CA	56A	56C	47.8	1	53.2	58.8	1	77	5.2
P4SMA62A	P4SMA62CA	62A	62C	53	1	58.9	65.1	1	85	4.8
P4SMA68A	P4SMA68CA	68A	68C	58.1	1	64.6	71.4	1	92	4.5
P4SMA75A	P4SMA75CA	75A	75C	64.1	1	71.3	78.8	1	103	4
P4SMA82A	P4SMA82CA	82A	82C	70.1	1	77.9	86.1	1	113	3.6
P4SMA91A	P4SMA91CA	91A	91C	77.8	1	86.5	95.5	1	125	3.3
P4SMA100A	P4SMA100CA	100A	100C	85.5	1	95	105	1	137	3
P4SMA110A	P4SMA110CA	110A	110C	94	1	105	116	1	152	2.7
P4SMA120A	P4SMA120CA	120A	120C	102	1	114	126	1	165	2.5
P4SMA130A	P4SMA130CA	130A	130C	111	1	124	137	1	179	2.3
P4SMA150A	P4SMA150CA	150A	150C	128	1	143	158	1	207	2
P4SMA160A	P4SMA160CA	160A	160C	136	1	152	168	1	219	1.9
P4SMA170A	P4SMA170CA	170A	170C	145	1	162	179	1	234	1.8
P4SMA180A	P4SMA180CA	180A	180C	154	1	171	189	1	246	1.6
P4SMA200A	P4SMA200CA	200A	200C	171	1	190	210	1	274	1.5
P4SMA220A	P4SMA220CA	220A	220C	185	1	209	231	1	328	1.3
P4SMA235A	P4SMA235CA	235A	235C	200	1	223	246	1	324	1.3
P4SMA250A	P4SMA250CA	250A	250C	214	1	237	263	1	344	1.2
P4SMA300A	P4SMA300CA	300A	300C	256	1	285	315	1	414	1
P4SMA350A	P4SMA350CA	350A	350C	300	1	332	368	1	482	0.9
P4SMA400A	P4SMA400CA	400A	400C	342	1	380	420	1	548	0.8
P4SMA440A	P4SMA440CA	440A	440C	376	1	418	462	1	602	0.7

Ratings and V-I characteristic curves (+25 °C unless otherwise noted)

V- I curve characteristics (Uni-directional)



V- I curve characteristics (Bi-directional)



Surge waveform: 10/1000 μ s

V_R : Stand-off voltage – Maximum voltage that can be applied

V_{BR} : Breakdown voltage


V_C : Clamping voltage – Peak voltage measured across the suppressor at a specified I_{PP}

I_R : Reverse leakage current


I_T : Test current

V_F : Forward voltage drop for Uni-directional TVS diode


Pulse waveform



Pulse derating curve



Peak pulse power dissipation vs. pulse width



Solder reflow profile



Table 1 - Standard SnPb solder (T_C)

Package thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2 - Lead (Pb) free solder (T_C)

Package thickness	Volume mm ³ <350	Volume mm ³ 350 - 2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 - 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Reference J-STD-020

Profile feature	Standard SnPb solder	Lead (Pb) free solder
Preheat and soak		
• Temperature min. (T_{smin})	100 °C	150 °C
• Temperature max. (T_{smax})	150 °C	200 °C
• Time (T_{smin} to T_{smax}) (t_s)	60-120 seconds	60-180 seconds
Ramp up rate T_L to T_p	3 °C/ second max.	3 °C/ second max.
Liquidous temperature (T_L)	183 °C	217 °C
Time (t_L) maintained above T_L	60-150 seconds	60-150 seconds
Peak package body temperature (T_p)*	Table 1	Table 2
Time (t_p)* within 5 °C of the specified classification temperature (T_C)	20 seconds*	40 seconds*
Ramp-down rate (T_p to T_L)	6 °C/ second max.	6 °C/ second max.
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.

* Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com/electronics

© 2020 Eaton
All Rights Reserved
Printed in USA
Publication No. 11211 BU-MC20189
November 2020

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

[P4SMA120A](#) [P4SMA16A](#) [P4SMA36A](#) [P4SMA56A](#) [P4SMA75CA](#) [P4SMA30A](#) [P4SMA68A](#) [P4SMA62CA](#)
[P4SMA235CA](#) [P4SMA170CA](#) [P4SMA12CA](#) [P4SMA18A](#) [P4SMA200CA](#) [P4SMA51A](#) [P4SMA30CA](#) [P4SMA250A](#)
[P4SMA16CA](#) [P4SMA33CA](#) [P4SMA24A](#) [P4SMA47CA](#) [P4SMA300A](#) [P4SMA39CA](#) [P4SMA10CA](#) [P4SMA440A](#)
[P4SMA15CA](#) [P4SMA235A](#) [P4SMA250CA](#) [P4SMA160CA](#) [P4SMA440CA](#) [P4SMA100A](#) [P4SMA22CA](#) [P4SMA13CA](#)
[P4SMA13A](#) [P4SMA100CA](#) [P4SMA20A](#) [P4SMA400A](#) [P4SMA220A](#) [P4SMA91A](#) [P4SMA160A](#) [P4SMA47A](#)
[P4SMA75A](#) [P4SMA56CA](#) [P4SMA170A](#) [P4SMA27A](#) [P4SMA51CA](#) [P4SMA27CA](#) [P4SMA130CA](#) [P4SMA12A](#)
[P4SMA43CA](#) [P4SMA68CA](#) [P4SMA15A](#) [P4SMA20CA](#) [P4SMA91CA](#) [P4SMA18CA](#) [P4SMA82CA](#) [P4SMA62A](#)
[P4SMA350CA](#) [P4SMA180CA](#) [P4SMA200A](#) [P4SMA300CA](#) [P4SMA33A](#) [P4SMA11CA](#) [P4SMA150A](#) [P4SMA110A](#)
[P4SMA82A](#) [P4SMA22A](#) [P4SMA220CA](#) [P4SMA130A](#) [P4SMA110CA](#) [P4SMA180A](#) [P4SMA10A](#) [P4SMA43A](#)
[P4SMA150CA](#) [P4SMA11A](#) [P4SMA24CA](#) [P4SMA36CA](#) [P4SMA39A](#) [P4SMA350A](#) [P4SMA120CA](#) [P4SMA400CA](#)