


SMARC-sAMX6i



SMARC - Smart Mobility Architecture

- ▶ Ultra low power COM based on Freescale™ i.MX6 family
- ▶ SoC scalable from Solo Core up to Quad Core
- ▶ Commercial and industrial temperature versions

POSSIBILITIES START HERE



► TECHNICAL INFORMATION

PROCESSOR	NXP i.MX 6 Solo, Dual and Quad Core ARM Cortex-A9 800 MHz, 1.0 GHz, 1.2 GHz
GRAPHICS	Dual Display HD 1080p encode and decode 2D and 3D acceleration
MEMORY	DDR3 up to 2 GByte, memory down
FLASH	Up to 64 GByte NAND/eMMC on-module (Custom Option)
ETHERNET	10/100/1000 Mbit/sec
USB	3x USB 2.0 port (one OTG)
DISPLAY	Parallel LCD 18/24 bit LVDS Single Channel 18/24bit HDMI
IMAGE CAPTURE INTERFACES	2 Interfaces (PCAM, CSI)
SERIAL	2x RX/TX (Ser1/3); 2x UART (Ser0/2)
ADDITIONAL INTERFACES	Up to 3 PCIe x1, MLB150, 12x GPIOs, SDIO, SATA eMMC, 2x SPI, 5x I ² C, 2x I ² S, SPDIF, WDT, 2x CAN, Battery and System Management
SW SUPPORT	Linux
POWER	tbd
THERMAL	Commercial temperature: 0 °C to +60 °C and Industrial temperature: -40 °C to 85 °C (800 MHz versions)
POWER SUPPLY	3 V to 5.25 V - Operates directly from single level Lithium Ion cells, or fixed 3.3 V or 5 V power supplies
COMPLIANCE	Form Factor: 82 x 50 mm Compliance: SMARC (Smart Mobility Architecture) specification by SGET

► ORDERING INFORMATION

ARTICLE*	PART NO.	DESCRIPTION
SMARC-SAMX6I 0.8 512/4 GB	51003-0540-08-1	SMARC with NXP i.MX6 Solo, 800 MHz single core, 512 MByte DRAM memory down, 4 GByte onboard Flash, industrial temperature, no SATA support
SMARC-SAMX6I 2X0.8 1/4 GB	51003-1040-08-2	SMARC with NXP i.MX6 Dual, 800 MHz dual core, 1 GByte DRAM memory down, 4 GByte onboard Flash, industrial temperature, with SATA support
SMARC-SAMX6I 4X0.8 1/4 GB	51003-1040-08-4	SMARC with NXP i.MX6 Quad, 800 MHz quad core, 1 GByte DRAM memory down, 4 GByte onboard Flash, industrial temperature, with SATA support
SMARC-SAMX6I 4X0.8 2/2 GB	51003-2040-08-4	SMARC with NXP i.MX6 Quad, 800 MHz quad core, 2 GByte DRAM memory down, 4 GByte onboard Flash, industrial temperature, with SATA support

*Please ask for more SoC or memory configurations.

► GLOBAL HEADQUARTERS

Kontron Europe GmbH

Gutenbergstraße 2
85737 Ismaning, Germany
Tel.: +49 821 4086-0
Fax: +49 821 4086-111
info@kontron.com

www.kontron.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kontron:

[51003-0540-08-1](#) [51003-1040-08-2](#) [51003-1040-08-4](#)