


K3932-N mITX

Industrial Series



Intel® Core™ i3 Processors & Intel® Processors N Series (Alder Lake N)

- Latest DDR5 memory technology for best-in-class system performance
- Intel® UHD Gen12 Graphics - driven by Intel® X^e architecture (within SoC)
- Up to 3x DisplayPort V1.4
- Dual Channel LVDS (24 Bit) and eDP V1.4b (4 K) onboard
- SATA CFast connector


K3932-N mITX Industrial Series

The Industrial Motherboard K3932-N mITX supports the Intel® Core™ i3 and Intel® Processor series (Alder Lake N) with latest UHD Gen12 graphics based on Intel® Xe architecture. It is equipped with three DisplayPorts, one embedded DisplayPort and one Dual-Channel LVDS (24bit) and supports three independent displays with up to 3x 4K resolution. It is also equipped with

extension slots for PCIe, M.2 and CFAST, and offers many other functions like GPIO, four COM ports, one ccTalk port and USB 3.2 Gen2. Designed and approved for 24/7 continuous operation and an enhanced temperature range up to 60 °C the K3932-N mITX fits perfectly with special requirements of certain markets.

- Intel® Core™ i3/Processor series (Alder Lake N)
- cTDP – Easy & flexible reduction of CPU TDP down to 6 W
- DDR5-4800 SODIMM, max 32 GByte
- Intel® UHD Gen12 Graphics (within SoC)
- Up to 3x DisplayPort V1.4a
- Dual Channel LVDS (24 bit) and eDP V1.4b
- PCI Express® x1 (Gen3, mechanical x4)
- 8 Bit GPIO & HD Audio onboard
- 3x USB 2.0, 4x USB 3.2 Gen1, 4x USB 3.2 Gen2
- Internal USB 3.2 Gen2 Key-A for USB-C extension cable
- Internal USB2 Stick socket
- 1x Realtek GbE LAN, 1x 2.5GbE incl. Teaming
- 1x SATA 6G
- 1x M.2 2230/2242/2280 (Key-M, PCIe x2 Gen3/NVMe SSD modules)
- 1x CFAST (SATA CF cards)
- 1x M.2 2230 (Key-E, WLAN/Bluetooth modules, CNVi support only)

- Intel® integrated iTPM V2.0
- 4x RS-232 support onboard (1x incl. RS485/422) + 1x ccTalk
- HW Watchdog onboard
- WideRange internal/external DC input (8 V – 34 V)



Technical Information

SYSTEM	PROCESSOR	Intel® Alder Lake N SoC series N2: Intel® Processor N97 (4C/12W) SoC N4: Intel® Processor N200 (4C/6W) SoC N6: Intel® Core™ i3 N305 (8C/15W) SoC DDR5 4800 SDRAM 1x SO DIMM socket, up to 32 GByte memory, non-ECC
VIDEO	MEMORY	
	GRAPHICS	Intel® UHD Graphics driven by Intel® Xe with up to 32 execution units (EUs) Up to 3x DPP V1.4a (up to 4K resolution ¹⁾) 1x Embedded DP (eDP V1.4b up to 4K resolution ²⁾) 1x Dual-Channel 24bit LVDS Following max. display combinations are supported: 3x DPP / 2x DPP + LVDS or eDP / 1x DPP + eDP + LVDS
AUDIO	AUDIO CODEC	Realtek ALC256
	AUDIO INTERFACE	Stereo ³ , High Definition Audio Codec
NETWORK CONNECTION	ETHERNET 1	Realtek RTL8111H with 10/100/1000 MBit/s, Wake-on-LAN (WoL) by interesting Packets, Link Status Change and Magic Packet™, PXE Support, BIOS MAC Address Display, Teaming Support
	ETHERNET 2	Intel® i226LM with 10/100/1000/2500 MBit/s, TSN Support, Wake-on-LAN (WoL) by interesting Packets, Link Status Change and Magic Packet™, PXE Support, BIOS MAC Address Display, Teaming Support
PERIPHERAL CONNECTION	USB	3x USB 2.0 (by header), 1x USB 2.0 stick socket 2x USB 3.2 Gen1 (Rear), 2x USB 3.2 Gen1 (by header) 2x USB 3.2 Gen2 (Rear), 1x USB 3.2 Gen2 Key A (header) for USB3 Type-C option
	SERIAL PORT	1x RS232/422/485; 3x RS232, 1x ccTalk (2x RearIO, 3x by header)
	OTHER I/Os	8 Bit GPIO (by header); WLAN LED support, WLAN enable/disable support 3.3 V/5 V/12 V supply voltage output; SMBus controller PCA9554A

1) 3x 4K support only with K39xx-N2 (N97). All other boards: 2x 4K + 1x FHD
2) 4K Resolution on eDP only with K39xx-N2 (N97)

STORAGE & EXPANSION	SATA PCIe/M.2 SLOTS	1x Serial ATA III 600 Interface (up to 6Gbit/s), NCQ, AHCI, 1x M.2 PCIe 2230/2242/2280 (Key-M, PCIe x2 Gen3/NVMe SSD modules) 1x CFast (SATA CF cards) 1x M.2 PCIe 2230 (Key-E, WLAN CNVi only/Bluetooth USB modules) 1x PCIe x4 (1 lane, Gen3, open slot)
POWER	CONNECTOR INPUT VOLTAGE	External/Internal DC-In (DC Jack/4-Pin Mini-Fit) DC Input 8 V - 34 V (max. 10 A/max. 130 W)
FIRMWARE	BIOS	AMI Aptio 5.x (UEFI) BIOS modified and adapted by Kontron; Recovery BIOS, SM-BIOS (DMI), BIOS and CPU Microcode Update, Quick Boot, Logo Boot, Quiet Boot, Plug & Play, Automatic DRAM and PCIe Configuration, BIOS Support for S.M.A.R.T., Advanced Power Management, ACPI S3/S4, Wake on time from S5. No legacy OS support, no MBR installation (UEFI only) BIOS POST-/BIOS BOOT-/OS-HW Watchdog
SYSTEM CONTROL	WATCHDOG REAL TIME CLOCK TPM	Integrated TPM V2.0 (Intel® integrated)
	FP HEADER SECURITY	1x Header for Reset button, HDD LED, Power button, Power LED Recovery BIOS, System and BIOS Password, Boot Sequence Control, Serial-/USB-Port Access Protection, Write Protection for Flash BIOS, EraseDisk (BIOS Feature), Intel integrated TPM V2.0
COOLING	FAN	2x PWM fan (CPU/System)
SOFTWARE	OS SUPPORT	MS Windows 10, MS Windows 11, MS Windows 10 IoT, Linux-64 No legacy OS support, no MBR installation (UEFI only)
MECHANICAL	DIMENSION (L x W)	Mini-ITX: 6.7" x 6.7" (170 x 170 mm)
ENVIRONMENTAL	OPERATION TEMPERATURE	0 °C - 60 °C
CERTIFICATION	EMC SAFETY	CE Class B, Industrial Immunity (EN 61000-6-2), FCC-B/ICES-003 verified, UKCA cTUVus acc. IEC62368-1

Motherboard Versions

	PROCESSOR (SoC)	GRAPHICS Intel® UHD Gen12 Gfx	MEMORY
K3932-N6	Intel® Core® i3 N305 Octa-Core @ 15 W TDP (Flex cTDP option**) TDP 15 W: 1.8/3.8/3 GHz* TDP 9 W: 1.0/3.8/3 GHz*	GPU @ 1/1.25 GHz 32x EU Up to 3 displays (2x 4K + 1x FHD)	DDR5-4800 One socket Max. 32 Gbyte
K3932-N4	Intel® Processor N200 Quad-Core @ 6 W TDP 1.0/3.7/3.2 GHz*	GPU @ 0.45/0.75 GHz 32x EU Up to 3 displays (2x 4K + 1x FHD)	DDR5-4800 One socket Max. 32 Gbyte
K3932-N2	Intel® Processor N97 Quad-Core @ 12 W TDP (Flex cTDP option**) 2.0/3.6/2.9 GHz*	GPU @ 0.85/1.2 GHz 24x EU Up to 3 displays (3x 4K)	DDR5-4800 One socket Max. 32 Gbyte

*) Base Frequency / 1 core Turbo / Multi core Turbo

**) cTDP – Easy & flexible reduction of CPU TDP down to 6 W

Power Supply Requirements

SOURCE	VOLTAGE RANGE	MIN. PS LOAD	MAX. VOLTAGE TOLERANCE	TYP. MOTHERBOARD INPUT POWER ¹	MAX. MOTHERBOARD INPUT POWER ²
DC-IN (wide range)	8 V - 34 V (recommended nominal range) 7.6 V - 36 V (absolute maximum ratings)	0 A	± 5 %	<10 W / 25 W	130 W

1) Motherboard incl. Memory and M.2 NVME SSD (approximations for MS Windows 10 Idle Mode / Full Processor Load @ 15 W TDP

2) Motherboard incl. Memory, M.2, PCIe/M.2 PCIe devices, USB

See TechNotes document for detailed power requirements

FEATURES	Chipset / SoC (APU) DPP / HDMI / LVDS / eDP Stereo Audio / 5.1 Multichannel Audio / Front Panel Audio Buzzer / int. Speaker Support (stereo) ² GbE LAN / Dual GbE LAN / 2.5GbE LAN WoL / PXE / LAN Teaming / TSN SATA / SATA RAID / cFast (SATA) / M.2 (SATA) / M.2 (PCIe/NVME) USB 2.0 / USB 3.2 (Gen1) / USB 3.2 (Gen2) / USB 3.2 (Gen2) Type-C FAN monitored & controlled CPU / AUX1 / AUX2 TEMP monitored CPU / onboard sensors / external sensor	Intel® Alderlake-N SoC + / - / + / + + / 0 ¹ / + + / + + / - / + + / + / + / + + / - / + / - / + + / + / + / 0 ³ + / + / - + / + / -
SPECIAL FEATURES	COM interface support for RS-232 / RS-485 / RS-422 Silent Fan / System Guard Recovery BIOS / Flash Update / Multi Boot HDD Password / EraseDisk / TPM V2.0 onboard / optional TPM module BIOS POST- / BIOS Boot- / OS- HW Watchdog Operating Mode 24-7 / 8-5 (hrs per day - days per week) Motherboard operating temperature range (chassis inside) ⁴	+ + / + + / + / + + / + / + / - + / + / + + / - 0 °C ... +60 °C
INTERNAL CONNECTORS	SO DIMM Sockets (DDR5 4800) PCI Express® x4: 1 lanes, Gen3 / Mini-PCIe SATA-III / M.2 Key-M SSD / M.2 Key-B M.2 2230 (Key-E for WLAN/Bluetooth) Front Panel Audio (9-Pin, HD Audio) / S-PDIF Out (Digital Audio) USB 2.0 pin header (2 port) / USB 2.0 single port header / USB Stick socket ⁵ USB 3.2 Gen1 pin header (2 ports) ⁶ / USB 3.2 Gen2 Key-A header ³ Serial COM header / CCTalk header / Parallel Port header LVDS / LVDS Backlight / Embedded DisplayPort @ 4 lanes FAN PSU / CPU (PWM) / AUX1 (PWM) Intrusion (Case Open) / GPIO (8 Bit) / SMBus Stereo Speaker header / Digital Mic header Front Panel (Power Switch, Reset Switch, LEDs, Intel 10 pin header) SATA Drive Power Connector (5 V/12 V) / DC-In Connector 8-34 V (4 pin)	1 1 / - 1 / 1 / 1 1 1 / 1 1 / 1 / 1 1 / 1 2 / 1 / - 1 / 1 / 1 - / 1 / 1 1 / 1 / 1 1 / - 1 1 / 1
EXTERNAL CONNECTORS	DisplayPort V1.4 / HDMI / DVI / VGA Audio Mic. In / Line in / Line out (or driver configuration) LAN (RJ-45) / PS/2 Keyboard / Mouse USB 2.0 / USB 3.2 Gen1 / USB 3.2 Gen2 DC-In connector (external input) 8-34 V @ 10 A max.; lockable Serial COM interface ⁷	3 / - / - / - - / 1 / 1 2 / - / - 0 / 2 / 2 1 2

1) Multichannel audio only via S/PDIF or DPP

2) Stereo speaker support; 2 W @4Ω

3) Type-C available via Adapter Cable


4) Forced cooling required for high operating temperature range. See TechNotes document for details

5) USB 2.0

6) USB3 connector includes separate USB 2.0 signal pins (2 channels)

7) RS-232; Thereof one port (COM2) supporting RS-232/RS-422/RS-485

Connector/Socket Diagram



Ordering Information

K3932-N mITX

ARTICLE	PART NO.	DESCRIPTION
K3932-N2 mITX	F5120-V222	Intel® Processor N97 (4C, 12 W), CFast
K3932-N4 mITX	F5120-V224	Intel® Processor N200 (4C, 6 W), CFast
K3932-N6 mITX	F5120-V226	Intel® Core® i3 N305 (8C, 15 W), CFast

Accessories

SLIM ACTIVE HEATSINK + BACKPLATE	F5000-C026	max. 15 W TDP
FANLESS HEATSINK + BACKPLATE	F5000-C025	max. 15 W TDP
RISERCARD	S26361-F5000-R006	1x PCIe X4
SERIAL PORT CABLE	S26361-F5000-K010	400 mm, fullsize slot bracket
USB-C GEN2 REAR EXTENSION CABLE	F5000-K013	USB 3.2 Gen2 adapter cable for internal USB Key-A socket
INTERNAL PSU KIT	S26361-F5000-P004	12 V/65 W, designed for SMARTCASE™ chassis
AC-ADAPTER 19V/65W	S26361-F5000-P006	For applications up to 35 W TDP (SoC)
AC-ADAPTER 20V/120W	S26361-F5000-P007	lockable connector
DRIVE POWER CABLE	S26361-F5000-K001	400 mm, power connector for 1x SATA and 1x slimline DVD

Global Headquarters

Kontron Europe GmbH

Gutenbergstraße 2
85737 Ismaning, Germany
Tel.: + 49 821 4086-0
info@kontron.com

www.kontron.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kontron:](#)

[F5120-V226](#) [F5120-V222](#) [F5120-V224](#)