

DATASHEET

Qseven System-on-Module

Hexa-Core ARM Cortex-A72/A53 featuring the Rockchip RK3399 application processor



70x70mm
Qseven



Secure
Element



ARMv8



2x 2.0GHz
4x 1.4GHz



up to 4GB
DDR3-1600



HDMI 2.0
2160p



eDP



2x MIPI-DSI



2x MIPI-CSI



PCIe 2.1



Gigabit
Ethernet



3x USB3.0
1x USB2.0



CAN

Best-in-class scalability with a hexa-core big.LITTLE configuration

Built on the industry-leading Rockchip RK3399, the **RK3399-Q7** module redefines the performance expected of embedded processor modules.

The RK3399 is a low power, high performance processor for computing, personal mobile internet devices and other smart device applications. Based on a big.LITTLE architecture, it integrates a dual-core Cortex-A72 and a quad-core Cortex-A53. These 64bit-capable ARMv8 processors support both the ARM Cryptographic Extension (e.g. for wire-rate AES encryption) and AdvSIMD vector processing.

A dual-channel memory interface sustains the memory bandwidths required by even the most demanding embedded applications.

Ready for visual computing and image processing applications

The **RK3399-Q7** module unlocks new application areas that require visual computing and image processing.

Content can be output on 3 independent display interfaces concurrently via HDMI 2.0, eDP and two MIPI-DSI interfaces. The ability to receive camera sensor input through two independent MIPI-CSI interfaces and to process the resulting imagestream in real-time with the powerful ARM processor cores enables a new class of vision and image-analytics applications.

The RK3399 supports multi-format video decoding (including H.264 and H.265 at 2160p60) and video encoding. An embedded high-performance ARM Mali T-864MP4 GPU supports OpenGL ES1.1/2.0/3.0/3.1 and OpenCL. A dedicated 2D hardware engine provides offloading for image scaling, rotation and window composition.

Connect to networks at Gigabit Ethernet speed

The **RK3399-Q7** module continues the design paradigm of our other embedded products. Gigabit Ethernet is a built-in peripheral of the RK3399 which ensures wire-rate throughput without any artificial performance bottlenecks and utilises the full capabilities of DMA to the main memory.

Connecting to industrial I/O modules through a 4-lane PCI-Express 2.1 interface

Industrial applications often require access to customer-specific I/O fabrics or programmable logic resources. With the **RK3399-Q7** module, customer-specific and standard off-the-shelf peripherals can be connected through a 4-lane PCI-Express 2.1 interface. On top of this, the **RK3399-Q7** module makes it easy to build application-specific PCIe accelerator cards by configuring it as a PCIe endpoint.

Enabling high-bandwidth connections through USB 3.0 SuperSpeed ports

As a high-bandwidth interconnect to external peripherals and storage devices, the **RK3399-Q7** module supports three USB 3.0 (with one port operating either in host or device mode) and one legacy USB 2.0 ports. Utilising USB 3.0 SuperSpeed, applications can transfer up to 5Gb/s per port.

State-of-the-art security for your assets

The **RK3399-Q7** features a secure element featured in all our system-on-module products. Enjoy the peace of mind afforded by a government-grade security solution for all identification, key-storage and asset-protection requirements. A Common Criteria (EAL4+) certified security module ensures that you will never again have to sacrifice security for performance.

Built on a GlobalPlatform 2.2.1 compliant JavaCard environment, the **RK3399-Q7** module provides a trusted foundation for security applications including digital asset protection, secure key-storage and remote device authentication.


Designed and supported in Vienna, Austria

Every module we design is backed by our expertise in system-level design, embedded software engineering and performance engineering. Our experienced engineering team offers engineering services to augment your in-house design resources—bringing your design faster to market.

Technical Summary

Form factor	Qseven 2.1
Processor	Rockchip RK3399 Hexa-Core ARM Cortex-A72/A53, up to 2.0GHz 2x Cortex-A72 (48KB+32KB L1 cache and 1024KB L2 cache) 4x Cortex-A53 (32KB+32KB L1 cache and 512KB L2 cache) ARM Mali T-864MP4 GPU Multi-format video encoding/decoding co-processor video decoding up to 2160p (60fps) video encoding up to 1080p (30fps)
Memory ¹	DDR3-1600 (2 independent channels, each 32 bit wide), up to 4GB on-module
NOR Flash ²	SPI NOR flash on-module
eMMC Flash ³	Up to 128GB eMMC on-module
Ethernet	10/100/1000 Mbps (with an on-module triple-speed GbE PHY)
USB	1x USB 3.0 SuperSpeed dual-role port 2x USB 3.0 SuperSpeed host port 1x USB 2.0 high-speed host ports
PCI-Express	4-lane PCIe 2.1, up to 5GT/s
Display ^{4,5,6}	HDMI 2.0, up to 2160p (60fps) 2x MIPI-DSI, each up to 2560x1600 (60fps) Embedded DisplayPort (eDP), up to 4 lanes (2.7Gb/s each)
Camera ^{6,7}	2x MIPI-CSI, each with 4 lanes (up to 1.5Gb/s per lane)
CAN	On-module communication offload controller for CAN
Additional Interfaces	UART, 8x GPIO, I ² S, I ² C, SMBus, SPI, FAN
Security Module	Global Platform 2.2.1 compliant JavaCard environment On-module state-of-the-art, EAL4-certified smartcard controller Note: Custom board variants may exclude the security-module option.
Operating Systems	Linux Android
Power Management	DVFS for thermal and power management
Power Supply	Operates from a single 5V supply
Consumption	< 15W
Operating environment	Commercial 0°C to 60°C Industrial -20°C to 85°C
Dimensions	70mm x 70mm (2.75" x 2.75")

¹ Orderable memory configurations: 512MB, 1GB, 2GB (standard configuration), 4GB
² Orderable SPI NOR flash configurations: 16Mb (standard configuration), 32Mb, 64Mb, 128Mb
³ Orderable eMMC flash configurations: 8GB (standard configuration), 16GB, 32GB, 64GB, 128GB
⁴ The RK3399 supports three concurrent active display output channels.
⁵ Embedded DisplayPort (eDP) and the primary MIPI-DSI controller share the QSeven "LVDS-A" pin-group.
⁶ The secondary MIPI-DSI controller and the secondary MIPI-CSI controller shares the QSeven "LVDS-B" pin-group.
⁷ The primary MIPI-CSI controller is available through the QSeven CSI feature connector.



Theobroma Systems Design und Consulting GmbH

Seestadtstrasse 27
1220 Wien, Austria

voice
fax
web
email

+43-1-2369893-0
+43-1-2369893-9
www.theobroma-systems.com
sales@theobroma-systems.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Theobroma Systems:

[SOM-RK3399-Q7-2.1-C-2048M-8G-CAN](#) [SOM-RK3399-Q7-2.1-I-4096M-32G-CAN](#)