

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.

SINGLE POLE			
Keylock Option	Lock Diagram	Key Position	Terminals Connected
K1 Series	100	1	8-1
	101	3	1-3
	102	3	3-1
	107	1	7-1
	108	5	6-7
	118	1	8-1
K2 Series	100	2 (Mom)	1-2
	101	5	6-7
	102	2 (Mom)	1-2
	118	2 (Mom)	1-2

TYPE K1

Key Code No.

3/4-24 uns thd.

.695 Dia.

.396

.960

.249

.225

TYPE K2 (Momentary) Standard

Key Code No.

3/4-24 uns thd.

.695 Dia.

.396

1.320

.249

.225

DOUBLE POLE

Keylock Option No.	Lock Diagram	Key Position	Terminals Connected
K1 Series	200	1	8-1, 4-5
	201	3	1-3, 5-7
	202	3	1-3, 5-7
K2 Series	206	1	8-1, 4-5
	201	2 (Mom)	1-2, 5-6
	206	2 (Mom)	1-2, 5-6

DIMENSIONS IN INCHES (MILLIMETERS)


DO NOT SCALE DRAWING

Dwg. No.

KEYLOCK SERIES

0 New.
DW 4/10/23 CH 4/11/23


1 Redrawn. Added Key Code to Order
Chart. DW 8/22/23




Electrical/Mechanical Specifications:
Contact ratings: 8A 125VAC, 4A 28VDC, 4A 250VAC; UL Recognized.
4A 125VAC, 4A 28VDC, 2A 250VAC; CSA Certified.
Electrical life: 10,000 cycles min. at full load.
Indexing: 45° or 90°, single-pole styles 3 positions max.,
double-pole styles 3 positions max.,
various key pull positions available.

Materials & Features:
Lock: Five tumblers brass mechanism - Zinc alloy nickel plated.
Face / Shell: Zinc Alloy nickel plated (std.); stainless steel optional.
Switch Housing: 6/6 Nylon (UL94V-2).

Panel Mounting




Terminal Standard



⊖ = Key Removable in this position.

Mounting Options

Panel Nut: .250 in. max.
Thickness Clip: .065 - .090 in.



Ordering Information:

K — [] — [] — [] — [] — [] — [] — [] — [] — []

Series 1= Maintained Action 2= Momentary Action	Keylock Option No. Corresponds to lock diagram	Lock Style S= Standard	Keying 1= No code stamp on lock (Std.)	Finish S= Standard Nickel Plating	Terminal 1= Standard 4= Wire leads (6" Black 22 AWG)	Mounting N= Nut C= Clip	Contact Material & Rating 1= Copper, Silver Plated (Standard) 2= Copper, Silver Plated (UL/CSA approved) 3= Gold Plated (Consult Factory)	Key Code Blank Code OC01 126 Code A126 45 Code T45 7021 Code 17021 06 Code OC06 * K2 Series Only
--------------------------------------------------------------	----------------------------------------------------------	----------------------------------	--------------------------------------------------	---------------------------------------------	----------------------------------------------------------------	--------------------------------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------	---------------------------------------------------------------------------------------------------------------------------

Consult factory for additional Key Codes.

KEYING: Two matching keys are provided with each switch lock. All K-Series switches come with 2 keys, keyed alike. Nickel plated with code number. All locks in a individual order will be keyed alike (Ex. OC01) unless otherwise specified at time of order. When it is necessary to reorder a specific key code (Ex. OC01), please include the key code when ordering.

Note: Keylock switches may be custom configured to customer requirements, including multiple key codes and wire harness assemblies.

CW Industries
A Unit of Electro Switch Corp.

TOLERANCES UNLESS OTHERWISE SPECIFIED

2 Place Decimal ± .010	METRIC
3 Place Decimal ± .005	1 Place Dec. ± .25mm
Angles ± 1°	2 Place Dec. ± .13mm

Title: **K SERIES SINGLE POLE AND DOUBLE POLE KEYLOCKS**

Division: **Switch**

Drawn by: DW 4/10/2023

Checked by: G. G. D. 8-22-23

Approval: [Signature] 8/22/23

Part No: **KEYLOCK SERIES**

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10

MASTER

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CW Industries:](#)

[K1-101S1S1N2 01](#)