


PIANO SWITCHES (FULL PITCH)

CFP



FEATURES

- RoHS compliant
- High-reliability
- Resin material is UL Recognized 94V-0


APPLICATIONS

- Communication devices, Air-conditioning equipment, Vending machines and various control equipment

INTERNAL STRUCTURE

	Part name	Material
①	Cover	Polyphenylenesulfide
②	Slider	Polyamide
③	Housing	Polyphenylenesulfide
④	Slider contact	Copper alloy, Gold-plated
⑤	Fixed contact	
⑥	Terminal pin	
⑦	Piano lever	Polyamide
⑧	Piano cover	Polyphenylenesulfide

PART NUMBER DESIGNATION



※ Please refer to the LIST OF PART NUMBERS when placing orders.

LIST OF PART NUMBERS

No. of bits	ON direction	Structure	Form of packaging	Shape of terminals		Packaging quantity
				B (Gull wing)	C (Through hole pins)	
2	Upper	Flat lever (without seal tape)	Taping	CFP-0201TB		500 pcs./reel
			Magazine	CFP-0201MB	CFP-0201MC	62 pcs./stick
	Lower	Convex lever (without seal tape)	Taping	CFP-0202TB		500 pcs./reel
			Magazine	CFP-0202MB	CFP-0202MC	62 pcs./stick
		Flat lever (without seal tape)	Taping	CFP-0211TB		500 pcs./reel
			Magazine	CFP-0211MB	CFP-0211MC	62 pcs./stick
3	Upper	Flat lever (without seal tape)	Taping	CFP-0301TB		500 pcs./reel
			Magazine	CFP-0301MB	CFP-0301MC	46 pcs./stick
	Lower	Convex lever (without seal tape)	Taping	CFP-0302TB		500 pcs./reel
			Magazine	CFP-0302MB	CFP-0302MC	46 pcs./stick
		Flat lever (without seal tape)	Taping	CFP-0311TB		500 pcs./reel
			Magazine	CFP-0311MB	CFP-0311MC	46 pcs./stick
4	Upper	Flat lever (without seal tape)	Taping	CFP-0401TB		500 pcs./reel
			Magazine	CFP-0401MB	CFP-0401MC	36 pcs./stick
	Lower	Convex lever (without seal tape)	Taping	CFP-0402TB		500 pcs./reel
			Magazine	CFP-0402MB	CFP-0402MC	36 pcs./stick
		Flat lever (without seal tape)	Taping	CFP-0411TB		500 pcs./reel
			Magazine	CFP-0411MB	CFP-0411MC	36 pcs./stick
5	Upper	Flat lever (without seal tape)	Taping	CFP-0501TB		500 pcs./reel
			Magazine	CFP-0501MB	CFP-0501MC	30 pcs./stick
	Lower	Convex lever (without seal tape)	Taping	CFP-0502TB		500 pcs./reel
			Magazine	CFP-0502MB	CFP-0502MC	30 pcs./stick
		Flat lever (without seal tape)	Taping	CFP-0511TB		500 pcs./reel
			Magazine	CFP-0511MB	CFP-0511MC	30 pcs./stick
6	Upper	Flat lever (without seal tape)	Taping	CFP-0601TB		500 pcs./reel
			Magazine	CFP-0601MB	CFP-0601MC	26 pcs./stick
	Lower	Convex lever (without seal tape)	Taping	CFP-0602TB		500 pcs./reel
			Magazine	CFP-0602MB	CFP-0602MC	26 pcs./stick
		Flat lever (without seal tape)	Taping	CFP-0611TB		500 pcs./reel
			Magazine	CFP-0611MB	CFP-0611MC	26 pcs./stick
8	Upper	Flat lever (without seal tape)	Taping	CFP-0801TB		500 pcs./reel
			Magazine	CFP-0801MB	CFP-0801MC	20 pcs./stick
	Lower	Convex lever (without seal tape)	Taping	CFP-0802TB		500 pcs./reel
			Magazine	CFP-0802MB	CFP-0802MC	20 pcs./stick
		Flat lever (without seal tape)	Taping	CFP-0811TB		500 pcs./reel
			Magazine	CFP-0811MB	CFP-0811MC	20 pcs./stick
10	Upper	Flat lever (without seal tape)	Taping	CFP-1001TB		500 pcs./reel
			Magazine	CFP-1001MB	CFP-1001MC	16 pcs./stick
	Lower	Convex lever (without seal tape)	Taping	CFP-1002TB		500 pcs./reel
			Magazine	CFP-1002MB	CFP-1002MC	16 pcs./stick
		Flat lever (without seal tape)	Taping	CFP-1011TB		500 pcs./reel
			Magazine	CFP-1011MB	CFP-1011MC	16 pcs./stick
		Convex lever (without seal tape)	Taping	CFP-1012TB		500 pcs./reel
			Magazine	CFP-1012MB	CFP-1012MC	16 pcs./stick

☐ : Not manufactured

※ Verify the above part numbers when placing orders.

Taping and magazine version can be supplied only in reel or stick units.

■ STANDARD SPECIFICATIONS

Operating temp. range	- 40 ~ 85 °C	
Storage temp. range		
Sealing	Non-washable	
Net weight	Approx. 0.55 g (CFP-02) Approx. 0.86 g (CFP-04) Approx. 1.19 g (CFP-06) Approx. 1.90 g (CFP-10)	Approx. 0.70 g (CFP-03) Approx. 1.03 g (CFP-05) Approx. 1.54 g (CFP-08)

■ ELECTRICAL CHARACTERISTICS

Contact rating Non-switching Switching Minimum	DC50 V 100 mA DC6 V, 100 mA DC24 V, 25 mA DC20 mV 1 µA
Contact resistance	50 mΩ maximum
Insulation resistance	1000 MΩ (DC100 V) minimum
Dielectric strength	AC500 V, 60 s

■ MECHANICAL CHARACTERISTICS


Operation angle	21 °
Operating force	7 N {0.71 kgf} maximum
Stop strength	10 N {1.02 kgf} 60 s
Solderability	245 ± 3 °C, 2 ~ 3 s
Soldering heat	Reflow : 255 °C (Peak temperature) Flow : 260 ± 3 °C, 5 ~ 6 s, two times maximum Please refer to the profile below)
	Manual soldering : 350 ± 10 °C, 3 ~ 4 s
Shear (Adhesion)	5 N {0.51 kgf} 10 s
Substrate bending	Width 90 mm, bend 3 mm, 5 s, 1 time
Pull-off strength	5 N {0.51 kgf} 10 s

■ ENVIRONMENTAL CHARACTERISTICS

Vibration	(Amplitude) 1.5 mm or (Acceleration) 98 m/s ² , 10-500 Hz, 3 directions for 10 cycles each
Shock	490 m/s ² , 11 ms, 6 directions for 3 times each
Load life	Continuous load 1000 cycles, DC6 ± 0.5 V, 100 ± 10 mA
Humidity	-10 ~ 65 °C, Relative humidity 0 ~ 96 %, 24 h for 10 cycles
High temp. exposure	85 °C, 96 h
Low temp. exposure	-40 °C, 96 h
Thermal shock	-40 (0.5 h) ~ 85 °C (0.5 h), 5 cycles

{ } : Reference only

〈Reflow profile for soldering heat evaluation〉




CFP


PIANO SWITCHES (FULL PITCH)

OUTLINE DIMENSIONS

Flat lever, Gull wing




Convex lever, Gull wing




Part number	Schematic	No. of bits	L dimension
CFP-02		2	7.5
CFP-03		3	10.05
CFP-04		4	12.6
CFP-05		5	15.15

Unless otherwise specified, tolerance : ± 0.3 (Unit : mm)

Flat lever, Through hole pin




Convex lever, Through hole pin



Part number	Schematic	No. of bits	L dimension
CFP-06		6	17.7
CFP-08		8	22.8
CFP-10		10	27.9


RECOMMENDED P.C.B. PAD DIMENSIONS

(Unit : mm)



SIZE OF P.C.B. PROCESSING

(Unit : mm)



CFP

PIANO SWITCHES (FULL PITCH)


PACKAGING SPECIFICATIONS

<Taping packaging specifications>


- Taping version is packaged in 500 pcs. per reel. Orders will be accepted for units of 500 pcs., i.e., 500, 1000, 1500 pcs., etc.
- Taping version is boxed with 1 reel.

Maximum number of consecutive missing pieces = 2
Leader length and reel dimension are shown in the diagrams below:

● Embossed tape dimensions



● 2 bits, 3 bits, 4 bits, 5 bits




● Reel dimensions


(Unit: mm)

(Conforms to JIS C 0806-3)

(In accordance with EIAJ ET-7200A)



● 6 bits, 8 bits, 10 bits



No. of bits	B	C	D
2, 3, 4, 5	24	11.5 ± 0.1	—
6	32	14.2 ± 0.1	28.4 ± 0.1
8, 10	44	20.2 ± 0.1	40.4 ± 0.1

<Magazine packaging specifications>

- Packing quantities of magazines are different depending on the bit number of the switches.
Please order the multiple numbers of the specific packing quantities. (e.g. 62 pcs., 124 pcs., 186 pcs., etc., in case of 2 bits version)

Pieces in package : 2 bits, 62 pcs./stick 3 bits, 46 pcs./stick
 4 bits, 36 pcs./stick 5 bits, 30 pcs./stick
 6 bits, 26 pcs./stick 8 bits, 20 pcs./stick
 10 bits, 16 pcs./stick

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Nidec:](#)

[CFP-0201TB](#) [CFP-0202TB](#) [CFP-0211TB](#) [CFP-0212TB](#) [CFP-0301TB](#) [CFP-0302TB](#) [CFP-0811TB](#) [CFP-0812TB](#)
[CFP-1001TB](#) [CFP-1002TB](#) [CFP-1011TB](#) [CFP-1012TB](#) [CFP-0601TB](#) [CFP-0602TB](#) [CFP-0611TB](#) [CFP-0612TB](#)
[CFP-0801TB](#) [CFP-0802TB](#) [CFP-0311TB](#) [CFP-0312TB](#) [CFP-0401TB](#) [CFP-0402TB](#) [CFP-0411TB](#) [CFP-0412TB](#)
[CFP-0201MB](#) [CFP-0201MC](#) [CFP-0202MB](#) [CFP-0202MC](#) [CFP-0211MB](#) [CFP-0211MC](#) [CFP-1002MB](#) [CFP-1002MC](#)
[CFP-1011MB](#) [CFP-1011MC](#) [CFP-1012MB](#) [CFP-1012MC](#) [CFP-0811MB](#) [CFP-0811MC](#) [CFP-0812MB](#) [CFP-](#)
[0812MC](#) [CFP-1001MB](#) [CFP-1001MC](#) [CFP-0612MB](#) [CFP-0612MC](#) [CFP-0801MB](#) [CFP-0801MC](#) [CFP-0802MB](#)
[CFP-0802MC](#) [CFP-0601MB](#) [CFP-0601MC](#) [CFP-0602MB](#) [CFP-0602MC](#) [CFP-0611MB](#) [CFP-0611MC](#) [CFP-0402MB](#)
[CFP-0402MC](#) [CFP-0411MB](#) [CFP-0411MC](#) [CFP-0412MB](#) [CFP-0412MC](#) [CFP-0311MB](#) [CFP-0311MC](#) [CFP-](#)
[0312MB](#) [CFP-0312MC](#) [CFP-0401MB](#) [CFP-0401MC](#) [CFP-0212MB](#) [CFP-0212MC](#) [CFP-0301MB](#) [CFP-0301MC](#)
[CFP-0302MB](#) [CFP-0302MC](#)