



18 TURNS CERMET TRIMMERS

CT-9



FEATURES

- RoHS compliant
- General use type
- Fine setting is possible with 18 turns configuration

INTERNAL STRUCTURE		
		
Part name	Material	Flammability
① Housing	Polybutyleneterephthalate	UL94V-0
② Base element	Ceramic	—
③ Wiper	Multi metal alloy	
④ Resistive element	RuO ₂ cermet	
⑤ Electrode	Ag-Pd cermet	
⑥ Adhesive	Epoxy	UL94V-0
⑦ Terminal pin	Copper, Tin-plated	—
⑧ Rotor gear	Polyamide	UL94HB
⑨ Rubber cushion	Silicone rubber	—
!0 Shaft	Brass, Nickel-plated	

PART NUMBER DESIGNATION

CT - 9EW 1MΩ (105)

Series name

Terminal pin
E : Sn (Lead-free)

Product shape
W : Top adjustment X : Side adjustment
P : Side adjustment

Resistance code

Resistance value

※ Please refer to the LIST OF PART NUMBERS when placing orders.

LIST OF PART NUMBERS

Adjustment position	Shape of terminal (Top view)	Form of packaging	Pieces in package
		Plastic pack	
Top adjustment 		CT-9EW	50 pcs./pack
Side adjustment (↑ Adjustment direction)		CT-9EX	
		CT-9EP	

ELECTRICAL CHARACTERISTICS

Nominal resistance range	10 Ω ~ 2 M Ω
Resistance tolerance	± 10 %
Power ratings	0.5 W (70 °C) 0 W (120 °C)
Resistance law	(B) Linear law
Maximum input voltage	DC300 V or power rating, whichever is smaller
Maximum wiper current	100 mA or power rating, whichever is smaller
Effective electrical turn	15 turns
End resistance	1 % or 2 Ω , whichever is greater
C.R.V.	1 % or 3 Ω , whichever is greater
Operating temp. range	— 55 ~ 120 °C
Temp. coefficient	10 Ω , 20 Ω : ± 250 10 ⁻⁶ /°C maximum 50 Ω ~ 2 M Ω : ± 100 10 ⁻⁶ /°C maximum
Insulation resistance	1000 M Ω minimum (DC500 V)
Dielectric strength	AC900 V, 60 s
Net weight	Approx. 0.94 g (CT-9EP) Approx. 0.95 g (CT-9EX, EW)

<Nominal resistance values>

➡ 10 Ω	➡ 20 Ω	50 Ω	100 Ω	200 Ω	500 Ω	1 k Ω	2 k Ω	5 k Ω
10 k Ω	20 k Ω	50 k Ω	100 k Ω	200 k Ω	500 k Ω	1 M Ω	2 M Ω	

Fig.1

※ The above part numbers are all available with the respective combination of <Nominal resistance values> (Fig. 1).

※ Verify the above part numbers when placing orders.

The products indicated by ➡ mark are manufactured upon receipt of order basis.

MECHANICAL CHARACTERISTICS

Mechanical turn	18 turns
Operating torque	35 mN·m {357 gf·cm} maximum
Mechanical stop	Clutch action
Rotational life	200 cycles [Δ R/R ≤ ± (2 Ω + 3 %)]
Terminal strength	10 N {1.02 kgf} minimum (Tensile strength)
Thrust to shaft	10 N {1.02 kgf} minimum
Solderability	245 ± 3 °C, 2 ~ 3 s

{ } : Reference only

ENVIRONMENTAL CHARACTERISTICS

Test item	Test conditions	Specifications
Thermal shock	— 65 ~ 125 °C (0.5 h), 5 cycles	[Δ R/R ≤ 1 %] [S.S. ≤ 1 %]
Humidity	— 10 ~ 65 °C (80 ~ 98 %), 10 cycles, 240 h	[Δ R/R ≤ 2 %]
Shock	981 m/s ² , 6 ms 6 directions for 3 times each	[Δ R/R ≤ 1 %] [S.S. ≤ 1 %]
Vibration	(Amplitude) 1.52 mm or (Acceleration) 196 m/s ² , 10 ~ 2000 Hz, 3 directions, 12 times each	
Load life	70 °C, 0.5 W, 1000 h	[Δ R/R ≤ 3 %] [S.S. ≤ 1 %]
Low temp. operation	— 55 °C, 2 h	[Δ R/R ≤ 2 %] [S.S. ≤ 2 %]
High temp. exposure	120 °C, 250 h	[Δ R/R ≤ 3 %] [S.S. ≤ 2 %]
Immersion seal	85 °C, 60 s	No leaks (No continuous bubbles)
Soldering heat	Flow 260 ± 3 °C, 5 ~ 6 s, two times maximum Manual soldering 380 ± 10 °C, 3 ~ 4 s	[Δ R/R ≤ 1 %]

Δ R/R : Change in total resistance
S.S. : Setting stability

CT-9

CERMET TRIMMERS

MAXIMUM INPUT RATINGS


Nominal resistance values (Ω)	Resistance code	Maximum input voltage (V)	Maximum wiper current (mA)
\rightarrow 10 \rightarrow 20 50 100 200 500	100 200 500 101 201 501	1.00 2.00 5.00 7.07 10.0 15.8	100 100 100 70.7 50.0 31.6
1 k 2 k 5 k 10 k 20 k 50 k	102 202 502 103 203 503	22.4 31.6 50.0 70.7 100 158	22.4 15.8 10.0 7.07 5.00 3.16
100 k 200 k 500 k 1 M 2 M	104 204 504 105 205	224 300 300 300 300	2.24 1.50 0.60 0.30 0.15

The products indicated by \rightarrow mark are manufactured upon receipt of order basis.


OUTLINE DIMENSIONS

Unless otherwise specified, tolerance: ± 0.3 (Unit: mm)

CT-9EW Top adjustment




CT-9EX Side adjustment



OUTLINE DIMENSIONS

CT-9EP Side adjustment



PACKAGING SPECIFICATIONS

<Bulk pack specifications>

- Unit of bulk in a plastic bag is 50 pcs. per pack.
- Boxing of bulk in a plastic bag is performed with 100 pcs. per box.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Nidec:

[CT-9EW104](#) [CT-9EW503](#) [CT-9EW502](#) [CT-9EW103](#) [CT-9EX502](#) [CT-9EX503](#) [CT-9EX504](#) [CT-9EX202](#) [CT-9EX203](#) [CT-9EX204](#) [CT-9EX205](#) [CT-9EX500](#) [CT-9EX501](#) [CT-9EX102](#) [CT-9EX103](#) [CT-9EX104](#) [CT-9EX105](#) [CT-9EX200](#) [CT-9EX201](#) [CT-9EW205](#) [CT-9EW500](#) [CT-9EW501](#) [CT-9EW504](#) [CT-9EX100](#) [CT-9EX101](#) [CT-9EW105](#) [CT-9EW200](#) [CT-9EW201](#) [CT-9EW202](#) [CT-9EW203](#) [CT-9EW204](#) [CT-9EP502](#) [CT-9EP503](#) [CT-9EP504](#) [CT-9EW100](#) [CT-9EW101](#) [CT-9EW102](#) [CT-9EP202](#) [CT-9EP203](#) [CT-9EP204](#) [CT-9EP205](#) [CT-9EP500](#) [CT-9EP501](#) [CT-9EP102](#) [CT-9EP103](#) [CT-9EP104](#) [CT-9EP105](#) [CT-9EP200](#) [CT-9EP201](#) [CT-9EP100](#) [CT-9EP101](#)