

## 16-Port 10/100/1000 Mbps 1U Rack-Mount/Desktop Gigabit Ethernet Unmanaged Switch, Metal Housing

MODEL NUMBER: NG16



Energy-efficient unmanaged switch sets up in seconds with no configuration required. Provides a Gigabit network connection for multiple devices. Ideal for home or small offices, workgroups and creative production environments.

### Description

The NG16 16-Port 10/100/1000 Mbps 1U Rack-Mount/Desktop Gigabit Ethernet Unmanaged Switch adds 10/100/1000 Mbps Ethernet capacity to your home office, small office, workgroup or creative production environment. Share large bandwidth-intensive files, such as CAD drawings and videos, at Gigabit speeds, improving efficiency and cutting costly downtime.

This rack-mount/desktop switch features 16 twisted-pair RJ45 Gigabit Ethernet ports that support auto-negotiable 10/100/1000 Mbps and auto MDI/MDIX cross-over detection functions for convenient plug-and-play capability. No configuration is required, so you can have your Gigabit network up and running immediately. Easy-to-read LEDs indicate connection and activity status for each port. IEEE 802.3x flow control allows smooth transmission of large files.

The NG16 supports IEEE 802.3az Energy Efficient Ethernet standards by putting unused ports into a low-power state without interrupting network connections. It consumes very little input power—just seven watts max. The detachable five-foot input cord with NEMA 5-15P plug connects to a protected UPS, generator or mains input AC source. The heavy-duty metal housing is designed for desktop installation or mounting into 1U of an EIA-standard 19-inch rack with the included brackets.

### Features

**Unmanaged Network Switch for Home/Small Offices or Workgroups** 16 twisted-pair RJ45 Gigabit Ethernet ports  
Auto-negotiable 10/100/1000 Mbps  
Automatic MDI/MDIX cross-over detection  
32 Gbps switching capacity (2 Gbps per port with full duplex)  
Easy-to-read LEDs indicate connection and activity status for each port  
Supports 9k jumbo frames  
Supports MAC address auto-learning and auto-aging  
Supports 802.3x flow control (full duplex) and back pressure (half duplex)

**Compliant with IEEE 802.3az Energy Efficient Ethernet Standards** Automatically shifts unused ports to low-power state without interrupting network connection  
Consumes very little input power—just 7W max  
Also meets IEEE 802.3ab, 802.3i, 802.3u and 802.3 standards

**Heavy-Duty Metal Housing** Fanless design for silent operation  
Detachable 5 ft. AC power cord with NEMA 5-15P plug  
Plug-and-play—no configuration necessary

**Versatile Installation Options** Includes rubber feet for secure placement on flat desktop surface  
Mounts in 1U of EIA-standard 19 in. rack with included brackets  
Grounding lug included

### Highlights

- 16 auto-negotiable 10/100/1000 Mbps RJ45 ports
- Supports auto MDI/MDIX cross-over function
- Consumes very little input power—just 7W max
- 2 Gbps switching capacity per port with full duplex
- Plug-and-play with no configuration required

### Package Includes

- NG16 16-Port 10/100/1000 Mbps 1U Rack-Mount/Desktop Gigabit Ethernet Unmanaged Switch
- Detachable AC power cord with NEMA 5-15P plug, 5 ft.
- (2) Mounting brackets
- (8) Screws
- (4) Rubber feet
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

#### Works with the Most Popular Web Browsers

The NG16 is browser-based and works independently from the connected computer's operating system. Because switch compatibility is based on common hardware standards, rather than system software dependencies, the NG16 accommodates most platforms. Preferred web browsers include Google Chrome (on both Windows and macOS) and Microsoft Edge (Windows only).

## Specifications

OVERVIEW	
UPC Code	037332194725
Product Type	Unmanaged Switch
INPUT	
Electrical Consumption (Max)	7W
Nominal Input Voltage Description	Accepts 100-240V AC nominal input
Voltage Compatibility (VAC)	100-240
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	5
Input Cord Length (m)	1.52
POWER	
Power Consumption (Watts)	7
CONNECTIONS	
Number of Ports	16
Ports	16
Ports Detail	16x 10/100/1000BASE-T
SFP Uplink Ports	0
PoE Supported Ports	0
Network Switch Ports	(16) 10/100/1000 (RJ45)
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Power LED (Green for Power On); One LED per RJ45 port (Green indicates 10/100Mbps link; Amber indicates 1000Mbps link; LEDs flash to indicate port activity)
PHYSICAL	
Primary Form Factor	Desktop; Rackmount
Color	Black
Form Factors Supported	Desktop, Rackmount
Shipping Dimensions (hwd / in.)	2.59 x 10.15 x 13.38



Powering Business Worldwide

TRIPP LITE  
SERIES

Shipping Dimensions (hwd / cm)	6.60 x 25.80 x 34.00
Shipping Weight (lbs.)	4.91
Shipping Weight (kg)	2.23
Unit Dimensions (hwd / in.)	4.960 x 11.023 x 1.730
Unit Dimensions (hwd / cm)	12.5 x 27.9 x 4.39
Unit Weight (lbs.)	3.2
Unit Weight (kg)	1.45
Rack Units	1
<b>ENVIRONMENTAL</b>	
Storage Temperature Range	-40° to 158°F (-40° to 70°C)
Relative Humidity	10 to 90% (non-condensing)
Operating Temperature	32 to 104 F (0 to 40 C)
<b>COMMUNICATIONS</b>	
Network Compatibility	1 Gbps (Gigabit)
Network Compatibility Details	Auto-negotiable
Switching Capacity	32 Gbps
Switching Capacity Details	2 Gbps per port with full duplex
<b>FEATURES &amp; SPECIFICATIONS</b>	
Jumbo Frames	10000
Console Port	No
MAC Auto Learning	Yes
RMON	No
SNMP	No
Storm Control	No
DHCP Snooping	No
Auto MDI/MDIX Crossover Detection	Yes
Fans (Type/Quantity)	Fanless
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	IEEE 802.3 Auto-Negotiation; IEEE 802.3ab 1000Base-T; IEEE 802.3az (Energy Efficient Ethernet); IEEE 802.3i 10Base-T; IEEE 802.3u 100Base-TX/FX; IEEE 802.3x Flow Control
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[NG16](#)