

PRESSURE TRANSDUCERS WITH AMP.


PA-850



FEATURES

- High corrosion resistance and drip-proof construction
Pressure port attachment made of SUS 316L
Proven IP-65 grade gauge body (IP-65 in accordance with IEC)
- Standard product provides both a switch output (hysteresis adjustable) and an analog output
- Absolute pressure type and compound pressure type which can control negative to positive pressure with only a single pressure gauge are all in line
- Three standard types of joint are provided
R2 : R 1/4 (M 5 female screw)
GF : G 3/8 with flash diaphragm
G2 : G 1/4 (M 5 female screw)

INTERNAL STRUCTURE PA-850 (R 1/4)



Part name		Material
①	Fitting	SUS 316L
②	Housing	SUS 316L
③	Plastic cover	ABS (Acrylonitrile butadiene styrene) + PC (Polycarbonate)
④	Stainless steel diaphragm	SUS 316L

MODEL NUMBER DESIGNATION

		PA-850 - 102 R - N R2			
Series name				Fitting	
Pressure reference		Rated pressure range		R2 : R 1/4 with M 5 female screw	
G : Gauge		102 : 0 ~ 100 kPa		GF : G 3/8 with flash diaphragm	
		352 : 0 ~ 350 kPa		G2 : G 1/4 with M 5 female screw	
		103 : 0 ~ 1000 kPa			
V : Gauge (Vacuum)		102 : 0 ~ - 100 kPa		Switch output interface	
R : Compound		102 : - 100 ~ 100 kPa		N : NPN open collector(Upper limit mode)	
		302 : - 100 ~ 300 kPa		P : PNP open collector(Upper limit mode)	
A : Absolute		102 : 0 ~ 100 kPa abs			

※ Please refer to the LIST OF MODEL NUMBERS when placing orders.

PA-850

PRESSURE TRANSDUCERS WITH AMP.

LIST OF MODEL NUMBERS

Fitting	Pressure reference		Gauge						Absolute
	SW output interface	kPa Rated pressure range	0 ~ 100	0 ~ 350	0 ~ 1000	0 ~ - 100	- 100 ~ 100	- 100 ~ 300	0 ~100
R2 (R 1/4)	NPN		PA-850-102G-NR2	PA-850-352G-NR2	PA-850-103G-NR2	PA-850-102V-NR2	PA-850-102R-NR2	PA-850-302R-NR2	PA-850-102A-NR2
	PNP		PA-850-102G-PR2	PA-850-352G-PR2	PA-850-103G-PR2	PA-850-102V-PR2	PA-850-102R-PR2	PA-850-302R-PR2	PA-850-102A-PR2
GF (G 3/8)	NPN		PA-850-102G-NGF	PA-850-352G-NGF	PA-850-103G-NGF	PA-850-102V-NGF	PA-850-102R-NGF	PA-850-302R-NGF	PA-850-102A-NGF
	PNP		PA-850-102G-PGF	PA-850-352G-PGF	PA-850-103G-PGF	PA-850-102V-PGF	PA-850-102R-PGF	PA-850-302R-PGF	PA-850-102A-PGF
G2 (G 1/4)	NPN		PA-850-102G-NG2	PA-850-352G-NG2	PA-850-103G-NG2	PA-850-102V-NG2	PA-850-102R-NG2	PA-850-302R-NG2	PA-850-102A-NG2
	PNP		PA-850-102G-PG2	PA-850-352G-PG2	PA-850-103G-PG2	PA-850-102V-PG2	PA-850-102R-PG2	PA-850-302R-PG2	PA-850-102A-PG2

※ Verify the above model numbers when placing orders.

STANDARD SPECIFICATIONS

● Unless otherwise specified, the specs are defined at an ambient temperature of 25±5 °C and excitation voltage of 12 V DC.

Item		Model number	PA-850						
			102G	352G	103G	102V	102R	302R	102A
General specifications	Pressure reference		Gauge						Absolute
	Rated pressure range kPa		100	350	1000	－ 100	－ 100 ~ 100	－ 100 ~ 300	100 (abs)
	Maximum pressure kPa		200	700	2000	200	200	600	200 (abs)
	Break-down pressure kPa		300	1050	3000	300	300	900	300 (abs)
	Operating temp. range °C		－ 20 ~ 80						
	Compensated temp. range °C		0 ~ 50						
	Operating humidity %RH		35 ~ 85 (No condensation)						
	Storage temp. °C		－ 20 ~ 80 (Atmospheric pressure, humidity 65 %RH maximum)						
	Pressure medium		Corrosive gases/liquids compatible with SUS 316L						
	Insulation resistance MΩ minimum		100 (500 V DC)						
	Dielectric strength		800 V AC, 60 s (Leakage current 1 mA maximum)						
	Sealed liquid		Silicone oil						
	Pressure port		R 1/4、G 3/8 (Flash diaphragm)、G 1/4 ※ 1						
	Net weight g		R2 : Approx. 165, GF : Approx. 180, G2 : Approx. 170						
	Protection grade		IP65						

※ 1 An "O" ring provided. (G 3/8 : P18、G 1/4 : P15)

PA-850

PRESSURE TRANSDUCERS WITH AMP.

Item		Model number	PA-850						
			102G	352G	103G	102V	102R	302R	102A
Power	Supply voltage	V DC	10.8 ~ 30 (Including ripple voltage)						
	Consumption current	maximum	20 mA						
Analog output	Output voltage	V	1 ~ 5						
	Zero voltage	V	1 ± 0.04			3 ± 0.1	2 ± 0.1	1 ± 0.04	
	Span voltage	V	4 ± 0.04			4 ± 0.1		4 ± 0.04	
	Output current	mA maximum	1 (Load resistance 5 kΩ minimum)						
	Linearity/Hysteresis		%F.S.					± 0.5	
	Thermal error	ZERO %F.S./°C		± 0.06					
		SPAN %F.S./°C		± 0.06					
	Supply voltage effect		V maximum	± 0.02					
	Response		ms	Approx. 2					
	Gravitational effect (From horizontal position to vertical position)		%F.S.	± 0.3	± 0.1	± 0.05	± 0.3		± 0.1
Switch output	No. of outputs		1						
	Output interface		NPN or PNP open collector output						
	Setting method		Adjustable by VR						
	Adjustable range		0 ~ 100 % of rated pressure range						0 ~ 108 % of rated pressure range
	Display		Red LED						
	Accuracy	0 ~ 50 °C (Reference temp.: 25 °C)	%F.S.		± 3				
	Hysteresis		Approx. 1 ~ 15 % of set value						
	Hysteresis setting method		Adjustable by VR						
	Switching capacity		30 V DC 100 mA						
	Residual voltage		NPN : 0.8 V, PNP : 1.2 V						

ENVIRONMENTAL CHARACTERISTICS

Test item	Test conditions (At 25 ± 5 °C)	Permissible change
Vibration	10 ~ 500 Hz, 1.5 mm maximum/98.1 m/s ² , 3 directions for 2 hours each	Switch output setting and analog output (Zero voltage, Span voltage) : ± 1 %F.S. maximum each
Shock	490 m/s ² 3 directions for 3 times each	
Pressure cycling	10 ⁶ cycles 0 ~ Rated pressure/Rated pressure range	
Moisture resistance	40 °C, 90 ~ 95 %RH, 240 hrs.	


PA-850

PRESSURE TRANSDUCERS WITH AMP.

OUTLINE DIMENSIONS


Unless otherwise specified, tolerance : ± 0.5 (Unit: mm)

Configurations of joint R2 (R1/4) type




Wire color	Connection
Brown	Power $\oplus$
White	Analog output
Black	Switch output
Blue	Common
Shield	Fitting

Configurations of joint GF (G 3/8) type



⚠ Extra care should be taken with the diaphragm part. Do not touch the diaphragm directly to avoid damaging the diaphragm.

Configurations of joint G2 (G 1/4) type




PA-850


PRESSURE TRANSDUCERS WITH AMP.

INTERNAL ELECTRICAL SCHEMATICS

● NPN output




● PNP output




SWITCH OUTPUT SCHEMATICS

Turns on at the set pressure and turns off at the set pressure minus the hysteresis.


● PA-850- * * * G




● PA-850-102V



● PA-850- * * * R



● PA-850- * * * A



※ Adjustable hysteresis

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Nidec:

[PA-850-102A-NGF](#) [PA-850-102A-PGF](#) [PA-850-102R-NG2](#) [PA-850-102R-NGF](#) [PA-850-102R-NR2](#) [PA-850-102R-PG2](#) [PA-850-302R-PGF](#) [PA-850-302R-PR2](#) [PA-850-102V-PGF](#) [PA-850-102V-PR2](#) [PA-850-302R-NG2](#) [PA-850-302R-NGF](#) [PA-850-302R-NR2](#) [PA-850-302R-PG2](#) [PA-850-102R-PGF](#) [PA-850-102R-PR2](#) [PA-850-102V-NG2](#) [PA-850-102V-NGF](#) [PA-850-102V-NR2](#) [PA-850-102V-PG2](#) [PA-850-102A-NR2](#) [PA-850-102A-NG2](#) [PA-850-102A-PG2](#) [PA-850-102A-PR2](#) [PA-850-102G-NG2](#) [PA-850-102G-NGF](#) [PA-850-102G-NR2](#) [PA-850-102G-PG2](#) [PA-850-102G-PGF](#) [PA-850-102G-PR2](#) [PA-850-103G-PG2](#) [PA-850-103G-PGF](#) [PA-850-103G-PR2](#) [PA-850-352G-NG2](#) [PA-850-352G-NGF](#) [PA-850-352G-NR2](#) [PA-850-352G-PG2](#) [PA-850-352G-PGF](#) [PA-850-352G-PR2](#) [PA-850-103G-NR2](#) [PA-850-103G-NGF](#) [PA-850-103G-NG2](#)