

USB 3.0 SuperSpeed Active Extension Repeater Cable (A M/F), 5M (16.4 ft.)

MODEL NUMBER: U330-05M



Description

This USB 3.0 active extension cable is a bus-powered extension cable that can be used to increase the length of a device cable without the worry of signal loss and potential performance problems. Increase the extension distance to 32.8 feet (10 meters) by connecting two U330-05M together. USB limits a cable's length to 16 feet (4.9 meters). Any length above 16 feet requires the use of an active cable such as this one. This cable has a signal booster built in. The cable must be plugged directly into a USB port (either on the PC or a hub). Use a standard six-foot (1.8-meter), 10-foot (3.1-meter) or 15-foot (4.6-meter) USB A/B cable to reach the desired distance. The U330-05M provides up to 770mA of power to the connected device. If your device requires more than 770mA of power, an external power supply will be required for the connected USB device.

Features

- Extend a USB 3.0 signal 16.4-ft. (5 m)
- Increase the extension distance to 32.8-ft. (10 m) by connecting two U330-05M together
- Works together with standard USB 3.0 cables
- Provides up to 770mA of power to the connected device. If your device requires more than 770mA of power, an external power supply will be required for the connected USB device.
- Backward compatible to previous USB generations

Specifications

OVERVIEW	
UPC Code	037332173492
INPUT	
Bus Powered	Yes
POWER	

Highlights

- Extend a USB 3.0 signal 16.4-ft. (5 m.)
- Increase the extension distance to 32.8-ft. (10 m.) by connecting two U330-05M together
- Supports USB 3.0 SuperSpeed data transfer rates up to 5Gbps

System Requirements

- A USB 3.0 Computer port and USB 3.0 device are required to meet USB 3.0 speeds. A USB 2.0 port or device can be used, but you will be limited to the speeds of that port / device.
- The U330-05M provides up to 770mA of power to the connected device. If your device requires more than 770mA of power, an external power supply will be required for the connected USB device.

Package Includes

- 16.4-ft. (5 m) USB3.0 Super Speed A/A Active Extension Cable (USB-A M/F)



Powering Business Worldwide

TRIPP-LITE
by **EATON**

Power Consumption (Watts)	0.25
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB 3.0 A (FEMALE)
Connector Plating	Nickel
PHYSICAL	
Color	Black
Material of Construction	ABS, PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Length (ft.)	16.4
Cable Length (m)	5.00
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.10
Shipping Weight (lbs.)	0.60
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.55
Unit Weight (kg)	0.25
ENVIRONMENTAL	
Operating Temperature Range	32° to 158°F (0° to 70°C)
Storage Temperature Range	14° to 176°F (-10° to 80°C)
Relative Humidity	10% to 90 % RH, Non-Condensing
BTUs	0.85 BTU/Hr
Power Provided to Connected Device(s)	Up to 0.77A
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
UASP Support	Yes
Driver Required	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U330-05M](#)