

SZV SERIES
105°C Low Impedance, Lead Free Reflow Soldering.
◆FEATURES

- Load Life : 105°C 1000 hours.
- Lead free reflow soldering is available.
- Available for high density mounting.
- Low impedance at 100kHz with selected materials.
- RoHS compliance.



◆SPECIFICATIONS

Items	Characteristics																							
Category Temperature Range	-55~ +105°C																							
Rated Voltage Range	6.3~ 35V.DC																							
Capacitance Tolerance	±20% (20°C, 120Hz)																							
Leakage Current(MAX)	I=0.01CV or 3 μA whichever is greater. (After 2 minutes application of rated voltage) I=Leakage Current(μA) C=Rated Capacitance(μF) V=Rated Voltage(V)																							
(tanδ) Dissipation Factor(MAX)	<table><tr><td>Rated Voltage (V)</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td></tr><tr><td>tan δ</td><td>0.26</td><td>0.19</td><td>0.16</td><td>0.14</td><td>0.12</td></tr></table> (20°C, 120Hz)						Rated Voltage (V)	6.3	10	16	25	35	tan δ	0.26	0.19	0.16	0.14	0.12						
Rated Voltage (V)	6.3	10	16	25	35																			
tan δ	0.26	0.19	0.16	0.14	0.12																			
Endurance	After applying rated voltage with rated ripple current for 1000 hrs at 105°C, the capacitors shall meet the following requirements. <table><tr><td>Capacitance Change</td><td colspan="5">Within ±25% of the initial value.</td></tr><tr><td>Dissipation Factor</td><td colspan="5">Not more than 200% of the specified value.</td></tr><tr><td>Leakage Current</td><td colspan="5">Not more than the specified value.</td></tr></table>						Capacitance Change	Within ±25% of the initial value.					Dissipation Factor	Not more than 200% of the specified value.					Leakage Current	Not more than the specified value.				
Capacitance Change	Within ±25% of the initial value.																							
Dissipation Factor	Not more than 200% of the specified value.																							
Leakage Current	Not more than the specified value.																							
Low Temperature Stability Impedance Ratio(MAX)	<table><tr><td>Rated Voltage(V)</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td></tr><tr><td>Z (-25°C)/Z (20°C)</td><td>2</td><td>2</td><td>2</td><td>2</td><td>2</td></tr><tr><td>Z (-55°C)/Z (20°C)</td><td>5</td><td>4</td><td>4</td><td>3</td><td>3</td></tr></table> (120Hz)						Rated Voltage(V)	6.3	10	16	25	35	Z (-25°C)/Z (20°C)	2	2	2	2	2	Z (-55°C)/Z (20°C)	5	4	4	3	3
Rated Voltage(V)	6.3	10	16	25	35																			
Z (-25°C)/Z (20°C)	2	2	2	2	2																			
Z (-55°C)/Z (20°C)	5	4	4	3	3																			

◆MULTIPLIER FOR RIPPLE CURRENT

Frequency coefficient

Frequency (Hz)	120	1k	10k	100k ≤
1 μF	0.30	0.60	0.80	1.00
2.2~4.7 μF	0.42	0.60	0.80	1.00
10~33 μF	0.55	0.75	0.90	1.00
47~100 μF	0.70	0.85	0.95	1.00

◆MARKING



Rated Voltage (V)	6.3	10	16	25	35
Rated Voltage code	j	A	C	E	V

◆PART NUMBER

□□□	SZV	□□□□□	□	□□□	□□	D×L
Rated Voltage	Series	Rated Capacitance	Capacitance Tolerance	Option	Lead Forming	Case Size

◆ DIMENSIONS

(mm)



φ D	L	A ₁	B ₁	C	W ₁	P
4	5.5	4.3	4.3	1.8	0.5~0.8	1.0
5	5.5	5.3	5.3	2.2	0.5~0.8	1.3
6.3	5.5	6.6	6.6	2.7	0.5~0.8	1.8

◆ STANDARD SIZE

Size φ D(mm), Ripple Current (mA r.m.s./105°C, 100kHz), Impedance(Ω MAX/20°C, 100kHz)

WV (V.DC) Cap(μF)	6.3 (0J)			10 (1A)			16 (1C)		
	Size	Ripple	Z	Size	Ripple	Z	Size	Ripple	Z
10							4×5.5	60	3.0
22	4×5.5	60	3.0				5×5.5	95	1.8
33				5×5.5	95	1.8	6.3×5.5	140	1.0
47	5×5.5	95	1.8				6.3×5.5	140	1.0
100	6.3×5.5	140	1.0						

WV (V.DC) Cap(μF)	25 (1E)			35 (1V)		
	Size	Ripple	Z	Size	Ripple	Z
1				4×5.5	60	3.9
2.2				4×5.5	60	3.7
3.3				4×5.5	60	3.6
4.7	4×5.5	60	3.6	4×5.5	60	3.6
10				5×5.5	95	2.0
22				6.3×5.5	140	1.0
33	6.3×5.5	140	1.0			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rubycon:](#)

[10SZV33M5X5.5](#) [16SZV33M6.3X5.5](#) [16SZV22M5X5.5](#) [16SZV47M6.3X5.5](#) [35SZV10M5X5.5](#) [35SZV1M4X5.5](#)
[6.3SZV100M6.3X5.5](#) [6.3SZV22M4X5.5](#) [35SZV3R3M4X5.5](#) [6.3SZV47M5X5.5](#) [16SZV10M4X5.5](#) [25SZV33M6.3X5.5](#)
[35SZV22M6.3X5.5](#)