

## USB-C Multiport Adapter - HDMI, USB 3.x (5Gbps) Hub Port, Gigabit Ethernet, 60W PD Charging, HDCP, Black

MODEL NUMBER: U444-06N-HGUB-C



Adds HDMI, USB-A, USB-C PD charging and Gigabit Ethernet ports to your tablet, laptop, notebook, smartphone or PC.

### Features

#### Mini Docking Station Turns Your Device's USB-C or Thunderbolt 3 Port into a Multiport Workstation

This USB-C to HDMI cable expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for transmitting digital audio and 1080p video to a large display, adding a thumb drive or other USB peripheral, powering and charging a PD Charging-compliant mobile device, and connecting to a Gigabit Ethernet network—all at the same time.

#### Supports USB DisplayPort Alternate Mode for Transmitting Audio/Video DisplayPort and USB Signals

With a source device that also supports USB DisplayPort Alt Mode, you can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary.

#### Transmits Crystal-Clear 1080p Video and Digital Audio to an HDMI Display

To send digital audio and HD video to an HDMI television, projector or monitor, connect the HDMI port to the display using an HDMI cable (sold separately). The HDMI port supports HD video resolutions up to 1920 x 1080 (1080p) at 60 Hz.

#### Connects a USB Peripheral

The USB-A port accepts USB peripherals, such as a flash drive, mouse, keyboard or printer. It supports fast USB 3.2 Gen 1 data transfer rates up to 5 Gbps and is backward compatible with USB 2.0 and USB 1.1 devices. The port provides up to 5V/1.5A (7.5W) of fast-charging power to mobile devices. **Note:** Host must support USB OTG (On-the-Go).

#### Charges a Connected Device

The USB-C Power Delivery (PD) port provides power and charging to the PD Charging-compliant device (such as a MacBook, Chromebook or Android smartphone) the U444-06N-HGUB-C is connected to. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 20V 3A (60W). **Note:** USB-C PD port does not support Quick Charge (QC).

#### Accesses a Wired Gigabit Ethernet Network

The RJ45 port offers access to a Gigabit Ethernet network when no Wi-Fi is available or when a wired connection offers faster speeds. Connect using a UTP cable (sold separately), and enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers.

#### Built-In USB-C Cable Connects in Either Direction

Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

#### Ready to Use Right Out of the Package

The plug-and-play USB 3.2 to HDMI adapter requires no software, drivers or external power. The compact

### Highlights

- Transmits DisplayPort signals from sources supporting USB DisplayPort Alt Mode
- Delivers HD picture quality at resolutions up to 1920 x 1080 (1080p) @60 Hz
- USB-A port provides up to 5V 1.5A (7.5W) of fast-charging power
- Connects you to a wired Ethernet network when no Wi-Fi is available
- USB-C PD 3.0 port supports 20V 3A (60W) power output for charging host device

### Applications

- Play video from your laptop or PC on an HDMI display, such as an HDTV or projector
- Access a wired Ethernet network in a location with no or spotty Wi-Fi
- Transfer data from a USB flash drive or connect your computer to a USB printer or other USB device
- Charge your connected notebook or laptop by connecting its wall charger to the USB-C PD Charging port

### System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with HDMI input (HDMI port)

### Package Includes

- U444-06N-HGUB-C USB-C Multiport Adapter, Black
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

unit fits easily into a pocket, briefcase or laptop bag for connecting on the go.

## Specifications

| OVERVIEW                       |   |
|--------------------------------|---|
| UPC Code                       | 037332209160  |
| Product Type                   | Multiport Adapter   |
| Technology                     | Cat5/5e; Cat6; HDMI; USB 3.x  |
| Host Connector                 | USB C (MALE)  |
| VIDEO                          |   |
| Video Input                    | USB C (MALE)  |
| Video Output                   | HDMI (FEMALE)   |
| Number of Monitors Supported   | 1   |
| Video Ports                    | HDMI (FEMALE)   |
| Video Ports Details            | HDMI 1.3; HDCP 1.3  |
| Resolutions Supported          | HDMI: 1080P 60Hz (1920 x 1080)  |
| Supported Resolutions          | 1280x720 (720p); 1920x1080 (1080p)  |
| Max Supported Video Resolution | HDMI: 1920 X 1080 (1080P) @ 60HZ  |
| Extended Mode                  | Yes   |
| Extended Mode Details          | Extend the desktop from your host computer to an HDMI monitor at video resolutions up to 1920 x 1080 (1080p) @ 60 Hz      |
| Mirror Mode                    | Yes   |
| Mirror Mode Details            | Mirror the video output from your host computer to an HDMI monitor at video resolutions up to 1920 x 1080 (1080p) @ 60 Hz |
| Max Supported Color Depth      | 30-bit Deep Color   |
| HDR Support                    | No  |
| 3D Video Supported             | No  |
| EDID Support                   | No  |
| DisplayPort Alt Mode           | Yes   |
| DATA                           |   |
| Data Ports                     | USB A (FEMALE)  |
| Data Ports Details             | USB-A - USB 3.2 Gen 1 (5 Gbps)  |
| NETWORK                        |   |
| Network Ports                  | RJ45 (FEMALE)   |
| INPUT                          |   |



Powering Business Worldwide

TRIPP LITE  
SERIES

|  |  |
|--|--|
| Built-In Cable Length (ft.)                    | 0.36   |
| Built-In Cable Length (m)                      | 0.11   |
| Built-In Cable Length (in.)                    | 4.33   |
| Built-In Cable Length (cm)                     | 1.1  |
| Bus Powered                                    | Yes  |
| Product Length (in.)                           | 6  |
| Product Length (cm.)                           | 15.24  |
| Product Length (ft.)                           | 0.5  |
| Product Length (m)                             | 0.15   |
| <b>BATTERY</b>                                 |  |
| Battery Charging (5V/1.5A Port)                | Yes  |
| <b>POWER</b>                                   |  |
| Power Consumption (Watts)                      | 2.60   |
| USB Power Delivery (PD) Charging Support       | Yes  |
| USB Power Delivery (PD) Charging Specification | 2.0  |
| <b>CONNECTIONS</b>                             |  |
| Number of Ports                                | 4  |
| Ports  | 1  |
| Ports Detail                                   | Supports 10/100/1000 Mbps (Gigabit) Ethernet connection            |
| Side A - Connector 1                           | USB C (MALE)   |
| Side B - Connector 1                           | HDMI (FEMALE)  |
| Side B - Connector 2                           | USB A (FEMALE)   |
| Side B - Connector 3                           | USB C (FEMALE)   |
| Side B - Connector 4                           | RJ45 (FEMALE)  |
| Connector Plating                              | Nickel   |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b>   |  |
| LED Indicators                                 | RJ45 Port = Green(Power), Orange (Data)                            |
| <b>CHARGING</b>                                |  |
| Number of Charging Ports                       | 2  |
| Total Charging Watts                           | 60   |
| Charging Port Type                             | USB A (FEMALE); USB C (FEMALE)                                     |
| Charging Ports                                 | USB-C: 60W (20V 3A) Power Delivery (PD 2.0); USB-A: 5V 1.5A (7.5W) |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                       |  |
|---------------------------------------|--|
| Charging Ports Details                | USB-A port supports fast charging up to 5V/1.5A (7.5W)USB-C port supports PD charging up to 20V/3A (60W) |
| Charging Ports / Amps                 | 1.5A; 3A   |
| <b>PHYSICAL</b>                       |  |
| Color                                 | Black  |
| Material of Construction              | PVC, ABS   |
| Cable Jacket Color                    | Black  |
| Cable Jacket Material                 | PVC  |
| Cable Jacket Rating                   | VW-1   |
| Cable Outer Diameter (OD)             | 3.9mm  |
| Wire Gauge (AWG)                      | 28+34  |
| Shipping Dimensions (hwd / in.)       | 0.91 x 5.51 x 3.94   |
| Shipping Weight (lbs.)                | 0.11   |
| Unit Dimensions (hwd / in.)           | 0.000 x 0.000 x 0.000  |
| Unit Packaging Type                   | Box  |
| Unit Weight (lbs.)                    | 0.09   |
| Unit Weight (kg)                      | 0.04   |
| <b>ENVIRONMENTAL</b>                  |  |
| Operating Temperature Range           | 32° to 113°F (0° to 45°C)  |
| Storage Temperature Range             | 14° to 158°F (-10° to 70°C)  |
| BTUs                                  | 9 BTU/Hr   |
| Operating Humidity Range              | 10% to 85% RH, Non-Condensing  |
| Storage Humidity Range                | 5% to 90% RH, Non-Condensing   |
| Power Provided to Connected Device(s) | USB-A: 5V/1.5A (7.5W); USB-C: PD Charging 20V/3A (60W)   |
| <b>COMMUNICATIONS</b>                 |  |
| Network Compatibility                 | 10 Mbps; 100 Mbps (Fast Ethernet); 1 Gbps (Gigabit)  |
| IEEE Standards Supported              | 802.3; 802.3u; 802.3az; 802.3x   |
| <b>FEATURES &amp; SPECIFICATIONS</b>  |  |
| USB Hub Ports                         | Yes  |
| Number of USB Hub Ports               | 1  |
| USB Specification                     | USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)                       |
| Multi-Resolution Support              | No   |
| Ethernet Support                      | Yes  |
| UASP Support                          | No   |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                     |                                     |
|-------------------------------------|-------------------------------------|
| Auto MDIX Support                   | No                                  |
| Full Duplex Support                 | No                                  |
| Suspend Mode Support                | Yes                                 |
| Remote Wakeup Support               | Yes                                 |
| HDCP Specification                  | 1.3                                 |
| Driver Required                     | No                                  |
| Recommended Category Cable          | Cat5/Cat5e/Cat6 Cables              |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                                     |
| TAA Compliant Option                | N                                   |
| Product Compliance                  | RoHS; CE (Europe); REACH; FCC (USA) |
| <b>WARRANTY &amp; SUPPORT</b>       |                                     |
| Product Warranty Period (Worldwide) | 3-year limited warranty             |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U444-06N-HGUB-C](#)