

NOTE

1. RATING : DC 12V 50mA
2. CONTACT RESISTANCE : 100mΩ MAX
3. GENERAL TOLERANCE : +/- 0.3 mm
4. MANUFACTURING SPECIFICATION
WOULD BE ACCORDANCE WITH WT0158
5. PART NO.(P/N.):

TS604VM1 - * * * R - R



6.2 x 6.2 mm
VERTICAL

DIMENSION "H"
025=2.5mm
031=3.1mm
035=3.5mm



OPERATING FORCE
A=100gf
B=160gf
C=260gf

STEM
□=BLACK
N=BROWN
R=RED

PACKING
R=REEL



P. C. B LAND DIMENSION



CIRCUIT DIAGRAM

TS604VM1-035 * R-R	3.5 mm
TS604VM1-031 * R-R	3.1 mm
TS604VM1-025 * R-R	2.5 mm
MODEL NO.	"H"

德利威電子股份有限公司
DAILYWELL ELECTRONICS CO.,LTD.

SCALE (比例) : 1 : 1

TITLE 圖名	Tactile Switch 6.2X6.2 SMD			SIZE 圖紙	A4
DWG NO. 圖號	TS604VM1-035CR-R			UNIT 單位	mm
REV. 版本	A	DATE 日期	OCT - 14 - 2016	SHEET 張數	1 of 1
CHECKED BY 審核				DRAWN BY 製圖	IRENE

FILE NAME : CA0285

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dailywell:

[TS604VM1-025BR-R](#)