

Cornell Dubilier

Engineering

Cornell Dubilier Marketing, Inc
Liberty, South Carolina
TEL: 864-843-2277 FAX:864-843-3800

Catalog Number: DCM403U050DC2B

Customer Part Number: _____

Date: 8/24/2011

Capacitance: 40000 μ F

Tolerance: - 10% + 75%

Working Volts: 50 VDC

Surge Volts: 65VDC

Leakage Current @ 25°C: 6000 μ A

ESR @ 120 Hz @ 25°C: 0.018 Ω max.

Ripple Current @ 120 Hz, 85°C: 13.5A

Diameter (D): 3.00 \pm 0.031 inches

Length (L): 4.125 \pm 0.062 inches


Total Length, W/Insulation (TL): 4.376 \pm 0.062 inches

Terminal Spacing (S): 1.25 \pm 0.015 inches

Terminal Thread (T): 10-32 UNF

Insulation: PVC

Operating Temperature: - 40°C ~ +85°C



ROHS Compliant for all date codes after "0513",
Per provisions of CD document 10-28.

"Controlled Copy" if viewed on CD Server or if copy is stamped
in Red, Otherwise considered as an "Uncontrolled Copy"

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cornell Dubilier:](#)

[DCM403U050DC2B](#)