

ProGrAnalog Corp.

08/18/2023

Ver 3.2

Xilinx Power Test Adaptor (PTA) - to test power delivery network to Zynq UltraScale+ ZU19-C1760 series FPGA's


Features

- Set of 3 Xilinx Power Test Adaptors (PTA) for PDN testing AMD Xilinx Zynq UltraScale+ ZU19-C1760 series FPGAs
- 5 Samtec connectors to slam: VCCINT, MGTAVCC, VCCAUX, VCCINT_IO, MGTAVTT.
- 6 SMP connectors for testing: MGTAVTT, VCCINT, MGTAVCC, VCCAUX, VCCINT_IO, GND.
- PTA with BGA footprint reflows onto ZU19-C1760 PCB pads.
- Remote Vsense on Samtec connectors and SMP mini connectors.
- Most rails can be tested with an LSP200 controller.
- GUI supports transient, pulse train, impedance and 3D plots.

Typical Test Setup

- Xilinx PTA reflowed onto the test board.
- LSP1000RS connected into VCCINT connector.

Pack of 3 Zynq ZU19-C1760 series PTA's



LoadSlammer GUI

Workspace
Test - 1


Available Tests

Name:
Rail:

Test - 1

None

Transient Test

Transient load step with adjustable rise times, current, and pulse width.

Pulse Train

Repeating load steps with a configurable frequency and duty cycle.

Impedance (Z)

Large signal output impedance with adjustable current amplitude and offset.


DC Load

DC Load with timer.


Delay


Timed delay.

Transient test



Mechanical Specs






Packing Tray Specs

56.57mm x149.80mm x14.6mm



A1 - top left corner




Schematics




MGTAVTT





VCCAUX






VCCINT_IO




MGTAVCC









Availability

Xilinx part number	ProGrAnalog part number
ZU19-C1760	PA-KIT-ZU19-C1760

<https://loadslammer.com>

Questions:

support@progranalog.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ProGrAnalog Corp:](#)

[PA-Kit-ZU19-C1760](#)