

Mica Capacitors **Miniature Dipped**


Types CD5, CD6, CD7, CDS5, CDS10, D7, CDS15, CDS19, CDS30



Small cases for tight places is what you get with CDE miniature dipped silver mical capacitors. Like the standard dipped mica capacitor, the miniature dipped product offers the same stability and rugged performance in low and moderate-humidity applications.

Highlights

- ◆ Reel packaging available
- ◆ Dimensions meet EIA RS153B specification
- ◆ 20,000 V/ μ s dV/dt pulse capability minimum
- ◆ Non-flammable units that meet IEC 695-2-2 are available



Part Numbers with the F at the end are RoHS-5 Compliant

Has more than 1000 ppm lead in some homogenous material but otherwise complies with the EU Directive 2002/95/EC requirement restricting the use of Lead (Pb), Mercury (Hg), Cadmium (Cd), Hexavalent chromium (Cr(VI)), PolyBrominated Biphenyls (PBB) and PolyBrominated Diphenyl Ethers (PBDE).

Specifications

Capacitance Range: 1 pF to 40,000 pF

Voltage Range: 50 Vdc to 500 Vdc

Capacitance Tolerance: $\pm 1/2$ pF (D), ± 1 pF (C), $\pm 1/2\%$ (E), $\pm 1\%$ (F), $\pm 2\%$ (G), $\pm 5\%$ (J)

Temperature Range: -55°C to $+125^{\circ}\text{C}$

Dielectric Strength Test: 200% of rated voltage

Ratings

Cap	Volts	Catalog	L	H	T	S	d
(pF)	(Vdc)	Part Number	inches (mm)	inches (mm)	inches (mm)	inches (mm)	inches (mm)
1	300	CD5CC010D03F	0.270 (6.9)	0.190 (4.8)	0.110 (2.8)	0.120 (3.0)	0.016 (4)
1	300	CDS5CC010D03F	0.250 (6.4)	0.160 (4.1)	0.090 (2.3)	0.120 (3.0)	0.016 (4)
1	500	CD6CD010D03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
1	500	CDS10CD010D03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
1	500	CDS15CD010D03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
2	300	CD5CC020D03F	0.270 (6.9)	0.190 (4.8)	0.110 (2.8)	0.120 (3.0)	0.016 (4)
2	300	CDS5CC020D03F	0.250 (6.4)	0.160 (4.1)	0.090 (2.3)	0.120 (3.0)	0.016 (4)
2	500	CD6CD020D03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
2	500	CDS10CD020D03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
2	500	CDS15CD020D03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
3	300	CD5CC030D03F	0.270 (6.9)	0.190 (4.8)	0.110 (2.8)	0.120 (3.0)	0.016 (4)
3	300	CDS5CC030D03F	0.250 (6.4)	0.160 (4.1)	0.090 (2.3)	0.120 (3.0)	0.016 (4)
3	500	CD6CD030D03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
3	500	CDS10CD030D03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
3	500	CDS15CD030D03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
4	300	CD5CC040D03F	0.270 (6.9)	0.190 (4.8)	0.110 (2.8)	0.120 (3.0)	0.016 (4)
4	300	CDS5CC040D03F	0.250 (6.4)	0.160 (4.1)	0.090 (2.3)	0.120 (3.0)	0.016 (4)
4	500	CD6CD040D03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
4	500	CDS10CD040D03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
4	500	CDS15CD040D03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
5	300	CD5CC050D03F	0.270 (6.9)	0.190 (4.8)	0.110 (2.8)	0.120 (3.0)	0.016 (4)
5	300	CDS5CC050D03F	0.250 (6.4)	0.160 (4.1)	0.090 (2.3)	0.120 (3.0)	0.016 (4)
5	500	CD6CD050D03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
5	500	CDS10CD050D03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
5	500	CDS15CD050D03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
6	300	CD5CC060D03F	0.270 (6.9)	0.190 (4.8)	0.110 (2.8)	0.120 (3.0)	0.016 (4)
6	300	CDS5CC060D03F	0.250 (6.4)	0.160 (4.1)	0.090 (2.3)	0.120 (3.0)	0.016 (4)
6	500	CD6CD060D03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
6	500	CDS10CD060D03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
6	500	CDS15CD060D03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
7	300	CD5CC070D03F	0.270 (6.9)	0.190 (4.8)	0.110 (2.8)	0.120 (3.0)	0.016 (4)

Cap	Volts	Catalog	L	H	T	S	d
(pF)	(Vdc)	Part Number	inches (mm)	inches (mm)	inches (mm)	inches (mm)	inches (mm)
7	300	CDS5CC070D03F	0.250 (6.4)	0.160 (4.1)	0.090 (2.3)	0.120 (3.0)	0.016 (4)
7	500	CD6CD070D03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
7	500	CDS10CD070D03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
7	500	CDS15CD070D03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
8	300	CD5CC080D03F	0.270 (6.9)	0.190 (4.8)	0.110 (2.8)	0.120 (3.0)	0.016 (4)
8	300	CDS5CC080D03F	0.250 (6.4)	0.160 (4.1)	0.090 (2.3)	0.120 (3.0)	0.016 (4)
8	500	CD6CD080D03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
8	500	CDS10CD080D03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
8	500	CDS15CD080D03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
9	300	CD5CC090D03F	0.270 (6.9)	0.190 (4.8)	0.110 (2.8)	0.120 (3.0)	0.016 (4)
9	300	CDS5CC090D03F	0.250 (6.4)	0.160 (4.1)	0.090 (2.3)	0.120 (3.0)	0.016 (4)
9	500	CD6CD090D03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
9	500	CDS10CD090D03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
9	500	CDS15CD090D03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
10	300	CD5CC100J03F	0.270 (6.9)	0.190 (4.8)	0.110 (2.8)	0.120 (3.0)	0.016 (4)
10	300	CDS5CC100J03F	0.250 (6.4)	0.160 (4.1)	0.090 (2.3)	0.120 (3.0)	0.016 (4)
10	500	CD6CD100D03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
10	500	CDS10CD100J03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
10	500	CDS15CD100J03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
11	300	CD5CC110J03F	0.270 (6.9)	0.190 (4.8)	0.110 (2.8)	0.120 (3.0)	0.016 (4)
11	300	CDS5CC110J03F	0.250 (6.4)	0.160 (4.1)	0.090 (2.3)	0.120 (3.0)	0.016 (4)
11	500	CD6CD110D03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
11	500	CDS10CD110J03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
11	500	CDS15CD110J03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
12	300	CD5CC120J03F	0.270 (6.9)	0.190 (4.8)	0.110 (2.8)	0.120 (3.0)	0.016 (4)
12	300	CDS5CC120J03	0.250 (6.4)	0.160 (4.1)	0.090 (2.3)	0.120 (3.0)	0.016 (4)
12	500	CD6CD120J03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
12	500	CDS10CD120J03	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
12	500	CDS15CD120J03	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
15	300	CD5CC150J03F	0.270 (6.9)	0.190 (4.8)	0.120 (3.0)	0.120 (3.0)	0.016 (4)
15	300	CDS5CC150J03F	0.250 (6.4)	0.170 (4.3)	0.100 (2.5)	0.120 (3.0)	0.016 (4)

Mica Capacitors Miniature Dipped

Cap	Volts	Catalog	L	H	T	S	d
(pF)	(Vdc)	Part Number	inches (mm)	inches (mm)	inches (mm)	inches (mm)	inches (mm)
15	500	CD6CD150UJ03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
15	500	CDS10CD150UJ03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
15	500	CDS15CD150UJ03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
18	300	CD5CC180UJ03F	0.270 (6.9)	0.200 (5.1)	0.120 (3.0)	0.120 (3.0)	0.016 (4)
18	300	CDS5CC180UJ03F	0.250 (6.4)	0.170 (4.3)	0.100 (2.5)	0.120 (3.0)	0.016 (4)
18	500	CD6CD180UJ03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
18	500	CDS10CD180UJ03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
18	500	CDS15CD180UJ03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
20	300	CD5EC200UJ03F	0.270 (6.9)	0.200 (5.1)	0.120 (3.0)	0.120 (3.0)	0.016 (4)
20	300	CDS5EC200UJ03F	0.250 (6.4)	0.170 (4.3)	0.100 (2.5)	0.120 (3.0)	0.016 (4)
20	500	CD6ED200UJ03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
20	500	CDS10ED200UJ03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
20	500	CDS15ED200UJ03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
22	300	CD5EC220UJ03F	0.270 (6.9)	0.200 (5.1)	0.120 (3.0)	0.120 (3.0)	0.016 (4)
22	300	CDS5EC220UJ03F	0.250 (6.4)	0.170 (4.3)	0.100 (2.5)	0.120 (3.0)	0.016 (4)
22	500	CD6ED220UJ03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
22	500	CDS10ED220UJ03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
22	500	CDS15ED220UJ03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
24	300	CD5EC240UJ03F	0.270 (6.9)	0.200 (5.1)	0.120 (3.0)	0.120 (3.0)	0.016 (4)
24	300	CDS5EC240UJ03F	0.250 (6.4)	0.170 (4.3)	0.100 (2.5)	0.120 (3.0)	0.016 (4)
24	500	CD6ED240UJ03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
24	500	CDS10ED240UJ03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
24	500	CDS15ED240UJ03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
27	300	CD5EC270UJ03F	0.270 (6.9)	0.200 (5.1)	0.130 (3.3)	0.120 (3.0)	0.016 (4)
27	300	CDS5EC270UJ03F	0.250 (6.4)	0.170 (4.3)	0.110 (2.8)	0.120 (3.0)	0.016 (4)
27	500	CD6ED270UJ03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
27	500	CDS10ED270UJ03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
27	500	CDS15ED270UJ03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
30	300	CD5EC300UJ03F	0.270 (6.9)	0.200 (5.1)	0.130 (3.3)	0.120 (3.0)	0.016 (4)
30	300	CDS5EC300UJ03F	0.250 (6.4)	0.170 (4.3)	0.110 (2.8)	0.120 (3.0)	0.016 (4)
30	500	CD6ED300UJ03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
30	500	CDS10ED300UJ03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
30	500	CDS15ED300UJ03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
33	300	CD5EC330UJ03F	0.270 (6.9)	0.200 (5.1)	0.130 (3.3)	0.120 (3.0)	0.016 (4)
33	300	CDS5EC330UJ03F	0.250 (6.4)	0.170 (4.3)	0.110 (2.8)	0.120 (3.0)	0.016 (4)
33	500	CD6ED330UJ03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
33	500	CDS10ED330UJ03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
33	500	CDS15ED330UJ03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
36	300	CD5EC360UJ03F	0.270 (6.9)	0.210 (5.3)	0.130 (3.3)	0.120 (3.0)	0.016 (4)
36	300	CDS5EC360UJ03F	0.250 (6.4)	0.170 (4.3)	0.110 (2.8)	0.120 (3.0)	0.016 (4)
36	500	CD6ED360UJ03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
36	500	CDS10ED360UJ03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
36	500	CDS15ED360UJ03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
39	300	CD5EC390UJ03F	0.270 (6.9)	0.210 (5.3)	0.130 (3.3)	0.120 (3.0)	0.016 (4)
39	300	CDS5EC390UJ03F	0.250 (6.4)	0.170 (4.3)	0.110 (2.8)	0.120 (3.0)	0.016 (4)
39	500	CD6ED390UJ03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
39	500	CDS10ED390UJ03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
39	500	CDS15ED390UJ03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
43	300	CD5EC430UJ03F	0.270 (6.9)	0.210 (5.3)	0.140 (3.6)	0.120 (3.0)	0.016 (4)
43	300	CDS5EC430UJ03F	0.250 (6.4)	0.170 (4.3)	0.120 (3.0)	0.120 (3.0)	0.016 (4)
43	500	CD6ED430UJ03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
43	500	CDS10ED430UJ03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
43	500	CDS15ED430UJ03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
47	300	CD5EC470UJ03F	0.270 (6.9)	0.210 (5.3)	0.140 (3.6)	0.120 (3.0)	0.016 (4)
47	300	CDS5EC470UJ03F	0.250 (6.4)	0.170 (4.3)	0.120 (3.0)	0.120 (3.0)	0.016 (4)
47	500	CD6ED470UJ03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
47	500	CDS10ED470UJ03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
47	500	CDS15ED470UJ03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
50	500	CD6ED500UJ03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
50	500	CDS10ED500UJ03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
50	500	CDS15ED500UJ03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
51	300	CD5EC510UJ03F	0.270 (6.9)	0.210 (5.3)	0.140 (3.6)	0.120 (3.0)	0.016 (4)
51	300	CDS5EC510UJ03F	0.250 (6.4)	0.170 (4.3)	0.120 (3.0)	0.120 (3.0)	0.016 (4)
51	500	CD6ED510UJ03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
51	500	CDS10ED510UJ03F	0.310 (7.9)	0.260 (6.6)	0.120 (3.0)	0.141 (3.6)	0.016 (4)
51	500	CDS15ED510UJ03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
56	300	CD5EC560UJ03F	0.270 (6.9)	0.220 (5.6)	0.150 (3.8)	0.120 (3.0)	0.016 (4)
56	300	CDS5EC560UJ03F	0.250 (6.4)	0.180 (4.6)	0.130 (3.3)	0.120 (3.0)	0.016 (4)
56	500	CD6ED560UJ03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
56	500	CDS10ED560UJ03F	0.310 (7.9)	0.260 (6.6)	0.130 (3.3)	0.141 (3.6)	0.016 (4)
56	500	CDS15ED560UJ03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
62	300	CD5EC620UJ03F	0.270 (6.9)	0.220 (5.6)	0.150 (3.8)	0.120 (3.0)	0.016 (4)
62	300	CDS5EC620UJ03F	0.250 (6.4)	0.180 (4.6)	0.130 (3.3)	0.120 (3.0)	0.016 (4)
62	500	CD6ED620UJ03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
62	500	CDS10ED620UJ03F	0.310 (7.9)	0.260 (6.6)	0.130 (3.3)	0.141 (3.6)	0.016 (4)
62	500	CDS15ED620UJ03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)

Cap	Volts	Catalog	L	H	T	S	d
(pF)	(Vdc)	Part Number	inches (mm)	inches (mm)	inches (mm)	inches (mm)	inches (mm)
68	300	CD5EC680UJ03F	0.270 (6.9)	0.220 (5.6)	0.150 (3.8)	0.120 (3.0)	0.016 (4)
68	300	CDS5EC680UJ03F	0.250 (6.4)	0.180 (4.6)	0.130 (3.3)	0.120 (3.0)	0.016 (4)
68	500	CD6ED680UJ03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
68	500	CDS10ED680UJ03F	0.310 (7.9)	0.260 (6.6)	0.130 (3.3)	0.141 (3.6)	0.016 (4)
68	500	CDS15ED680UJ03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
75	300	CD5EC750UJ03F	0.270 (6.9)	0.230 (5.8)	0.160 (4.1)	0.120 (3.0)	0.016 (4)
75	300	CDS5EC750UJ03F	0.250 (6.4)	0.190 (4.8)	0.140 (3.6)	0.120 (3.0)	0.016 (4)
75	500	CD6ED750UJ03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
75	500	CDS10ED750UJ03F	0.310 (7.9)	0.260 (6.6)	0.130 (3.3)	0.141 (3.6)	0.016 (4)
75	500	CDS15ED750UJ03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
82	300	CD5EC820UJ03F	0.270 (6.9)	0.230 (5.8)	0.160 (4.1)	0.120 (3.0)	0.016 (4)
82	300	CD6EC820UJ03	0.250 (6.4)	0.190 (4.8)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
82	300	CDS5EC820UJ03F	0.275 (7.0)	0.175 (4.4)	0.140 (3.6)	0.120 (3.0)	0.016 (4)
82	500	CDS10ED820UJ03F	0.310 (7.9)	0.260 (6.6)	0.130 (3.3)	0.141 (3.6)	0.016 (4)
82	500	CDS15ED820UJ03F	0.430 (10.9)	0.280 (7.1)	0.140 (3.6)	0.234 (5.9)	0.025 (6)
91	300	CD5FC910UJ03F	0.270 (6.9)	0.230 (5.8)	0.170 (4.3)	0.120 (3.0)	0.016 (4)
91	300	CD6FC910UJ03	0.275 (7.0)	0.190 (4.8)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
91	300	CDS5FC910UJ03F	0.250 (6.4)	0.175 (4.4)	0.150 (3.8)	0.120 (3.0)	0.016 (4)
91	500	CDS10FD910UJ03F	0.310 (7.9)	0.260 (6.6)	0.130 (3.3)	0.141 (3.6)	0.016 (4)
91	500	CDS15FD910UJ03F	0.430 (10.9)	0.280 (7.1)	0.150 (3.8)	0.234 (5.9)	0.025 (6)
100	300	CD5FC101UJ03F	0.270 (6.9)	0.240 (6.1)	0.180 (4.6)	0.120 (3.0)	0.016 (4)
100	300	CD6FC101UJ03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
100	300	CDS5FC101UJ03F	0.250 (6.4)	0.200 (5.1)	0.160 (4.1)	0.120 (3.0)	0.016 (4)
100	500	CDS10FD101UJ03F	0.320 (8.1)	0.260 (6.6)	0.130 (3.3)	0.141 (3.6)	0.016 (4)
100	500	CDS15FD101UJ03F	0.430 (10.9)	0.280 (7.1)	0.150 (3.8)	0.234 (5.9)	0.025 (6)
110	300	CD5FC111UJ03F	0.270 (6.9)	0.240 (6.1)	0.180 (4.6)	0.120 (3.0)	0.016 (4)
110	300	CD6FC111UJ03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
110	300	CDS5FC111UJ03F	0.250 (6.4)	0.240 (6.1)	0.180 (4.6)	0.120 (3.0)	0.016 (4)
110	500	CDS10FD111UJ03F	0.320 (8.1)	0.260 (6.6)	0.130 (3.3)	0.141 (3.6)	0.016 (4)
110	500	CDS15FD111UJ03F	0.440 (11.2)	0.290 (7.4)	0.150 (3.8)	0.234 (5.9)	0.025 (6)
120	300	CD5FC121UJ03F	0.270 (6.9)	0.250 (6.4)	0.190 (4.8)	0.120 (3.0)	0.016 (4)
120	300	CD6FC121UJ03	0.275 (7.0)	0.175 (4.4)	0.095 (2.4)	0.172 (4.4)	0.016 (4)
120	300	CDS5FC121UJ03F	0.250 (6.4)	0.250 (6.4)	0.190 (4.8)	0.120 (3.0)	0.016 (4)
120	500	CDS10FD121UJ03F	0.320 (8.1)	0.260 (6.6)	0.140 (3.6)	0.141 (3.6)	0.016 (4)
120	500	CDS15FD121UJ03F	0.440 (11.2)	0.290 (7.4)	0.150 (3.8)	0.234 (5.9)	0.025 (6)
130	100	CD5FA131UJ03F	0.270 (6.9)	0.230 (5.8)	0.160 (4.1)	0.120 (3.0)	0.016 (4)
130	100	CDS5FA131UJ03F	0.250 (6.4)	0.190 (4.8)	0.140 (3.6)	0.120 (3.0)	0.016 (4)
130	500	CD7FD131UJ03	0.265 (6.7)	0.260 (6.6)	0.110 (2.8)	0.172 (4.4)	0.016 (4)
130	500	CDS10FD131UJ03F	0.320 (8.1)	0.260 (6.6)	0.140 (3.6)	0.141 (3.6)	0.016 (4)
130	500	CDS15FD131UJ03F	0.440 (11.2)	0.290 (7.4)	0.150 (3.8)	0.234 (5.9)	0.025 (6)
150	100	CD5FA151UJ03F	0.270 (6.9)	0.230 (5.8)	0.170 (4.3)	0.120 (3.0)	0.016 (4)
150	100	CDS5					

Mica Capacitors **Miniature Dipped**

Cap		Volts	Catalog	L	H	T	S	d	Cap		Volts	Catalog	L	H	T	S	d
(pF)	(Vdc)	Part Number	inches (mm)	inches (mm)	inches (mm)	inches (mm)	inches (mm)	inches (mm)	(pF)	(Vdc)	Part Number	inches (mm)	inches (mm)	inches (mm)	inches (mm)	inches (mm)	inches (mm)
270	300	CD7FC271J03	0.265 (6.7)	0.260 (6.6)	0.110 (2.8)	0.172 (4.4)	0.016 (.4)		1000	100	CD7FA102J03	0.320 (8.1)	0.300 (7.6)	0.155 (3.9)	0.172 (4.4)	0.016 (.4)	
270	300	CDS10FC271J03F	0.340 (8.6)	0.270 (6.9)	0.160 (4.1)	0.141 (3.6)	0.016 (.4)		1000	100	D71F102J03F	0.340 (8.6)	0.310 (7.9)	0.170 (4.3)	0.141 (3.6)	0.016 (.4)	
270	500	D75F271J03F	0.340 (8.6)	0.270 (6.9)	0.160 (4.1)	0.141 (3.6)	0.016 (.4)		1000	100	CDS15FA102J03F	0.450 (11.4)	0.310 (7.9)	0.170 (4.3)	0.234 (5.9)	0.025 (.6)	
270	500	CDS15FD271J03F	0.440 (11.2)	0.290 (7.4)	0.160 (4.1)	0.234 (5.9)	0.025 (.6)		1000	500	CDS19FD102J03F	0.620 (15.7)	0.460 (11.7)	0.160 (4.1)	0.344 (8.7)	0.032 (.8)	
270	500	CDS19FD271J03F	0.610 (15.5)	0.450 (11.4)	0.130 (3.3)	0.344 (8.7)	0.032 (.8)		1100	100	CD7FA112J03	0.320 (8.1)	0.300 (7.6)	0.155 (3.9)	0.172 (4.4)	0.016 (.4)	
300	50	CD5FY301J03F	0.270 (6.9)	0.230 (5.8)	0.170 (4.3)	0.120 (3.0)	0.016 (.4)		1100	100	D71F112J03F	0.340 (8.6)	0.310 (7.9)	0.170 (4.3)	0.141 (3.6)	0.016 (.4)	
300	50	CDS5FY301J03F	0.250 (6.4)	0.190 (4.8)	0.150 (3.8)	0.120 (3.0)	0.016 (.4)		1100	100	CDS15FA112J03F	0.460 (11.7)	0.310 (7.9)	0.180 (4.6)	0.234 (5.9)	0.025 (.6)	
300	300	CD7FC301J03	0.265 (6.7)	0.260 (6.6)	0.110 (2.8)	0.172 (4.4)	0.016 (.4)		1100	500	CDS19FD112J03F	0.620 (15.7)	0.460 (11.7)	0.160 (4.1)	0.344 (8.7)	0.032 (.8)	
300	300	CDS10FC301J03F	0.340 (8.6)	0.270 (6.9)	0.160 (4.1)	0.141 (3.6)	0.016 (.4)		1200	100	CD7FA122J03	0.320 (8.1)	0.300 (7.6)	0.155 (3.9)	0.172 (4.4)	0.016 (.4)	
300	500	D75F301J03F	0.340 (8.6)	0.270 (6.9)	0.160 (4.1)	0.141 (3.6)	0.016 (.4)		1200	100	D71F122J03F	0.340 (8.6)	0.310 (7.9)	0.170 (4.3)	0.141 (3.6)	0.016 (.4)	
300	500	CDS15FD301J03F	0.440 (11.2)	0.290 (7.4)	0.160 (4.1)	0.234 (5.9)	0.025 (.6)		1200	100	CDS19FA122J03F	0.460 (11.7)	0.310 (7.9)	0.180 (4.6)	0.234 (5.9)	0.025 (.6)	
300	500	CDS19FD301J03F	0.610 (15.5)	0.450 (11.4)	0.130 (3.3)	0.344 (8.7)	0.032 (.8)		1200	500	CDS19FD122J03F	0.620 (15.7)	0.460 (11.7)	0.170 (4.3)	0.344 (8.7)	0.032 (.8)	
330	50	CD5FY331J03F	0.270 (6.9)	0.240 (6.1)	0.180 (4.6)	0.120 (3.0)	0.016 (.4)		1300	100	CD7FA132J03	0.330 (8.4)	0.310 (7.9)	0.175 (4.4)	0.172 (4.4)	0.016 (.4)	
330	50	CDS5FY331J03F	0.250 (6.4)	0.190 (4.8)	0.160 (4.1)	0.120 (3.0)	0.016 (.4)		1300	100	D71F132J03F	0.340 (8.6)	0.310 (7.9)	0.170 (4.3)	0.141 (3.6)	0.016 (.4)	
330	100	CD7FA331J03	0.275 (7.0)	0.260 (6.6)	0.125 (3.2)	0.172 (4.4)	0.016 (.4)		1300	500	CDS19FD132J03F	0.620 (15.7)	0.460 (11.7)	0.170 (4.3)	0.344 (8.7)	0.032 (.8)	
330	100	CDS10FA331J03F	0.340 (8.6)	0.270 (6.9)	0.160 (4.1)	0.141 (3.6)	0.016 (.4)		1500	100	CD7FA152J03	0.330 (8.4)	0.310 (7.9)	0.175 (4.4)	0.172 (4.4)	0.016 (.4)	
330	500	D75F331J03F	0.340 (8.6)	0.270 (6.9)	0.160 (4.1)	0.141 (3.6)	0.016 (.4)		1500	100	D71F152J03F	0.340 (8.6)	0.310 (7.9)	0.170 (4.3)	0.141 (3.6)	0.016 (.4)	
330	500	CDS15FD331J03F	0.440 (11.2)	0.290 (7.4)	0.160 (4.1)	0.234 (5.9)	0.025 (.6)		1500	100	CDS15FA152J03F	0.460 (11.7)	0.310 (7.9)	0.180 (4.6)	0.234 (5.9)	0.025 (.6)	
330	500	CDS19FD331J03F	0.610 (15.5)	0.450 (11.4)	0.130 (3.3)	0.344 (8.7)	0.032 (.8)		1500	500	CDS19FD152J03F	0.620 (15.7)	0.460 (11.7)	0.170 (4.3)	0.344 (8.7)	0.032 (.8)	
360	50	CD5FY361J03F	0.270 (6.9)	0.240 (6.1)	0.190 (4.8)	0.120 (3.0)	0.016 (.4)		1600	500	CDS19FD162J03F	0.620 (15.7)	0.460 (11.7)	0.180 (4.6)	0.344 (8.7)	0.032 (.8)	
360	50	CDS5FY361J03F	0.250 (6.4)	0.190 (4.8)	0.160 (4.1)	0.120 (3.0)	0.016 (.4)		1800	500	CDS19FD182J03F	0.620 (15.7)	0.460 (11.7)	0.180 (4.6)	0.344 (8.7)	0.032 (.8)	
360	100	CD7FA361J03	0.275 (7.0)	0.260 (6.6)	0.125 (3.2)	0.172 (4.4)	0.016 (.4)		2000	500	CDS19FD202J03F	0.630 (16.0)	0.460 (11.7)	0.190 (4.8)	0.344 (8.7)	0.032 (.8)	
360	100	CDS10FA361J03F	0.340 (8.6)	0.270 (6.9)	0.160 (4.1)	0.141 (3.6)	0.016 (.4)		2000	500	CDS30FD202J03F	0.720 (18.3)	0.790 (20.1)	0.180 (4.6)	0.438 (11.1)	0.040 (1.0)	
360	500	D75F361J03F	0.340 (8.6)	0.270 (6.9)	0.160 (4.1)	0.141 (3.6)	0.016 (.4)		2200	500	CDS19FD222J03F	0.630 (16.0)	0.460 (11.7)	0.190 (4.8)	0.344 (8.7)	0.032 (.8)	
360	500	CDS15FD361J03F	0.440 (11.2)	0.290 (7.4)	0.160 (4.1)	0.234 (5.9)	0.025 (.6)		2200	500	CDS30FD222J03F	0.720 (18.3)	0.790 (20.1)	0.180 (4.6)	0.438 (11.1)	0.040 (1.0)	
360	500	CDS19FD361J03F	0.610 (15.5)	0.450 (11.4)	0.140 (3.6)	0.344 (8.7)	0.032 (.8)		2400	500	CDS19FD242J03F	0.630 (16.0)	0.470 (11.9)	0.210 (5.3)	0.344 (8.7)	0.032 (.8)	
390	50	CD5FY391J03F	0.270 (6.9)	0.250 (6.4)	0.190 (4.8)	0.120 (3.0)	0.016 (.4)		2400	500	CDS30FD242J03F	0.720 (18.3)	0.790 (20.1)	0.180 (4.6)	0.438 (11.1)	0.040 (1.0)	
390	50	CDS5FY391J03F	0.250 (6.4)	0.190 (4.8)	0.170 (4.3)	0.120 (3.0)	0.016 (.4)		2500	500	CDS19FD252J03F	0.630 (16.0)	0.470 (11.9)	0.210 (5.3)	0.344 (8.7)	0.032 (.8)	
390	100	CD7FA391J03	0.275 (7.0)	0.260 (6.6)	0.125 (3.2)	0.172 (4.4)	0.016 (.4)		2500	500	CDS30FD252J03F	0.720 (18.3)	0.790 (20.1)	0.190 (4.8)	0.438 (11.1)	0.040 (1.0)	
390	100	CDS10FA391J03F	0.340 (8.6)	0.270 (6.9)	0.160 (4.1)	0.141 (3.6)	0.016 (.4)		2700	500	CDS19FD272J03F	0.630 (16.0)	0.470 (11.9)	0.210 (5.3)	0.344 (8.7)	0.032 (.8)	
390	500	D75F391J03F	0.340 (8.6)	0.270 (6.9)	0.160 (4.1)	0.141 (3.6)	0.016 (.4)		2700	500	CDS30FD272J03F	0.720 (18.3)	0.790 (20.1)	0.190 (4.8)	0.438 (11.1)	0.040 (1.0)	
390	500	CDS15FD391J03F	0.440 (11.2)	0.290 (7.4)	0.160 (4.1)	0.234 (5.9)	0.025 (.6)		3000	500	CDS19FD302J03F	0.630 (16.0)	0.470 (11.9)	0.210 (5.3)	0.344 (8.7)	0.032 (.8)	
390	500	CDS19FD391J03F	0.610 (15.5)	0.450 (11.4)	0.140 (3.6)	0.344 (8.7)	0.032 (.8)		3000	500	CDS30FD302J03F	0.720 (18.3)	0.790 (20.1)	0.190 (4.8)	0.438 (11.1)	0.040 (1.0)	
400	50	CD5FY401J03F	0.270 (6.9)	0.250 (6.4)	0.190 (4.8)	0.120 (3.0)	0.016 (.4)		3300	500	CDS19FD332J03F	0.630 (16.0)	0.470 (11.9)	0.210 (5.3)	0.344 (8.7)	0.032 (.8)	
400	50	CDS5FY401J03F	0.250 (6.4)	0.190 (4.8)	0.170 (4.3)	0.120 (3.0)	0.016 (.4)		3300	500	CDS30FD332J03F	0.720 (18.3)	0.790 (20.1)	0.190 (4.8)	0.438 (11.1)	0.040 (1.0)	
400	100	CDS10FA401J03F	0.340 (8.6)	0.270 (6.9)	0.160 (4.1)	0.141 (3.6)	0.016 (.4)		3600	500	CDS19FD362J03F	0.630 (16.0)	0.470 (11.9)	0.210 (5.3)	0.344 (8.7)	0.032 (.8)	
430	100	CD7FA431J03	0.275 (7.0)	0.260 (6.6)	0.125 (3.2)	0.172 (4.4)	0.016 (.4)		3600	500	CDS30FD362J03F	0.720 (18.3)	0.790 (20.1)	0.200 (5.1)	0.438 (11.1)	0.040 (1.0)	
430	500	D75FA431J03F	0.340 (8.6)	0.310 (7.9)	0.160 (4.1)	0.141 (3.6)	0.016 (.4)		3900	500	CDS19FD392J03F	0.630 (16.0)	0.470 (11.9)	0.210 (5.3)	0.344 (8.7)	0.032 (.8)	
430	500	CDS15FD431J03F	0.440 (11.2)	0.290 (7.4)	0.160 (4.1)	0.234 (5.9)	0.025 (.6)		3900	500	CDS30FD392J03F	0.720 (18.3)	0.790 (20.1)	0.200 (5.1)	0.438 (11.1)	0.040 (1.0)	
430	500	CDS19FD431J03F	0.610 (15.5)	0.450 (11.4)	0.140 (3.6)	0.344 (8.7)	0.032 (.8)		4300	500	CDS19FD432J03F	0.630 (16.0)	0.470 (11.9)	0.220 (5.6)	0.344 (8.7)	0.032 (.8)	
470	100	CD7FA471J03	0.275 (7.0)	0.260 (6.6)	0.125 (3.2)	0.172 (4.4)	0.016 (.4)		4300	500	CDS30FD432J03F	0.720 (18.3)	0.790 (20.1)	0.200 (5.1)	0.438 (11.1)	0.040 (1.0)	
470	500	D75FA471J03F	0.340 (8.6)	0.310 (7.9)	0.160 (4.1)	0.141 (3.6)	0.016 (.4)		4700	500	CDS19FD472J03F	0.630 (16.0)	0.470 (11.9)	0.230 (5.8)	0.344 (8.7)	0.032 (.8)	
470	500	CDS15FD471J03F	0.440 (11.2)	0.300 (7.6)	0.160 (4.1)	0.234 (5.9)	0.025 (.6)		4700	500	CDS30FD472J03F	0.720 (18.3)	0.790 (20.1)	0.210 (5.3)	0.438 (11.1)	0.040 (1.0)	
470	500	CDS19FD471J03F	0.610 (15.5)	0.450 (11.4)	0.140 (3.6)	0.344 (8.7)	0.032 (.8)		5000	500	CDS19FD502J03F	0.630 (16.0)	0.480 (12.2)	0.240 (6.1)	0.344 (8.7)	0.032 (.8)	
470	500	CDS30FD471J03F	0.720 (18.3)	0.790 (20.1)	0.180 (4.6)	0.438 (11.1)	0.040 (1.0)		5000	500	CDS30FD502J03F	0.720 (18.3)	0.790 (20.1)	0.210 (5.3)	0.438 (11.1)	0.040 (1.0)	
500	500	D75F501J03F	0.340 (8.6)	0.310 (7.9)	0.160 (4.1)	0.141 (3.6)	0.016 (.4)		5100	500	CDS19FD512J03F	0.630 (16.0)	0.480 (12.2)	0.240 (6.1)	0.344 (8.7)	0.032 (.8)	
500	500	CDS15FD501J03F	0.440 (11.2)	0.300 (7.6)	0.160 (4.1)	0.234 (5.9)	0.025 (.6)		5100	500	CDS30FD512J03F	0.720 (18.3)	0.790 (20.1)	0.210 (5.3)	0.438 (11.1)	0.040 (1.0)	
500	500	CDS19FD501J03F	0.610 (15.5)	0.450 (11.4)	0.140 (3.6)	0.344 (8.7)	0.032 (.8)		5600	300	CDS19FC562J03F	0.640 (16.3)	0.480 (12.2)	0.250 (6.4)	0.344 (8.7)	0.032 (.8)	
510	100	CD7FA511J03	0.275 (7.0)	0.260 (6.6)	0.125 (3.2)	0.172 (4.4)	0.016 (.4)		5600	500	CDS30FD562J03F	0.720 (18.3)	0.790 (20.1)	0.220 (5.6)	0.438 (11.1)	0.040 (1.0)	
510	500	D75F511J03F	0.340 (8.6)	0.310 (7.9)	0.160 (4.1)	0.141 (3.6)	0.016 (.4)		6200	300	CDS19FC622J03F	0.640 (16.3)	0.480 (12.2)	0.260 (6.6)	0.344 (8.7)	0.032 (.8)	
510	500	CDS15FD511J03F	0.440 (11.2)	0.300 (7.6)	0.160 (4.1)	0.234 (5.9)	0.025 (.6)		6200	500	CDS30FD622J03F	0.730 (18.5)	0.800 (20.3)	0.220 (5.6)	0.438 (11.1)	0.040 (1.0)	
510	500	CDS19FD511J03F	0.610 (15.5)	0.450 (11.4)	0.140 (3.6)	0.344 (8.7)	0.032 (.8)		6800	300	CDS19FC682J03F	0.640 (16.3)	0.490 (12.4)	0.270 (6.9)	0.344 (8.7)	0.032 (.8)	
560	100	CD7FA561J03	0.275 (7.0)	0.260 (6.6)	0.125 (3.2)	0.172 (4.4)	0.016 (.4)		6800	500	CDS30FD682J03F	0.730 (18.5)	0.800 (20.3)	0.230 (5.8)	0.438 (11.1)	0.040 (1.0)	
560	300	D73F561J03F	0.340 (8.6)	0.310 (7.9)	0.160 (4.1)	0.141 (3.6)	0.016 (.4)		7500	100	CDS19FA752J03F	0.650 (16.5)	0.490 (12.4)	0.280 (7.1)	0.344 (8.7)	0.032 (.8)	
560	300	CDS15FC561J03F	0.450 (11.4)	0.310 (7.9)	0.160 (4.1)	0.234 (5.9)	0.025 (.6)		7500	500	CDS30FD752J03F	0.730 (18.5)	0.800 (20.3)	0.240 (6.1)	0.438 (11.1)	0.040 (1.0)	
560	500	CDS19FD561J03F	0.610 (15.5)	0.450 (11.4)	0.150 (3.8)	0.344 (8.7)	0.032 (.8)		8200	100	CDS19FA822J03F	0.650 (16.5)	0.490 (12.4)	0.300 (7.6)	0.344 (8.7)	0.032 (.8)	
620	100	CD7FA621J03	0.275 (7.0)	0.260 (6.6)	0.125 (3.2)	0.172 (4.4)	0										

Mica Capacitors **Miniature Dipped**

Notice and Disclaimer: All product drawings, descriptions, specifications, statements, information and data (collectively, the "Information") in this datasheet or other publication are subject to change. The customer is responsible for checking, confirming and verifying the extent to which the Information contained in this datasheet or other publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without any guarantee, warranty, representation or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on the knowledge that the Cornell Dubilier company providing such statements ("Cornell Dubilier") has of operating conditions that such Cornell Dubilier company regards as typical for such applications, but are not intended to constitute any guarantee, warranty or representation regarding any such matter – and Cornell Dubilier specifically and expressly disclaims any guarantee, warranty or representation concerning the suitability for a specific customer application, use, storage, transportation, or operating environment. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by Cornell Dubilier with reference to the use of any Cornell Dubilier products is given gratis (unless otherwise specified by Cornell Dubilier), and Cornell Dubilier assumes no obligation or liability for the advice given or results obtained. Although Cornell Dubilier strives to apply the most stringent quality and safety standards regarding the design and manufacturing of its products, in light of the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies or other appropriate protective measures) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage. Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated in such warnings, cautions and notes, or that other safety measures may not be required.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cornell Dubilier:

[CD5FA131JO3](#) [CD5CC150JO3](#) [CD5CC120JO3](#) [CD5CC180JO3](#) [CD5CC180DO3](#) [CD5CC100JO3](#) [CD5FA201JO3](#)
[CD5CC050CO3](#) [CD5FC121JO3](#) [CD5FC101JO3](#) [CD5FA181JO3](#) [CD5FA151JO3](#) [CD5EC430JO3](#) [CD7FC271FO3](#)
[CD5FC111GO3](#) [CD5CC070DO3](#) [CD5CC050DO3](#) [CD5CC020DO3](#) [CD5CC030DO3](#) [CD5CC010DO3](#)
[CD5CC060DO3](#) [CD5CC080DO3](#) [CD5CC040DO3](#) [CD5EC680JO3](#) [CDS19FD502FO3](#) [CD6ED220DO3](#)
[CD5EC620JO3](#) [CD5EC510JO3](#) [CD5EC330JO3](#) [CD5FC910JO3](#) [CD5EC300JO3](#) [CD6FC910FO3](#) [CD5EC560JO3](#)
[CD5CC100DO3](#) [CD5EC360JO3](#) [CD5EC390JO3](#) [CD5EC200JO3](#) [CD5EC240JO3](#) [CD5EC820JO3](#) [D73F681FO3](#)
[D75F431JO3](#) [D75F391JO3](#) [CD5FC101FO3](#) [CD7FC221GO3](#) [CDS10CD050DO3](#) [CDS5EC200DO3](#) [CD5FA201FO3](#)
[CD5FY331FO3](#) [CD5EC560FO3](#) [CD5FY271FO3](#) [CD5CC040CO3](#) [CD5CC040CO3F](#) [CD5CC050CO3F](#)
[CD5CC060CO3](#) [CD5CC060CO3F](#) [CD5CC070CO3](#) [CD5CC070CO3F](#) [CD5CC080CO3](#) [CD5CC080CO3F](#)
[CD5CC090CO3](#) [CD5CC090CO3F](#) [CD5CC090DO3](#) [CD5CC100DO3F](#) [CD5CC110DO3](#) [CD5CC110DO3F](#)
[CD5CC110JO3](#) [CD5CC120DO3](#) [CD5CC120DO3F](#) [CD5CC150DO3](#) [CD5CC150DO3F](#) [CD5CC180DO3F](#)
[CD5EC200DO3](#) [CD5EC200DO3F](#) [CD5EC220DO3](#) [CD5EC220DO3F](#) [CD5EC220JO3](#) [CD5EC240DO3](#)
[CD5EC240DO3F](#) [CD5EC270GO3](#) [CD5EC270GO3F](#) [CD5EC270JO3](#) [CD5EC300GO3](#) [CD5EC300GO3F](#)
[CD5EC330GO3](#) [CD5EC330GO3F](#) [CD5EC360GO3](#) [CD5EC360GO3F](#) [CD5EC390GO3](#) [CD5EC390GO3F](#)
[CD5EC430GO3](#) [CD5EC430GO3F](#) [CD5EC470GO3](#) [CD5EC470GO3F](#) [CD5EC470JO3](#) [CD5EC510GO3](#)
[CD5EC510GO3F](#) [CD5EC560GO3](#) [CD5EC560GO3F](#) [CD5EC620GO3](#) [CD5EC620GO3F](#)