







SEE
DETAIL "A"

SEE DETAIL "B"

SECTION A-A



DETAIL "B"
SCALE=6:1




DETAIL "A"
CHAMFER
SCALE=6:1

NOTES: UNLESS OTHERWISE SPECIFIED

1. COSMETIC SPECIFICATION REFER TO WI-QA-038.

IMPEDANCE (Z)			
Frequency	25 MHz	100 MHz	300 MHz
Nominal (REF)	96 Ω	191 Ω	308 Ω
Minimum	- Ω	153 Ω	- Ω

Z vs. FREQUENCY
(REF. ONLY)




AGILENT E4991A Impedance/Material Analyzer
HP 16092A-Test Fixture

FERRITE CORE DIMENSIONS (SPEC): mm [in]

A	25.40 [1.000]	±	0.46 [.018]
B	15.49 [.610]	±	0.30 [.012]
C	28.50 [1.122]	±	0.71 [.028]

WEIGHT/1000 44.57 kgs [98.26 Lbs]



DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
				PROJECT/PART NUMBER:	REV	PART TYPE:	DRAWN BY:
				28B0999-300	B	FERRITE CORE	Jcai
B	ADD DOT AND NOTES, UPDATED LOGO	03/19/2019	Jcai	DATE:	08/18/09	SCALE:	2:1
A	ORIGINAL DRAFT	08/18/09	Jcai	CAD #	28B0999-300-B	TOOL #	B0999D
REV	DESCRIPTION	DATE	INT	MATERIAL: FERRITE			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[28B0999-300](#)