

Surface Mount Multilayer Varistors

Normal Surge Protection (NA) Series

Features:

- Fast Response < 0.5 ns
- Low Capacitance
- Low Clamping Voltage and High Energy Absorption

Application Fields:

- Telecommunications
- Automotive Systems
- Data Systems
- Power Supplies

Ordering Information:

Part Number	Working Voltage (max)		Breakdown Voltage 1 mA (V)	Peak Current (max) 8/20 μ s (A)	Clamping Voltage (max)		Energy Absorption (max) 10/1000 μ s (J)	Typical Capacitance Ref. 1 KHz (pF)
	AC (V _{RMS})	DC (V)			(A)	(V)		
MLV0402NA006V0020	4	5.5	8 (7.5~10.5)	20	1	20	0.05	200
MLV0402NA009V0020	6	9	12 (10.2~13.8)	20	1	23	0.05	135
MLV0402NA011V0020	8	11	15 (12.8~17.3)	20	1	25	0.05	75
MLV0402NA014V0020	11	14	18 (15.3~20.7)	20	1	30	0.05	50
MLV0402NA018V0020	14	18	24 (21.6~26.4)	20	1	39	0.05	45
MLV0603NA006V0030	4	5.5	8 (7.5~10.5)	30	1	20	0.1	360
MLV0603NA009V0030	6	9	12 (10.2~13.8)	30	1	23	0.1	300
MLV0603NA014V0030	11	14	18 (15.3~20.7)	30	1	30	0.1	210
MLV0603NA018V0030	14	18	24 (21.6~26.4)	30	1	39	0.1	160
MLV0603NA022V0030	17	22	27 (24.3~29.7)	30	1	44	0.1	145
MLV0603NA030V0030	25	30	39 (35.1~42.9)	30	1	65	0.1	110
MLV0603NA038V0030	30	38	47 (42.3~51.7)	30	1	77	0.1	90
MLV0805NA006V0080	4	5.5	8 (7.5~10.5)	80	1	20	0.1	1400
MLV0805NA009V0080	6	9	12 (10.2~13.8)	80	1	23	0.1	650
MLV0805NA011V0100	8	11	15 (12.75~17.25)	100	1	25	0.2	410
MLV0805NA014V0100	11	14	18 (15.3~20.7)	100	1	30	0.2	350
MLV0805NA018V0100	14	18	24 (21.6~26.4)	100	1	39	0.2	300
MLV0805NA022V0100	17	22	27 (24.3~29.7)	100	1	44	0.2	250
MLV0805NA026V0100	20	26	33 (29.7~36.3)	100	1	54	0.3	220
MLV0805NA030V0100	25	30	39 (35.1~42.9)	100	1	65	0.3	200
MLV0805NA038V0100	30	38	47 (42.3~51.7)	100	1	77	0.3	150
MLV0805NA045V0080	35	45	56 (50.4~61.6)	80	1	90	0.3	110
MLV1206NA006V0100	4	5.5	8 (7.5~10.5)	100	1	20	0.2	3100
MLV1206NA014V0100	11	14	18 (15.3~20.7)	100	1	30	0.3	800
MLV1206NA018V0100	14	18	24 (21.6~26.4)	100	1	38	0.3	620
MLV1206NA022V0100	17	22	27 (24.3~29.7)	100	1	44	0.4	700
MLV1206NA026V0100	20	26	33 (29.7~36.3)	100	1	54	0.5	480
MLV1206NA030V0100	25	30	39 (35.1~42.9)	100	1	65	0.6	400

Surface Mount Multilayer Varistors

Normal Surge Protection (NA) Series

Ordering Information:

Part Number	Working Voltage (max)		Breakdown Voltage 1 mA (V)	Peak Current (max) 8/20 μ s (A)	Clamping Voltage (max)		Energy Absorption (max) 10/1000 μ s (J)	Typical Capacitance 1 KHz (pF)
	AC (V _{RMS})	DC (V)			(A)	(V)		
MLV1206NA038V0100	30	38	47 (42.3~51.7)	100	1	77	0.7	260
MLV1206NA045V0100	35	45	56 (50.4~61.6)	100	1	90	0.8	230
MLV1206NA056V0100	40	56	68 (61.2~74.8)	100	1	110	1.0	200
MLV1206NA065V0100	50	65	82 (73.8~90.2)	100	1	135	0.5	175
MLV1206NA085V0100	60	85	100 (90~110)	100	1	165	0.6	150
MLV1210NA006V0250	4.5	5.5	8 (7.5~10.5)	250	2.5	20	0.5	5200
MLV1210NA018V0250	14	18	24 (21.6~26.4)	250	2.5	38	0.8	1150
MLV1210NA022V0250	17	22	27 (24.3~29.7)	250	2.5	44	1.0	1720
MLV1210NA026V0250	20	26	33 (29.7~36.3)	250	2.5	54	1.2	610
MLV1210NA030V0250	25	30	39 (35.1~42.9)	250	2.5	65	1.4	920
MLV1210NA038V0250	30	38	47 (42.3~51.7)	250	2.5	77	1.6	780
MLV1210NA045V0250	35	45	56 (50.4~61.6)	250	2.5	90	2.0	400
MLV1210NA056V0250	40	56	68 (61.2~74.8)	250	2.5	110	2.3	300
MLV1210NA085V0200	60	85	100 (90~110)	200	2.5	165	1.4	210
MLV1812NA018V0500	14	18	24 (21.6~26.4)	500	5	38	1.7	2000
MLV1812NA030V0500	25	30	39 (35.1~42.9)	500	5	65	2.9	2500
MLV1812NA038V0500	30	38	47 (42.3~51.7)	500	5	77	3.5	2200
MLV1812NA045V0500	35	45	56 (50.4~61.6)	500	5	90	4.2	1000
MLV2220NA018V1000	14	18	24 (21.6~26.4)	1000	10	38	3.1	8500
MLV2220NA030V1000	25	30	39 (35.1~42.9)	1000	10	65	5.5	3900
MLV2220NA038V1000	30	38	47 (42.3~51.7)	1000	10	77	6.3	4600
MLV2220NA056V1000	40	56	68 (61.2~74.8)	1000	10	110	8.8	4000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AEM:

[MLV0603NA009V0030T](#) [MLV0805NA009V0080T](#) [MLV2220NA009V1000T](#) [MLV1210NA056V0250T](#)
[MLV1812NA085V0400T](#) [MLV1206NA009V0100T](#) [MLV1812NA090V0400T](#) [MLV0805NA014V0100T](#)
[MLV0603NA038V0030T](#) [MLV1210NA030V0250T](#) [MLV0805NA003V0040T](#) [MLV1210NA006V0250T](#)
[MLV1206NA014V0100T](#) [MLV1210NA014V0250T](#) [MLV1812NA065V0400T](#) [MLV0603NA006V0030T](#)
[MLV0805NA026V0100T](#) [MLV1812NA030V0500T](#) [MLV1206NA030V0100T](#) [MLV0603NA003V0030T](#)
[MLV1210NA017V0250T](#) [MLV2220NA017V1000T](#) [MLV2220NA026V1000T](#) [MLV1210NA038V0250T](#)
[MLV1210NA022V0250T](#) [MLV0805NA056V0080T](#) [MLV0402NA014V0020T](#) [MLV1206NA038V0100T](#)
[MLV1206NA018V0100T](#) [MLV0603NA026V0030T](#) [MLV0402NA006V0020T](#) [MLV0603NA022V0030T](#)
[MLV1206NA065V0100T](#) [MLV1206NA056V0100T](#) [MLV0805NA065V0060T](#) [MLV1812NA011V0500T](#)
[MLV1210NA065V0250T](#) [MLV2220NA038V1000T](#) [MLV2220NA011V1000T](#) [MLV1812NA017V0500T](#)
[MLV1812NA022V0500T](#) [MLV2220NA056V1000T](#) [MLV0603NA018V0030T](#) [MLV2220NA022V1000T](#)
[MLV0603NA045V0030T](#) [MLV1210NA011V0250T](#) [MLV0402NA018V0020T](#) [MLV1812NA056V0500T](#)
[MLV0805NA006V0080T](#) [MLV1206NA085V0100T](#) [MLV1812NA045V0500T](#) [MLV0402NA017V0020T](#)
[MLV0402NA003V0020T](#) [MLV0805NA045V0080T](#) [MLV1206NA017V0100T](#) [MLV1812NA038V0500T](#)
[MLV1210NA026V0250T](#) [MLV0402NA038V0020T](#) [MLV1812NA009V0500T](#) [MLV1206NA090V0100T](#)
[MLV0402NA030V0020T](#) [MLV0805NA017V0100T](#) [MLV1812NA026V0500T](#) [MLV2220NA018V1000T](#)
[MLV0402NA009V0020T](#) [MLV1812NA018V0500T](#) [MLV0805NA011V0100T](#) [MLV2220NA085V0800T](#)
[MLV2220NA090V0800T](#) [MLV0402NA026V0020T](#) [MLV2220NA014V1000T](#) [MLV0805NA030V0100T](#)
[MLV0805NA018V0100T](#) [MLV0805NA022V0100T](#) [MLV0603NA011V0030T](#) [MLV1206NA003V0060T](#)
[MLV2220NA065V0800T](#) [MLV1812NA014V0500T](#) [MLV1210NA085V0200T](#) [MLV1206NA022V0100T](#)
[MLV1206NA026V0100T](#) [MLV1210NA045V0250T](#) [MLV0402NA011V0020T](#) [MLV1210NA009V0250T](#)
[MLV0603NA030V0030T](#) [MLV1206NA006V0100T](#) [MLV0805NA038V0100T](#) [MLV2220NA045V1000T](#)
[MLV0603NA017V0030T](#) [MLV1210NA018V0250T](#) [MLV1812NA127V0300T](#) [MLV2220NA030V1000T](#)
[MLV0402NA022V0020T](#) [MLV1206NA011V0100T](#) [MLV1210NA090V0200T](#) [MLV0603NA014V0030T](#)
[MLV1206NA045V0100T](#) [MLV0402NA014V0020TM](#) [MLV0402NA018V0020TM](#) [MLV0402NA011V0020](#)