Cree® PLCC4 1 in 1 SMD LED CLM4B-RKC/AKC

PRODUCT DESCRIPTION

CREE 🔶

SMD LEDs is packaged in the industry standard package. These LEDs have high reliability performance and are designed to work under a wide range of environmental conditions. This high reliability feature makes them ideally suited to be used under illumination application conditions.

Its wide viewing angle makes these LEDs ideally suited for channel letter, or general backlighting and illumination applications. The flat top emitting surface makes it easy for these LEDs to mate with light pipes.

FEATURES

- Size (mm):3.2 x 2.8
- Color and Typical Dominant Wavelength: Red (624nm) Amber (591nm)
- Luminous Intensity (mcd) CLM4B-RKC:(1120 - 2240) CLM4B-AKC:(1400 - 2800)
- Lead-Free
- RoHS Compliant

APPLICATIONS

- Channel Letter
- Architectural Lighting

ABSOLUTE MAXIMUM RATINGS ($T_A = 25^{\circ}C$)

Items	Color	Symbol	Absolute Maximum Rating	Unit
Forward Current	Red/Amber	I _F	70	mA
Peak Forward Current Note	Red/Amber	I _{FP}	200	mA
Reverse Voltage	Red/Amber	V _R	5	V
Power Dissipation	Red	P _D	210	mW
Power Dissipation	Amber	P _D	182	mW
Operation Temperature	Red/Amber	T _{opr}	-40 ~ +100	°C
Storage Temperature	Red/Amber	T _{stg}	-40 ~ +100	°C
Junction Temperature	Red/Amber	Τ,	110	°C
Junction/Ambient	Red	R _{THJA}	270	°C/W
Junction/Ambient	Amber	R _{THJA}	240	°C/W
Junction/Solder Point	Red	R _{THJS}	130	°C/W
Junction/Solder Point	Amber	R _{THJS}	120	°C/W
Electrostatic Discharge Classification(MIL-STD-883E)	Red/Amber	ESD	Class 2	

Note: Pulse width ≤ 0.1 msec, duty $\leq 1/10$.

TYPICAL ELECTRICAL & OPTICAL CHARACTERISTICS (T_A = 25^{\circ}C)

Characteristics	Color	Symbol	Condition	Unit	Minimum	Typical	Maximum
Forward Voltage	Red	V _F	$I_{F} = 50 \text{ mA}$	V		2.5	3.0
Forward Voltage	Amber	V _F	$I_{F} = 50 \text{ mA}$	V		2.2	2.6
Reverse Current	Red/Amber	I _R	$V_{R} = 5 V$	μA			10
Deminent Weyeleneth	Red	λ_{D}	$I_{F} = 50 \text{ mA}$	nm	618	624	630
	Amber	λ_{D}	$I_{F} = 50 \text{ mA}$	nm	587	591	596
	Red	λ_{D}	$I_{F} = 50 \text{ mA}$	mcd	1120	1700	
Luminous intensity	Amber	I_v	$I_{F} = 50 \text{ mA}$	mcd	1400	1900	

Note: Continuous reverse voltage can cause LED damage.

INTENSITY BIN LIMIT (I_F = 50 mA)

Red(CLM4B-RKC)

Bin Code	Min.(mcd)	Max.(mcd)
Wa	1120	1400
Wb	1400	1800
Xa	1800	2240

Bin Code	Min.(mcd)	Max.(mcd)
Wb	1400	1800
Xa	1800	2240
Xb	2240	2800

Tolerance of measurement of luminous intensity is $\pm 10\%$.

COLOR BIN LIMIT ($I_F = 50 \text{ mA}$)

Red (CLM4B-RKC)

Bin Code	Min.(nm)	Max.(nm)
RA	618	630

Amber(CLM4B-AKC)
--------	------------

Bin Code	Min.(nm)	Max.(nm)
A3	587	590
A4	590	593
A5	593	596

Tolerance of measurement of dominant wavelength is ± 1 nm.

ORDER CODE TABLE*

Color	Luminous Intensity (mcd) Dominant Wave		Navelength	avelength			
COIOF		Min.	Max.	Color Bin	Min.(nm)	Color Bin	Max.(nm)
Red	CLM4B-RKC-CWaXaAA3	1120	2240	RA	618	RA	630
Red	CLM4B-RKC-CWbXaAA3	1400	2240	RA	618	RA	630

		Luminous Intensity (mcd)		Dominant Wavelength			
COIOF		Min.	Max.	Color Bin	Min.(nm)	Color Bin	Max.(nm)
Amber	CLM4B-AKC-CWbXb353	1400	2800	A3	587	A5	596
Amber	CLM4B-AKC-CWbXb343	1400	2800	A3	587	A4	593

Notes:

- 1. The above kit numbers represent order codes that include multiple intensity-bin and color-bin codes. Only one intensity-bin code and one color-bin code will be shipped on each bulk. Single intensity-bin code and single color-bin codes will not be orderable.
- 2. Please refer to the "Cree LED Lamp Reliability Test Standards" document ^{#1} for reliability test conditions.
- 3. Please refer to the "Cree LED Lamp Soldering & Handling" document ^{#2} for information about how to use this LED product safely.

#1: Refer to http://www.cree.com/led-components/media/documents/LED_Lamp_Reliability_Test_Standard.pdf #2: Refer to http://www.cree.com/led-components/media/documents/sh-HB.pdf



GRAPHS





(RELATIVE LUMINOUS INTENSITY)



FIG.4 RELATIVE LUMINOUS INTENSITY VS. WAVELENGTH.



FIG.6 FAR FIELD PATTERN

I_F(mA)



TEMPERATURE (Tjmax=110 °C)

FIG.5 RED&AMBER MAXIMUM FORWARD DC CURRENT VS AMBIENT TEMPERATURE (Tjmax=110 $^\circ C)$

The above data are collected from statistical figures that do not necessarily correspond to the actual parameters of each single LED. Hence, these data will be changed without further notice.



MECHANICAL DIMENSIONS

All dimensions are in mm.



NOTES

RoHS Compliance

The levels of RoHS-restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application in accordance with EU Directive 2011/65/EC (RoHS2), as implemented by EU member states on January 2, 2013 and amended on March 31, 2015 by EU Directive 2015/863/EU.

RoHS Declarations for this product can be obtained from your Cree representative or from the Product Ecology section of the Cree website.

Vision Advisory Claim

Users should be cautioned not to stare at the light of this LED product. The bright light can damage the eye.



KIT NUMBER SYSTEM

Cree LED lamps are tested and sorted into performance bins. A bin is specified by ranges of color, forward voltage, and brightness. Sorted LEDs are packaged for shipping in various convenient options. Please refer to the "Cree LED Lamp Packaging Standard" document for more information about shipping and packaging options.

Cree LEDs are sold by order codes in combinations of bins called kits. Order codes are configured in the following manner:



REFLOW SOLDERING

- The CLM4B-RKC AKC is rated as a MSL 5a product.
- The recommended floor life out of bag is 24hrs.
- The temperature profile is as below.

Use only with CLM4B-RKC AKC

Solder
Average ramp-up rate = 4°C/s max
Preheat temperature = 150°C ~200°C
Preheat time = 120s max
Ramp-down rate = 6°C/s max
Peak temperature = 235°C max
Time within $5^{\circ}C$ of actual Peak Temperature = $10s \max$
Duration above 217°C is 45s max

Refer to "http://www.cree.com/led-components/media/documents/sh-HB.pdf" for soldering & handling details.

NOTES

- The packaging sizes of these SMD products are very small and the resin is still soft after solidification. Users are required to handle with care. Never touch the resin surface of SMD products.
- To avoid damaging the product's surface and interior device, it is recommended to choose a special nozzle to pick up the SMD products during the process of SMT production. If handling is necessary, take special care when picking up these products. The following method is necessary:

PACKAGING

- The boxes are not water resistant and they must be kept away from water and moisture.
- The LEDs are packed in cardboard boxes after packaging in normal or anti-electrostatic bags.
- Cardboard boxes will be used to protect the LEDs from mechanical shocks during transportation.
- The reel pack is applied in SMD LED.
- Max 2000 pcs per reel.

Copyright © 2019 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree and the Cree logo are registered trademarks of Cree, Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cree, Inc.:

CLM4B-AKC-CWbXb343 CLM4B-AKC-CWbXb353 CLM4B-RKC-CWbXaAA3 CLM4B-RKC-CWaXaAA3