



MGV12035R6M-10

PHYSICAL DIMENSIONS:

A	13.50	±	0.50
B	12.60	±	0.30
C	3.50	±	0.30
D	3.60	±	0.50
E	2.30	±	0.50


LAND PATTERNS FOR REFLOW SOLDERING



ELECTRICAL SPECIFICATION @ 25°C

	Min	Nom	Max
INDUCTANCE (uH)			
L @ 100 KHz/0.25V ± 20%	4.48	5.60	6.72
DCR (Ω)			0.019

Saturation Current ³ Isat (A)	19.00
Temperature Rise Current Irms ⁴ (A)	9.50



RoHS



UNCONTROLLED
DOCUMENT

NOTES: UNLESS OTHERWISE SPECIFIED

- COMPONENTS SHOULD BE ADEQUATELY PREHEATED BEFORE SOLDERING.
- OPERATION TEMPERATURE RANGE:
-40°C~+125°C (INCLUDING SELF-HEATING).
- SATURATION CURRENT Isat IS DEFINED AS MAXIMUM AMOUNT OF CURRENT BY WHICH INDUCTANCE WILL DROP BY TYPICAL VALUE OF 25% OF INITIAL INDUCTANCE (Ta=25±5°C).
- TEMPERATURE RISE CURRENT (Irms): DC CURRENT THAT CAUSES THE TEMPERATURE RISE (ΔT ≤ 40°C) FROM 25°C AMBIENT.

DIMENSIONS ARE IN mm.				<p>This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.</p> <p>Laird</p>				
				PROJECT/PART NUMBER:		REV	PART TYPE:	DRAWN BY:
				MGV12035R6M-10		A	POWER INDUCTOR	QIU
				DATE: 05/14/13		SCALE: NTS		SHEET:
A	ORIGINAL DRAFT		05/14/13	QIU	CAD #	TOOL #	1 of 1	
REV	DESCRIPTION		DATE	INT	MGV12035R6M-10-A			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[MGV12035R6M-10](#)