


Thin, Flexible, Resonant Microwave Absorber

THIN, FLEXIBLE, RESONANT ABSORBER



Eccosorb SF-U is a narrow banded, magnetically loaded resonant absorber sheet for free-space applications. These polyurethane rubber sheets are designed to be bonded to flat or curved metallic surfaces to reduce the reflectivity in a narrow band of frequencies. Eccosorb SF-U reflects -20 dB or less of normally incident microwave energy at the design frequency in the range of 1 to 26 GHz.

FEATURES AND BENEFITS

- High mechanical strength
- ease of bonding
- excellent abrasion resistance
- Silicone-free

MARKETS

- Commercial Telecom
- Security and Defense
- Automotive

SPECIFICATIONS

TYPICAL PROPERTIES	ECCOSORB SF-U
Max service temperature °C (°F)	120 (325)
Hardness (Shore A)	80
Surface Density Range	3 to 21.5
Density Range g/cm ³	2.6 – 4.7
Tensile Strength MPa	2. – 5.5
Elongation at break %	60 – 225
Tear Strength N/mm	3.0 to 15

Data for design engineer guidance only. Observed performance varies in application. Engineers are reminded to test the material in application.

APPLICATIONS



- Lining radar nacelles and the exterior of airframes particularly where high power is present.
- Lining of cavity backed and shrouded telecommunication antennas where narrowband performance is required.
- Lining metal surfaces of vehicles to reduce overall radar signature.
- Attaching to masts of ships, walls, etc to reduce reflections and echoes from nearby antennas.
- Lining magnetron housings to prevent detuning.
- Fabricating into tapered shapes for impedance matching in waveguide or microstrip applications.
- Lining metal surfaces to attenuate surface currents, suppressing reflections inside microwave modules, and dampening cavity resonances in microwave modules.
- For module interference, cavity resonance and surface current problems, ECCOSORB® GDS-U, ECCOSORB® MCS-U and ECCOSORB® BSR-U are recommended due to their high magnetic loss properties, broadband performance, as well as the availability of a wider range of thicknesses (0.010" to 0.100")

AVAILABILITY

- Standard sheets are 305 x 305mm (12"x12")
- Thickness varies depending on resonant frequency desired.
- Other resonant frequencies can be supplied on special order.
- The material can also be supplied in customized shapes.
- It can be supplied with a pressure sensitive adhesive (PSA).

INSTRUCTIONS FOR USE

- Eccosorb SF-U is designed to function directly in front of a metallic surface. If this is not the case, a metallic foil should first be bonded to the object.
- To obtain a strong bond of the absorber to the object, clean the surface with a degreasing solvent, apply a thin coat of primer to the dried surface and apply a RTV silicone adhesive.
- Eccosorb SF-U can be readily cut with a sharp knife and template. It is a very flexible material and will conform to mild curvatures.



RFP-DS-SFU 121715

Any information furnished by Laird Technologies, Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird Technologies materials rests with the end user. Laird Technologies makes no warranties as to the fitness, merchantability, suitability or non-infringement of any Laird Technologies materials or products for any specific or general uses. Laird Technologies shall not be liable for incidental or consequential damages of any kind. All Laird Technologies products are sold pursuant to the Laird Technologies' Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request. © Copyright 2015 Laird Technologies, Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Technologies Logo, and other marks are trademarks or registered trademarks of Laird Technologies, Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird Technologies or any third party intellectual property rights.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[303540028](#)