

Versal AI Core Series VCK190 Evaluation Kit

OVERVIEW

Versal® AI Core series VCK190 evaluation kit, equipped with the best AI performance-in-portfolio VC1902 device, is built for designs requiring high throughput AI inference and signal processing compute performance. Delivering 100X greater compute power than today's server-class CPUs, with various connectivity options and standardized development flows, the VCK190 is an ideal evaluation and prototyping platform for cloud, network, and edge applications.

HIGHLIGHTS

Evaluate Versal AI Core Series Capabilities

- > Equipped with Versal ACAP VC1902 production silicon
- > AI and DSP Engines providing 100X greater compute over today's server-class CPUs
- > Pre-built partner reference designs for rapid prototyping

Breadth of Connectivity Options for Rapid Development

- > PCIe® Gen4 interface for high compute performance markets
- > HDMI for video processing applications
- > SFP28/QSFP28/RJ-45 for networking applications
- > DDR4 and LPDDR4 memory interfaces
- > FMC expansion connectors supporting a variety of optional plug-in cards


Co-Optimized Tools and Debug Method

- > Fully supported by Vivado® Design Suite, Vitis™ unified software platform, and Vitis AI



TARGET APPLICATIONS

- > Data Center Compute
- > 5G Radio & Beamforming (DFE)
- > Cable-Access (Head-End)
- > Wireless Test Equipment
- > Automotive/ADAS prototyping
- > A&D Radar, Early Warning



- | | |
|----|-------------------------|
| 01 | VCK190 Evaluation Board |
| 02 | QSPI Boot Module |
| 03 | Pmod Module |
| 04 | 2 Ethernet Cables |
| 05 | USB Type-C Cable |
| 06 | 2 Micro SD Cards |
| 07 | 180W (12V) Power Supply |

TAKE THE NEXT STEP

To purchase or to learn more about the Versal AI Core series VCK190 evaluation kit, visit www.xilinx.com/vck190

Corporate Headquarters

Xilinx, Inc.
2100 Logic Drive
San Jose, CA 95124
USA
Tel: 408-559-7778
www.xilinx.com

Xilinx Europe

Xilinx Europe
Blancoli Avenue
Citywest Business Campus
Saggart, County Dublin
Ireland
Tel: +353-1-464-0311
www.xilinx.com

Japan

Xilinx K.K.
Art Village Osaki Central Tower 4F
1-2-2 Osaki, Shinagawa-ku
Tokyo 141-0032 Japan
Tel: +81-3-6744-7777
japan.xilinx.com

Asia Pacific Pte. Ltd.

Xilinx, Asia Pacific
5 Changi Business Park
Singapore 486040
Tel: +65-6407-3000
www.xilinx.com

India

Xilinx India Technology Services Pvt. Ltd.
Block A, B, C, 8th & 13th floors,
Meenakshi Tech Park, Survey No. 39
Gachibowli(V), Seri Lingampally (M),
Hyderabad -500 084
Tel: +91-40-6721-4747
www.xilinx.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xilinx:

[EK-VCK190-G-ED](#) [EK-VCK190-G-ED-J](#)