

# Zynq UltraScale+ RFSoc ZCU216 Evaluation Kit

## OVERVIEW

Equipped with the industry's only single-chip adaptable radio device, the Zynq® UltraScale+™ RFSoc ZCU216 evaluation kit is the ideal platform for both rapid prototyping and high-performance RF application development.

Reference add-on cards and connectivity options make the ZCU216 kit suitable for developing, testing, and debug of next-gen products while reducing development complexity and improving time to market.

Co-optimized with Xilinx's comprehensive Vivado® Design Suite, the ZCU216 kit comes with design files, development tools, and IPs.

## KEY FEATURES

### Featuring Industry's Only Adaptable Single-Chip Radio Platform

- > Zynq UltraScale+ RFSoc Gen 3 ZU49DR on the ZCU216 board
- > Full sub-6GHz with extended mmWave and multi-band support
- > Integrated direct RF-sampling enabling RF design in the digital domain
- > 16 14-bit resolution 2.5GSPS ADCs
- > 16 14-bit resolution 10GSPS DACs

### Reference Design and Add-on Cards for Fast Evaluation and Prototyping

- > XM650 16T16R loopback card for quick loopback test, multi-tile synchronization (MTS), and example reference layout for baluns
- > XM655 16T16R breakout card for in-depth performance measurements and external clocking
- > CLK104 add-on card for internal and external reference clocking

### Flexible I/O Options

- > FPGA Mezzanine Card (FMC+) interface for I/O expansion
- > 2 18GB/s 400pin RFMC2.0 interfaces
- > 4 SFP28 interfaces for high-speed I/Os


### Simplified Development Platform for Short Design Cycle

- > Simplified hardware design with fewer RF components vs. discrete solutions
- > Easy RF configuration enabled by Xilinx® Vivado® Design Suite, IPs, and RF evaluation tool



## TARGET APPLICATIONS

- > 5G Wireless in Sub-6Ghz
- > Millimeter Wave Intermediate Frequency (IF) Applications and Unlicensed Bands
- > Digital Phased Array Radar
- > Fixed Wireless Access
- > Terrestrial Satellite Communications
- > Test and Measurement



01	ZCU216 Evaluation Board	08	4 SSMP to SSMP Cables
02	XM655 16T16R Breakout Add-On Card	09	4 Joy Signal Jumper Cables
03	XM650 16T16R N79 Loopback Add-On Card	10	Ethernet Cable
04	CLK104 RF Clock Add-On Card	11	2 Micro USB Cables
05	6 Filters 2 Low Pass: DC-2500MHz 2 Mid Band Pass: 3000-4300MHz 2 High Band Pass: 4900-6200MHz	12	MicroSD Card
06	2 Carlisle SMA 8 Cable Assemblies	13	Power Cords and Adapters
07	2 SMA Cables	14	Vivado® Design Suite: System Edition Voucher
		15	Hand Tools

## TAKE THE NEXT STEP

For more information, documents, and reference designs, or to purchase, visit [www.xilinx.com/zcu216](http://www.xilinx.com/zcu216)

## Corporate Headquarters

Xilinx, Inc.  
2100 Logic Drive  
San Jose, CA 95124  
USA  
Tel: 408-559-7778  
[www.xilinx.com](http://www.xilinx.com)

## Xilinx Europe

Xilinx Europe  
Blancoli Avenue  
Citywest Business Campus  
Saggart, County Dublin  
Ireland  
Tel: +353-1-464-0311  
[www.xilinx.com](http://www.xilinx.com)

## Japan

Xilinx K.K.  
Art Village Osaki Central Tower 4F  
1-2-2 Osaki, Shinagawa-ku  
Tokyo 141-0032 Japan  
Tel: +81-3-6744-7777  
[japan.xilinx.com](http://japan.xilinx.com)

## Asia Pacific Pte. Ltd.

Xilinx, Asia Pacific  
5 Changi Business Park  
Singapore 486040  
Tel: +65-6407-3000  
[www.xilinx.com](http://www.xilinx.com)

## India

Xilinx India Technology Services Pvt. Ltd.  
Block A, B, C, 8th & 13th floors,  
Meenakshi Tech Park, Survey No. 39  
Gachibowli(V), Seri Lingampally (M),  
Hyderabad -500 084  
Tel: +91-40-6721-4747  
[www.xilinx.com](http://www.xilinx.com)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xilinx:

[EK-U1-ZCU216-ES1-G](#) [EK-U1-ZCU216-G](#) [EK-U1-ZCU216-G-J](#)