



# Flat Terminal block 5 poles with snap-in pins LNEZDA+DA- and contact opening function 46.485.1117.50



Minimum mounting distance  
Metal surface



Compliance with creepage distances and clearances  
has to be ensured by the structural design of the luminaire.

CAD

T 85  
-35°C



max. ø 1,8 mm



max. ø 1,8 mm



0,5 - 1,2



24A

250 V  
400 V

# Flat Terminal block 5 poles with snap-in pins LNEZDA+DA- and contact opening function 46.485.1117.50



## DESCRIPTION

Flat terminal block 5 pole with contact opening function

Upper terminal connection: 0.5 - 2.5 mm<sup>2</sup>

Direct insertion of solid wire ends and finely stranded wire ends by using the contact opening function Contact opening function - also for release of already inserted wires

Lower terminal connection:

- 0.5 - 2.5 mm<sup>2</sup> for solid wire ends

- 1.5 - 2.5 mm<sup>2</sup> for rigid and stranded wire ends

- Wire release function by twisting and pulling

Strip length: 9 ±1 mm

Top Test openings

Approvals: ÖVE Reg. Compliance with creepage distances and clearances (eg according to EN 60598) has to be ensured by the structural design of the luminaire.

Sheet metall cutout is compatible to 46.415.1114.50

Product name:	Flat Terminal block 5 poles with snap-in pins LNEZDA+DA- and contact opening function
---------------	---

Mounting method 1:	Snap-in pins LNEZDA+DA-
--------------------	-------------------------

Material:	Housing: PA, beige, PC, white
-----------	-------------------------------

Marking:	LN ? DA+ DA-
----------	--------------

Material thickness:	0.5 - 1.2
---------------------	-----------

Contact opening:	With integral cable release
------------------	-----------------------------

Quantity of poles:	5
--------------------	---

Color:	white
--------	-------

Weight:	12
---------	----

Pkg.:	500
-------	-----