



TYS4030220M-10

PHYSICAL DIMENSIONS:

A	4.00	±	0.20
B	4.00	±	0.20
C	3.00		MAX.
D	1.30	±	0.30
E	1.40	±	0.30





RECOMMENDED SOLDERING CONDITIONS




ELECTRICAL SPECIFICATION

	Min	Nom	Max
INDUCTANCE (uH) L @ 100 KHz/1V ± 20%	17.6	22.0	26.4
DCR (Ω)		0.225	0.2925


Saturation Current(A)	1.30	Max.
SRF (MHz)	10	Ref.
Temperature Rise Current (A)	1.00	Max.



CHARACTERISTICS OF TEMPERATURE RISE



CURRENT VS INDUCTANCE DROP IN RATES



RoHS

NOTES:

1. OPERATION TEMPERATURE RANGE: -40°C~+125°C (INCLUDING SELF-HEATING).
2. STORAGE TEMPERATURE RANGE (PACKAGING CONDITIONS): -10°C TO +40°C AND RH 70% (MAX.)
3. UNLESS OTHERWISE SPECIFIED, THE STANDARD ATMOSPHERIC CONDITIONS FOR MEASUREMENT/TEST AS:
A. AMBIENT TEMPERATURE: 20±15°C.
B. RELATIVE HUMIDITY: 65%±20%.
4. SATURATION CURRENT IS THE DC CURRENT AT WHICH THE INDUCTANCE DROPS OFF APPROXIMATELY 30% FROM ITS VALUE WITHOUT CURRENT.(AMBIENT TEMPERATURE 25±5°C)
5. TEMPERATURE RISE CURRENT (IRMS):
DC CURRENT THAT CAUSES THE TEMPERATURE RISE ($\Delta T \leq 40^\circ\text{C}$) FROM 25°C AMBIENT.

DIMENSIONS ARE IN mm .				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
D	CHANGE DIMENSIONS: D/E	07/28/16	QIU	PROJECT/PART NUMBER: TYS4030220M-10			
C	MODIFY "D,E"	4/21/16	QIU				
B	CHANGE LOGO	08/06/15	QIU				
A	ORIGINAL DRAFT	08/07/12	QIU				
REV	DESCRIPTION	DATE	INT				
				DATE:	09/06/12	SCALE:	NTS
				CAD #		TOOL #	-
				SHEET: 1 of 1			

Laird

REV D PART TYPE: POWER INDUCTOR DRAWN BY: QIU

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[TYS4030150M-10](#) [TYS4030220M-10](#)