



TYS6045330M-10

PHYSICAL DIMENSIONS:

A	6.00	± 0.30
B	6.00	± 0.30
C	4.50	MAX.
D	1.55	± 0.30
E	2.90	± 0.30



RECOMMENDED SOLDERING CONDITIONS





ELECTRICAL SPECIFICATION


	Min	Nom	Max
INDUCTANCE (uH) L @ 100 KHz/1V ± 20%	26.4	33.0	39.6
DCR (Ω)		0.137	0.1781

Saturation Current(A)	1.65
SRF (MHz)	7.8
Temperature Rise Current (A)	1.45


RoHS



CHARACTERISTICS OF TEMPERATURE RISE



CURRENT VS INDUCTANCE DROP IN RATES



NOTES: UNLESS OTHERWISE SPECIFIED

1. OPERATING TEMPERATURE RANGE: -40°C TO +125°C (INCLUDING SELF-HEATING) .
2. STORAGE TEMPERATURE RANGE (PACKAGING CONDITIONS): -10°C TO +40°C AND RH 70% (MAX.)
3. UNLESS OTHERWISE SPECIFIED, THE STANDARD ATMOSPHERIC CONDITIONS FOR MEASUREMENT/TEST AS:
A. AMBIENT TEMPERATURE: 20±15°C.
B. RELATIVE HUMIDITY: 65%±20%.
4. DEFINITION OF SATURATION CURRENT (ISAT): DC CURRENT AT WHICH THE INDUCTANCE DROPS ≤30% FROM ITS VALUE WITHOUT CURRENT.
5. DEFINITION OF TEMPERATURE RISE CURRENT (IRMS): DC CURRENT THAT CAUSES THE TEMPERATURE RISE (ΔT ≤40°C) FROM 20°C AMBIENT.

DIMENSIONS ARE IN mm .				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved. 						
PROJECT/PART NUMBER:				REV		PART TYPE:		DRAWN BY:		
TYS6045330M-10				B		POWER INDUCTOR		QIU		
B	CHANGE TEMP FROM -25°C~-+125°C		12/24/12	QIU	DATE: 05/08/12		SCALE: NTS		SHEET:	
A	ORIGINAL DRAFT		05/08/12	QIU	CAD #		TOOL #		1 of 1	
REV	DESCRIPTION		DATE	INT	TYS6045330M-10-B		-			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[TYS6045330M-10](#)