


2.0×1.6mm for Consumer Products/ Mobile Communications



RoHS Compliant

Features

- Crystal unit for Consumer Products
- Ultra-miniature and low profile (2.0×1.6×0.40mm)
- Ceramic package
- Reflow compatible

Applications

- Digital Electronics
- Consumer Products
- Mobile Communications, Bluetooth®, Wireless LAN

* Bluetooth® Trademarks are owned by Bluetooth SIG Inc.

How to Order

CX2016DB 27000 D0 G J CC
① ② ③ ④ ⑤ ⑥ ⑦

① Series

② Frequency

③ Load Capacitance

④ Frequency Tolerance

D0 8 pF **G** ±15×10⁻⁶

⑤ Operating Temp. Range ⑥ Frequency Temp. Stability

EJ -10 to +70°C ±15×10⁻⁶
LJ -30 to +85°C ±15×10⁻⁶

⑦ Individual Specification
(STD Specification is "CC")

Packaging (Tape & Reel 1000/ 3000/ 15000 pcs./ reel)

Specifications

Item	Symbol	Specification		Units	Remarks
Frequency Range	f _{nom}	16000 to 60000		kHz	
Overtone Order	OT	Fundamental		—	
Load Capacitance	CL	8		pF	Please contact us for other Load Capacitance.
Frequency Tolerance	f _{tol}	±15		×10 ⁻⁶	25°C±3°C
Motional Series Resistance	R1	Table 1		ohm	
Drive Level	DL	Table 2		μW	
Operating Temp. Range	T _{use}	-10 to +70	-30 to +85	°C	
Storage Temp. Range	T _{stg}	-40 to +85		°C	
Frequency Temp. Characteristics	f _{tem}	±15		×10 ⁻⁶	Freq. deviation from the value at 25°C

Please contact us for other specifications.

Table1 Motional Series Resistance


Frequency Range	Motional Series Resistance
16000≤f _{nom} <18000kHz	200Ω max.
18000≤f _{nom} <26000kHz	150Ω max.
26000≤f _{nom} <40000kHz	60Ω max.
40000≤f _{nom} ≤60000kHz	50Ω max.

Table2 Level of Drive

Frequency Range	Level of Drive
16000≤f _{nom} ≤60000kHz	10μW (100μW max.)


Dimensions

(Unit: mm)



Recommended Land Pattern

(Unit: mm)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kyocera AVX:](#)

[CX2016DB24000D0GEJZ1](#) [CX2016DB24576D0GEJZ1](#) [CX2016DB27000D0GEJZ1](#) [CX2016DB24576D0GEJCC](#)
[CX2016DB27000D0GEJCC](#) [CX2016DB24000D0GEJCC](#) [CX2016DB16000D0GEJCC](#) [CX2016DB16000D0GLJCC](#)