




FEATURES

- ※Side actuation
- ※Wide stem for easy operation
- ※Gold contact for high reliability


APPLICATION

- ※Industrial control
- ※Automatic machines control
- ※Telecommunication

SPECIFICATION

Contact Rating	25mA, 24V DC
Contact Resistance	100mΩ max.
Insulation Resistance	100MΩ min. 500V DC
Dielectric Strength	500V AC/1 minute
Operating Force	800gf max.
Travel	1mm
Operating Life	2,000 cycles
Operating Temp.	-20°C ~ +85°C
Storage Temp.	-40°C ~ +85°C

CIRCUIT



PACKAGE


<Tube>

NPI(R)/NPM(R)-02: 70 pcs
NPI(R)/NPM(R)-04: 40 pcs
NPI(R)/NPM(R)-06: 28 pcs
NPI(R)/NPM(R)-08: 20 pcs
NPI(R)/NPM(R)-10: 16 pcs



<Tape & Reel>

NPM(R)-02, 04, 06, 08, 10: 700 pcs


HOW TO ORDER




NPI





PART NO.	NO.OF POS.	DIM.A	DIM.B
NPI(R)-02	2	6.48	2.54
NPI(R)-04	4	11.56	7.62
NPI(R)-06	6	16.64	12.70
NPI(R)-08	8	21.72	17.78
NPI(R)-10	10	26.80	22.86



NPM



PART NO.	NO.OF POS.	DIM.A	DIM.B
NPM(R)-02	2	6.48	2.54
NPM(R)-04	4	11.56	7.62
NPM(R)-06	6	16.64	12.70
NPM(R)-08	8	21.72	17.78
NPM(R)-10	10	26.80	22.86



P.C.B. LAYOUT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diptronics:

[NPM-02-V](#) [NPMR-06-V-T/R](#) [NPIR-08-V](#) [NPMR-08-V-T/R](#) [NPM-08-V](#) [NPM-02-V-T/R](#) [NPM-04-V-T/R](#) [NPM-08-V-T/R](#) [NPM-06-V-T/R](#) [NPMR-04-V-T/R](#) [NPMR-10-V-T/R](#) [NPI-02-V](#) [NPMR-02-V-T/R](#) [NPM-10-V-T/R](#) [NPM-06-V](#) [NPIR-06-V](#) [NPI-06-V](#) [NPIR-02-V](#) [NPI-10-V](#) [NPM-04-V](#) [NPM-10-V](#) [NPI-04-V](#) [NPI-08-V](#) [NPIR-10-V](#) [NPIR-04-V](#)