

### FEATURES

- ※ Guiding post offers easy orientation
- ※ 3.80 & 5.30mm stem height available


### APPLICATION

- ※ DSC
- ※ Detection of disc loading

### SPECIFICATION

Contact Rating	1mA, 5V DC
Contact Resistance	1Ω max.
Insulation Resistance	100MΩ min. 100V DC
Dielectric Strength	100V AC/1 minute
Operating Force	40gf max.
Travel	3.9mm max. Stem Height 5.3mm 2.6mm max. Stem Height 3.8mm
Operating Life	100,000 cycles
Operating Temp.	-10°C ~ +60°C
Storage Temp.	-20°C ~ +70°C

### CIRCUIT




### PACKAGE


#### <Tape & Reel>

ATE-1□□: 900 pcs  
ATE-2□K: 900 pcs  
ATE-2□: 1200 pcs


### HOW TO ORDER



### ATE-1



### ATE-2C



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diptronics:

[ATE-2C-V-T/R](#) [ATE-2-V-T/R](#) [ATE-1K-V-T/R](#) [ATE-2K-V-T/R](#) [ATE-1-V-T/R](#) [ATE-1CK-V-T/R](#) [ATE-2CK-V-T/R](#) [ATE-1C-V-T/R](#)