








本公司智慧財產，未經同意不得複製
Diptronics copyright,
may not be used without permission from Diptronics.





Specifications

- Rating : 50 μ A 5V DC/50mA 26V DC
- Initial contact resistance : 100m Ω Max.
- Insulation resistance : 100M Ω Min. 250V DC
- Dielectric strength : 500V AC for 1 minute.
- Operating force : 200 $\pm$ 50gf.
- Operating life : 300,000cycles Min.
- General tolerances $\pm$ 0.4mm

ZONE	REV.	DESCRIPTION	DATE	APPD.
A	REL.DWG		2022.02.07	林后瑞

APPD: 林后瑞	Q' TY:	SCALE: 5:1	UNIT: mm	PART NO: ESH-P4HCQB	MAT' L:	FINISH:
CHKD: 張志瑞	DESIGN: Tai	REV: A	UNIT: mm	PART NO: ESH-P4HCQB	MAT' L:	FINISH:
DIPTRONICS 國達實業股份有限公司 2022.02.10 ISSUED R&D DEPT				PART NAME: Detector Switch		

ITEM	DESC.	Q'TY	MATERIALS	TREATMENT	REMARK
1	COVER	1	HIGH TEMP THERMOPLASTIC	WHITE	—
2	BASE	1	HIGH TEMP THERMOPLASTIC	BLACK	—
3	STEM	1	HIGH TEMP THERMOPLASTIC	BLACK	—
4	ACTION ARM	1	HIGH TEMP THERMOPLASTIC	BLACK	
5	SILICONE CAP	1	SILICONE RUBBER	GREEN	—
6	CONTACT	2	COPPER ALLOY	SILVER PLATING	—
7	TERMINAL	6	BRASS	SILVER PLATING	—
8	SPRING	1	SWP		
9	SPRING	1	SUS304		
10		-	GREASE	WHITE	
11		-	EPOXY	BLACK	



ESH - P 4 H G Q B

Actuator: _____
P = Pin Plunger

Contact Form: _____
4= DPDT

Package Style: _____
B = Tube (Through Hole Type Only)

Q = Halogen Free

Plating: _____
G=Silver Plating

Terminal: _____
H = Through Hole Type

				TITLE: DETCETOR SWITCH (ESH)	APPD. : 
				PROD. NO.: ESH-P4HGQB	CHKD. : 
A	DWG.REL			PR. : Tai	
REV.	ECO. NO.	APPD		FILE NO. : E-V-CT131	REV. : A

表單編號 : S-236

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Diptronics:](#)

[ESH-P4HGQB](#)