




Specification

500ES290	Transceiver
Center Frequency	50.0±1.0KHz
Transmitting Sound Pressure Level at 50.0KHz; 0dB re 20μPa per 300Vac pk-pk, 200Vdc bias at 50 cm	116.0 dB min.
Receiving Sensitivity at 50.0KHz, 200Vdc bias, 0dB = 1 volt/μbar (0dB = 1 volt/Pa)	-65.0 dB (-45.0 dB)
Capacitance at 1KHz ±20%	600 - 700 pF
Suggested DC Bias Voltage	200 V
Suggested AC Driving Voltage	300V pk-pk
Maximum Combined Voltage	400V
Total Beam Angle	-6dB 13° typical
Operation Temperature	0 to 60°C
Standard Finish	
Foil (Diaphragm):	
1. 500ES290-G	Gold
2. 500ES290-A	Aluminum
Housing	ABS


All specification taken typical at 25°C

Dimensions: dimensions are in mm




Transmitting Sound Pressure Level


Tested under 300Vac pk-pk, 200Vdc bias @50 cm



Receiving Sensitivity: Tested under 200Vdc bias



Beam Angle: Tested at 50.0KHz frequency



S. Square Enterprise Company Limited
Pro-Wave Electronics Corporation

[Http://www.pro-wave.com.tw](http://www.pro-wave.com.tw) ; E-mail: sales@pro-wave.com.tw ; Tel: 886-2-22465101 ; Fax: 886-2-22465105

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pro-Wave Electronics:](#)

[500ES290](#)