


Material: UL94 V-2 Nylon 6/6		
Color: Natural		
Part No.	A	
	mm	in
CBLS105A	3.2	.126
CBLS110A	5	.197
CBLS115A	6.3	.248
CBLS120A	8	.315
CBLS125A	10	.394
CBLS130A	12	.472
CBLS135A	14	.551
CBLS140A	16	.630
CBLS145A	18	.709
CBLS150A	25	.984

TO SNAP LOCK IN A 3.5 (.137) Ø HOLE, IN
A 1.2 - 1.7 (.047 - .067) PANEL THICKNESS



TO SNAP LOCK IN A 4.8 (.187) Ø HOLE, IN
A 0.8 - 2.2 (.031 - .086) PANEL THICKNESS

TOLERANCES
UNLESS NOTED
≤ 5 mm ±0.2
5 - 20 mm ±0.3
20 - 40 mm ±0.4
40 - 60 mm ±0.5
60 - 100 mm ±0.8
≥ 100 mm ±1.0

TITLE: DUAL LOCKING CIRCUIT BOARD SUPPORT				DWG IN MM (IN)	PRINT TYPE CA
	FILE: CBLS1XX	DWN: CLC		PART #	
	SHEET: 1 OF 1	SHEET SIZE: A	DT: 01/08/15		
	RE:				
	 ESSENTRA COMPONENTS			SEE TABLE	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[CBLS150A](#) [CBLS105A](#) [CBLS110A](#) [CBLS115A](#) [CBLS120A](#) [CBLS125A](#) [CBLS130A](#) [CBLS135A](#) [CBLS140A](#)
[CBLS145A](#)