


TO SNAP LOCK IN A 4 (.156) Ø HOLE, IN A
1.6 - 1.8 (.062 - .071) PANEL THICKNESS



TO SNAP LOCK IN A 4.8 (.187) Ø HOLE, IN A
0.8 - 2.2 (.031 - .087) PANEL THICKNESS

Material: UL94 V-2 Nylon 6/6		
Color: Natural		
Part No.	A	
	mm	in
CBDLS305A	4	.157
CBDLS310A	5	.197
CBDLS315A	6.4	.252
CBDLS320A	7	.276
CBDLS325A	9.5	.374
CBDLS330A	10	.394
CBDLS335A	12.7	.500
CBDLS340A	15.9	.626
CBDLS345A	19	.748
CBDLS350A	20	.787
CBDLS355A	22	.866
CBDLS360A	25.4	1.000
CBDLS365A	28.6	1.126
CBDLS370A	30	1.181
CBDLS375A	35	1.378
CBDLS380A	38	1.496
CBDLS385A	45	1.772

TOLERANCES
UNLESS NOTED

≤ 5 mm	±0.2
5 - 20 mm	±0.3
20 - 40 mm	±0.4
40 - 60 mm	±0.5
60 - 100 mm	±0.8
≥ 100 mm	±1.0

TITLE: DUAL LOCKING CIRCUIT BOARD SUPPORT						DWG IN MM (IN)	
	FILE #:CBDLS		DWN: CLC		PART #	PRINT TYPE	
	SHEET: 1 OF 1	SHEET SIZE: A	DT: 01/08/15				
	RE:		 ESSENTRA COMPONENTS				
					SEE TABLE		CA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[CBDLS345A](#) [CBDLS360A](#) [CBDLS315A](#) [CBDLS330A](#) [CBDLS375A](#) [CBDLS350A](#) [CBDLS305A](#) [CBDLS335A](#)
[CBDLS365A](#) [CBDLS310A](#) [CBDLS320A](#) [CBDLS380A](#) [CBDLS370A](#) [CBDLS355A](#) [CBDLS385A](#) [CBDLS340A](#)
[CBDLS325A](#)