




NOTES:
1. MATERIAL: NYLON 6/6 UL94 V-2 (RMS-01).
NYLON 6/6 UL 94 V-0 (RMS-19) AVAILABLE BY SPECIAL ORDER.
UV STABILIZED NYLON (RMS-46) AVAILABLE BY SPECIAL ORDER ONLY.
COLOR, BLACK. TO ORDER ADD "-UVB" TO THE END OF PART NO.
2. COLOR: BLACK.
NATURAL BY SPECIAL ORDER

C	SEE CO 200370 FOR CHANGES	SK	05/26/09
B	SEE ECN # 917 FOR CHANGES	SK	01/18/05
A	RELEASED FOR PRODUCTION	SM	10/19/04
REV.	DESCRIPTION	ENGR.	DATE

PART NO.	HOLE DIAMETER ±.003 [0.08]	HEAD DIAMETER	SUGGESTED TOTAL BOARD THICKNESS	HEAD HEIGHT	LENGTH
RBF-4-8.6-8	.157(4.00)	.32(8.0)	.08-.17(2.1-4.3)	.04(1.0)	.34(8.6)
RBF-4-11.1-8			.08-.28(2.1-7.2)		.44(11.1)
RBF-4-15-8			.22-.42(5.7-10.7)		.59(15.0)
RBF-4-8.6-12		.47(12.0)	.08-.17(2.1-4.3)	.06(1.5)	.34(8.6)
RBF-4-11.1-12			.08-.28(2.1-7.2)		.44(11.1)
RBF-4-15-12			.22-.42(5.7-10.7)		.59(15.0)
RBF-4-8.6-16		.63(16.0)	.08-.17(2.1-4.3)	.08(2.0)	.34(8.6)
RBF-4-11.1-16			.08-.28(2.1-7.2)		.44(11.1)
RBF-4-15-16			.22-.42(5.7-10.7)		.59(15.0)
RBF-4.8-8.6-8	.188(4.76)	.32(8.0)	.08-.17(2.1-4.3)	.04(1.0)	.34(8.6)
RBF-4.8-11.1-8			.08-.28(2.1-7.2)		.44(11.1)
RBF-4.8-15-8			.22-.42(5.7-10.7)		.59(15.0)
RBF-4.8-8.6-12		.47(12.0)	.08-.17(2.1-4.3)	.06(1.5)	.34(8.6)
RBF-4.8-11.1-12			.08-.28(2.1-7.2)		.44(11.1)
RBF-4.8-15-12			.22-.42(5.7-10.7)		.59(15.0)
RBF-4.8-8.6-16		.63(16.0)	.08-.17(2.1-4.3)	.08(2.0)	.34(8.6)
RBF-4.8-11.1-16			.08-.28(2.1-7.2)		.44(11.1)
RBF-4.8-15-16			.22-.42(5.7-10.7)		.59(15.0)
RBF-6.4-8.6-8	*.250(6.35)	.32(8.0)	.08-.17(2.1-4.3)	.04(1.0)	.34(8.6)
RBF-6.4-11.1-8			.08-.28(2.1-7.2)		.44(11.1)
RBF-6.4-15-8			.22-.42(5.7-10.7)		.59(15.0)
RBF-6.4-8.6-12		.47(12.0)	.08-.17(2.1-4.3)	.06(1.5)	.34(8.6)
RBF-6.4-11.1-12			.08-.28(2.1-7.2)		.44(11.1)
RBF-6.4-15-12			.22-.42(5.7-10.7)		.59(15.0)
RBF-6.4-8.6-16		.63(16.0)	.08-.17(2.1-4.3)	.08(2.0)	.34(8.6)
RBF-6.4-11.1-16			.08-.28(2.1-7.2)		.44(11.1)
RBF-6.4-15-16			.22-.42(5.7-10.7)		.59(15.0)
RBF-7.1-11.1-8	*.281(7.14)	.32(8.0)	.08-.28(2.1-7.2)	.04(1.0)	.44(11.1)
RBF-7.1-15-8			.15-.42(3.8-10.7)		.59(15.0)
RBF-7.1-19-8			.27-.56(6.9-14.2)		.75(19.0)
RBF-7.1-11.1-12		.47(12.0)	.08-.28(2.1-7.2)	.06(1.5)	.44(11.1)
RBF-7.1-15-12			.15-.42(3.8-10.7)		.59(15.0)
RBF-7.1-19-12			.27-.56(6.9-14.2)		.75(19.0)
RBF-7.1-11.1-16		.63(16.0)	.08-.28(2.1-7.2)	.08(2.0)	.44(11.1)
RBF-7.1-15-16			.15-.42(3.8-10.7)		.59(15.0)
RBF-7.1-19-16			.27-.56(6.9-14.2)		.75(19.0)

* FOR USE IN METAL, LEADING EDGE OF HOLE MUST BE BROKE

TITLE: BARBED PUSH FASTENER						DWG IN IN [MM]	
CREATED USING SOLIDWORKS	FILE #: RBF		DWN: D.J.Z.	APP: DJZ		FINAL	
TOLERANCES UNLESS NOTED .XX=±.01 .XXX=±.005 FRAC.=±1/64 ANG.=±1°	SHEET: 1 OF 1		SHEET SIZE: B		DT: 06/09/2004	CHKD: SJ	PART #
RE: RICHCO INC.		RICHCO, INC.		ENG@RICHCO-INC.COM (773) 539-4060		SEE TABLE	
		--				PRINT TYPE CA	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[RBF-4-8.6-8](#) [RBF-4-11.1-8](#) [RBF-4-15-8](#)