

PDZ-GW series Single Zener diodes in a SOD123 package Rev. 1 — 4 September 2017

Product data sheet

Product profile 1

1.1 General description

General-purpose Zener diodes in a SOD123 small Surface-Mounted Device (SMD) plastic package.

1.2 Features and benefits

- Non-repetitive peak reverse power dissipation: P_{ZSM} ≤ 40 W
- Total power dissipation: P_{tot} ≤ 365 mW
- Tolerance series:
 - B2: approximately ± 2 %
- Wide working voltage range: nominal 2.4 V to 36 V (E24 range)
- Low reverse current I_R range
- · Small plastic package suitable for surface-mounted design
- AEC-Q101 gualified

1.3 Applications

· General regulation functions

1.4 Quick reference data

Table 1. Quick reference data

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V _F	forward voltage	I _F = 10 mA ^[1]	-	-	0.9	V
P _{tot}	total power dissipation	$T_{amb} \le 25 \ ^{\circ}C$ ^[2]	-	-	365	mW
		[3]	-	-	625	mW

[1] Pulse test: $t_p \le 300 \ \mu s$; $\delta \le 0.02$.

[2] Device mounted on an FR4 Printed-Circuit Board (PCB), single-sided copper, tin-plated and standard footprint.

[3] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for cathode 1 cm²



Single Zener diodes in a SOD123 package

2 Pinning information

Table 2. Pinning

Pin	Symbol	Description	Simplified outline	Graphic symbol
1	К	cathode ^[1]		
2	A	anode	12	1 2 006aaa152

[1] The marking bar indicates the cathode.

3 Ordering information

Table 3. Ordering information

Type number	Package					
	Name	Description	Version			
PDZ2.4BGW to PDZ36BGW ^[1]	-	plastic surface-mounted package; 2 leads	SOD123			

[1] The series consists of 29 types with nominal working voltages from 2.4 V to 36 V.

4 Marking

Table 4. Marking Codes

Type number	Marking Code	Type number	Marking Code	Type number	Marking Code
PDZ2.4BGW	B1	PDZ6.2BGW	BB	PDZ16BGW	BM
PDZ2.7BGW	B2	PDZ6.8BGW	BC	PDZ18BGW	BN
PDZ3.0BGW	B3	PDZ7.5BGW	BD	PDZ20BGW	BP
PDZ3.3BGW	B4	PDZ8.2BGW	BE	PDZ22BGW	BQ
PDZ3.6BGW	B5	PDZ9.1BGW	BF	PDZ24BGW	BR
PDZ3.9BGW	B6	PDZ10BGW	BG	PDZ27BGW	BS
PDZ4.3BGW	B7	PDZ11BGW	BH	PDZ30BGW	BT
PDZ4.7BGW	B8	PDZ12BGW	BJ	PDZ33BGW	BU
PDZ5.1BGW	B9	PDZ13BGW	ВК	PDZ36BGW	BV
PDZ5.6BGW	BA	PDZ15BGW	BL		

Single Zener diodes in a SOD123 package

Limiting values 5

Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions		Min	Max	Unit
I _F	forward current			-	200	mA
I _{ZSM}	non-repetitive peak reverse current			-	see charac table	teristics
P _{ZSM}	non-repetitive peak power dissipation		[1]	-	40	W
P _{tot}	total power dissipation	T _{amb} ≤ 25 °C	[2]	-	365	mW
			[3]	-	625	mW
Т _ј	junction temperature			-	150	
T _{amb}	ambient temperature			-55	+150	°C
T _{stg}	storage temperature			-65	+150	°C

[1] $t_p = 100 \ \mu s$; square wave; $T_j = 25 \ ^{\circ}C$ prior to surge. [2] Device mounted on an FR4 PCB, single-sided copper, tin-plated and standard footprint.

[2] Device mounted on an FR4 PCB, single-sided copper, tin-plated and standard footprint.
 [3] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for cathode 1 cm².

Thermal characteristics 6

Table 6. Thermal characteristics

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
R _{th(j-a)}	thermal resistance from junction	in free air ^[1]	-	-	340	K/W
to ambient		[2]	-	-	200	K/W
R _{th(j-sp)}	thermal resistance from junction to solder point	[3]	-	-	50	K/W

[1] Device mounted on an FR4 Printed-Circuit Board (PCB), single-sided copper, tin-plated and standard footprint.

[2] [3] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for cathode 1 cm²

Soldering point of cathode tab.

Characteristics 7

Table 7. Characteristics

 $T_i = 25 \text{ °C}$ unless otherwise specified.

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
V _F	forward voltage	I _F = 10 mA	[1]	-	-	0.9	V
V _F	forward voltage	I _F = 100 mA	[1]	-	-	1.1	V

[1] Pulse test: $t_p \le 300 \ \mu s$; $\delta \le 0.02$.

Single Zener diodes in a SOD123 package

Table 8. Characteristics per type; PDZ2.4BGW to PDZ36BGW

 $T_i = 25$ °C unless otherwise specified.

PDZx BGW	Sel	Worki voltag V _Z (V) I _Z = 5 r	je ;	Maximum differential resistance r _{dif} (Ω)		Revers current I _R (μΑ)		Temperature coefficient S _Z (mV/K); I _Z = 5 mA	Diode capacitance C _d (pF) ^[1]	Non- repetitive peak reverse current I _{ZSM} (A) ^[2]
		Min	Max	l _Z = 0.5 mA	l _Z = 5 mA	Max	V _R (V)	Тур	Мах	Мах
2.4	В	2.43	2.63	1000	100	50	1.0	-1.6	450	8.0
2.7	В	2.69	2.91	1000	100	20	1.0	-2.0	440	8.0
3.0	В	2.85	3.07	1000	95	10	1.0	-2.1	425	8.0
3.3	В	3.32	3.53	1000	95	5	1.0	-2.4	410	8.0
3.6	В	3.60	3.85	500 @ 1 mA	90	5	1.0	-2.4	390	8.0
3.9	В	3.89	4.16	500 @ 1 mA	90	3	1.0	-2.5	370	8.0
4.3	В	4.17	4.48	600 @ 1 mA	90	3	1.0	-2.5	350	8.0
4.7	В	4.55	4.75	600 @ 1 mA	90	2	1.0	-1.4	325	8.0
5.1	В	4.96	5.20	250	60	2	1.5	0.3	300	5.5
5.6	В	5.48	5.73	100	50	1	2.5	1.9	275	5.5
6.2	В	6.06	6.33	80	50	0.5	3.0	2.7	250	5.5
6.8	В	6.65	6.93	60	40	0.5	3.5	3.4	215	5.5
7.5	В	7.28	7.60	60	10	0.5	4.0	4.0	170	3.5
8.2	В	8.02	8.36	60	10	0.5	5.0	4.6	150	3.5
9.1	В	8.85	9.23	60	10	0.5	6.0	5.5	120	3.5
10	В	9.77	10.21	60	10	0.1	7.0	6.4	110	3.5
11	В	10.78	11.22	60	10	0.1	8.0	7.4	108	3.0
12	В	11.74	12.24	80	10	0.1	9.0	8.4	105	3.0
13	В	12.91	13.49	80	10	0.1	10.0	9.4	103	2.5
15	В	14.34	14.98	80	15	0.05	11.0	11.4	99	2.0
16	В	15.85	16.51	80	20	0.05	12.0	12.4	97	1.5
18	В	17.56	18.35	80	20	0.05	13.0	14.4	93	1.5
20	В	19.52	20.39	100	20	0.05	15.0	16.4	88	1.5
22	В	21.54	22.47	100	25	0.05	17.0	18.4	84	1.3
24	В	23.72	24.78	120	30	0.05	19.0	20.4	80	1.3

PDZ-GW_SER


© Nexperia B.V. 2017. All rights reserved.

PDZ-GW series

Single Zener diodes in a SOD123 package


PDZx BGW	Sel	Worki voltag V _Z (V) I _Z = 5 r	e ;	Maximum differential resistance r _{dif} (Ω)		Revers current I _R (μΑ)		Temperature coefficient S _Z (mV/K); I _Z = 5 mA	Diode capacitance C _d (pF) ^[1]	Non- repetitive peak reverse current I _{ZSM} (A) ^[2]
		Min	Мах	l _Z = 0.5 mA	I _Z = 5 mA	Мах	V _R (V)	Тур	Max	Max
27	В	26.19	27.53	150	40	0.05	21.0	23.4	73	1.0
30	В	29.19	30.69	200	40	0.05	23.0	26.6	66	1.0
33	В	32.15	33.79	250	40	0.05	25.0	29.7	60	0.9
36	В	35.07	36.87	300	60	0.05	27.0	33.0	59	0.8

[1] f = 1 MHz; $V_R = 0 V$. [2] $t_p = 100 \ \mu s$; $T_{amb} = 25 \ ^{\circ}C$.




PDZ-GW series

Single Zener diodes in a SOD123 package




PDZ2.4BGW to PDZ4.3BGW $T_i = 25 \degree C$ to 150 $\degree C$






PDZ2.4BGW to PDZ4.3BGW T_j = 25 °C

Figure 5. Working current as a function of working voltage; typical values



PDZ4.7BGW to PDZ12BGW T_i = 25 °C to 150 °C

Figure 4. Temperature coefficient as a function of working current; typical values




PDZ4.7BGW to PDZ12BGW T_i = 25 °C

Figure 6. Working current as a function of working voltage; typical values

PDZ-GW series

Single Zener diodes in a SOD123 package




8 Test information

8.1 Quality information

This product has been qualified in accordance with the Automotive Electronics Council (AEC) standard Q101 - Stress test qualification for discrete semiconductors, and is suitable for use in automotive applications.


9 Package outline



PDZ-GW_SER Product data sheet

Single Zener diodes in a SOD123 package

10 Soldering



Single Zener diodes in a SOD123 package

11 Revision history

Table 9. Revision history				
Document ID	Release date	Data sheet status	Change notice	Supersedes
PDZ-GW_SER v.1	20170904	Product data sheet	-	-

Single Zener diodes in a SOD123 package

12 Legal information

12.1 Data sheet status

Document status ^{[1][2]}	Product status ^[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

Please consult the most recently issued document before initiating or completing a design. [1]

The term 'short data sheet' is explained in section "Definitions".

[2] [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nexperia.com.

12.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification - The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

12.3 Disclaimers

Limited warranty and liability - Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia. In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory. Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia

Right to make changes - Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use - Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification. Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products. Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale - Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nexperia.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer

No offer to sell or license - Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Single Zener diodes in a SOD123 package

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications. In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer

design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

12.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

PDZ-GW series

Single Zener diodes in a SOD123 package

Contents

1	Product profile	
1.1	General description	1
1.2	Features and benefits	1
1.3	Applications	1
1.4	Quick reference data	1
2	Pinning information	2
3	Ordering information	2
4	Marking	2
5	Limiting values	3
6	Thermal characteristics	3
7	Characteristics	3
8	Test information	7
8.1	Quality information	7
9	Package outline	7
10	Soldering	8
11	Revision history	9
12	Legal information	

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© Nexperia B.V. 2017.

All rights reserved.

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com

Date of release: 4 September 2017 Document identifier: PDZ-GW_SER

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Nexperia:

PDZ10BGWX PDZ12BGWJ PDZ15BGWX PDZ16BGWJ PDZ18BGWJ PDZ3.9BGWX PDZ4.7BGWJ PDZ5.1BGWX PDZ5.6BGWJ PDZ6.2BGWX PDZ2.4BGWX PDZ16BGWX PDZ36BGWX PDZ33BGWJ PDZ20BGWJ PDZ11BGWJ PDZ27BGWX PDZ3.3BGWJ PDZ12BGWX PDZ5.6BGWX PDZ6.2BGWJ PDZ7.5BGWJ PDZ27BGWJ PDZ6.8BGWJ PDZ3.6BGWX PDZ3.0BGWX PDZ2.7BGWX PDZ7.5BGWX PDZ24BGWX PDZ13BGWX PDZ2.4BGWJ PDZ36BGWJ PDZ20BGWX PDZ2.7BGWJ PDZ22BGWJ PDZ30BGWX PDZ9.1BGWJ PDZ4.7BGWX PDZ10BGWJ PDZ36BGWX PDZ4.3BGWJ PDZ24BGWJ PDZ4.3BGWX PDZ30BGWJ PDZ5.1BGWJ PDZ15BGWJ PDZ22BGWX PDZ13BGWJ PDZ3.0BGWJ PDZ3.6BGWJ PDZ8.2BGWX PDZ18BGWX PDZ9.1BGWX PDZ6.8BGWX PDZ3.3BGWX PDZ3.3BGWX PDZ3.0BGWJ PDZ3.0BGWJ