

› Logic Controller Millenium Evo

- › Up to 44 I/Os - 16 DI (4 HighSpeed / 8 AI) - 8 DO
- › Wireless programming & Control with bluetooth Interface and Crouzet Virtual Display
- › Modbus RTU Network (Slave)
- › Local datalog management
- › Up to 1000 programing blocks with intuitive Crouzet Soft to go from simple to complex applications



XBP24
Base 24 I/O



XBP24-E
Base 24 I/O Ethernet



XDP24
Base 24 I/O



XDP24-E
Base 24 I/O Ethernet

Product selection		
LCD display	Ethernet network	Part number
No	No	88 975 001
No	Yes	88 975 011
Yes	No	88 975 101
Yes	Yes	88 975 111

Product selection KIT	
Bluetooth Kit (Millenium EVO Ethernet 88 975 111, Bluetooth interface 88 980 112, Bluetooth receiver 88 980 116)	88 975 911
Bluetooth Kit (Millenium EVO Standalone 88 975 101, Bluetooth interface 88 980 112, Bluetooth receiver 88 980 116)	88 975 901

	XBP24	XBP24-E	XDP24	XDP24-E
General characteristics				
Part number	88 975 001	88 975 011	88 975 101	88 975 111
Products certification	CE, cULus Listed			
Conformity with the low voltage directive (in accordance with 2014/35/EU)	IEC/EN 61131-2 (Open equipment)			
Conformity with the EMC directive (in accordance with 2014/30/EU)	IEC/EN 61000-6-1 (Residential, commercial and light-industrial environments) IEC/EN 61000-6-2 (Industrial) IEC/EN 61000-6-3 (Residential, commercial and light-industrial environments) IEC/EN 61000-6-4 (Industrial)			
Power supply earthing	None			
Overvoltage category	3 in accordance with IEC/EN 60664-1			
Pollution	Degree : 2 in accordance with IEC/EN 61131-2			
Maximum utilization altitude	Operation: 2000 m Transport: 3000 m			
Mechanical resistance	Immunity to vibrations IEC/EN 60068-2-6, Fc test Immunity to shock IEC/EN 60068-2-27, Ea test			
Resistance to electrostatic discharge	Immunity to ESD IEC/EN 61000-4-2, level 3			
Resistance to HF interference (Immunity)	Immunity to radiated electrostatic fields IEC/EN 61000-4-3, level 3 Immunity to fast transients (burst immunity) IEC/EN 61000-4-4, level 3 Immunity to shock waves IEC/EN 61000-4-5 Radio frequency in common mode IEC/EN 61000-4-6, level 3			
Conducted and radiated emissions (in accordance with EN 55022/11 group 1)	Class B			
Operation temperature	-20 °C (-4 °F) → +60 °C (140 °F) (+40 °C (104 °F) in a non-ventilated enclosure) UL: maximum surrounding air: +50 °C (122 °F)			

Standard product

Product made to order

Contact us

	XBP24	XBP24-E	XDP24	XDP24-E
Storage temperature	-40°C (-40 °F) → +80°C (176 °F)			
Relative humidity	95% max. (no condensation or dripping water)			
Screw terminals connection capacity	Flexible wire with ferrule: 1 conductor: 0.2 to 2.5 mm ² (AWG 24-14) Flexible wire with ferrule: 2 conductors: 0.2 to 0.75 mm ² (AWG 24-18) Rigid wire: 1 conductor: 0.2 to 2.5 mm ² (AWG 24-14) Rigid wire: 2 conductors: 0.2 to 0.75 mm ² (AWG 24-18) Tightening torque: 0.5 N.m (4.5 lb-in) (tighten using screwdriver diam. 3.5 mm) Stripping length: 6 mm			
Material	Lexan, UL94V0			
Environnement	Reach, RoHS, Halogen free 1272/2008/CE			
On front panel color	Grey RAL 7035			
On sole color	Black RAL 9011			
Protection rating (in accordance with IEC/EN 60529)	IP 40 on front panel IP 20 on terminal block			
Weight	Without packing: 270 g With packing: 320 g	Without packing: 300 g With packing: 350 g		Without packing: 330 g With packing: 380 g
Dimensions	Without packing: 124.6 x 90 x 61.1 mm / 4.91 x 3.54 x 2.4 inch With packing: 148 x 103 x 65 mm / 5.83 x 4.06 x 2.56 inch		Without packing: 124.6 x 90 x 62 mm / 4.91 x 3.54 x 2.44 inch With packing: 148 x 103 x 65 mm / 5.83 x 4.06 x 2.56 inch	

Processing characteristics				
LCD display	Without		Display with 4 lines of 18 characters, yellow/green	
Programming method	FBD (Function Block Diagram), including SFC (Sequential Function Chart) (Grafcet)			
Program size	Function blocks: typically 512 blocks Macro blocks: 127 max. (255 blocks per macro)			
Program memory	Flash			
Removable memory	N.A			
Data memory	2 k octets			
Back-up time (in the event of power failure)	Program and settings in the controller: 10 years Data memory: 10 years			
Data back-up	Data backup in the flash memory is guaranteed if the product is powered on more than 10 seconds			
Cycle time	From 2 ms* to 90 ms, default value: 10 ms *: Depending on configuration			
Clock data retention	10 years (lithium battery) at 25°C (77°F)			
Clock drift	Drift < 12 min/year (at 25°C (77°F)) 6 s / month (at 25°C (77°F) with user-definable correction of drift). Synchronizable by network			
Timer block accuracy	0.5 % ± 2 cycle time			
Start up time on power up	< 8 s base alone, < 5 s base + 2 expansions + 1 accessory (RS485)	< 10 s base alone, < 5 s base + 2 expansions + 1 accessory (RS485)	< 8 s base alone, < 5 s base + 2 expansions + 1 accessory (RS485)	< 10 s base alone, < 5 s base + 2 expansions + 1 accessory (RS485)
Self test	Test firmware integrity (checksum memory) Stability of the internal power supply Check the conformity of the em4 device configuration with the configuration in the application program.			

Supply				
Nominal voltage	24 VDC (-15% / +20%)			
Operating limits	20.4 - 28.8 VDC			
Immunity from micro power cuts	≤ 1 ms (repetition 20 times)			
Max. absorbed power	3.8 W @ 24 VDC, 5 W @ 28.8 VDC, 1.5 W @ 24 VDC I/O OFF	4.8W @ 24 VDC, 6.2 W @ 28.8 VDC, 1.5W @ 24 VDC I/O OFF	4W @ 24 VDC, 5.3 W @ 28.8 VDC, - 0.3 W backlight OFF 1.5W @ 24 VDC (I/O + backlight) OFF	5W @ 24 VDC, 6.5 W @ 28.8 VDC, - 0.3 W backlight OFF 1.5W @ 24 VDC (I/O + backlight) OFF

	XBP24	XBP24-E	XDP24	XDP24-E
Protection against polarity inversions	Yes			
Power monitoring	Yes and value available through the application «FB Status», 1/10V, 5%.			
Inputs				
Digital and high speed digital inputs 24 VDC - 4 inputs from I1 to I4				
Input used as digital input				
Input voltage	24 VDC (-15% / +20%)			
Input current	1.8 mA @ 20.4 V 2.1 mA @ 24 V 2.5 mA @ 28.8 V			
Input impedance	11.6 kΩ			
Logic 1 voltage threshold	≥ 15 VDC			
Making current at logic state 1	≥ 1.3 mA			
Logic 0 voltage threshold	≤ 10 VDC			
Release current at logic state 0	≤ 0.8 mA			
Response time	1 to 2 cycle times			
Sensor type	Contact or 3-wire PNP			
Conforming to IEC/EN 61131-2	Type 1			
Input type	Resistive			
Isolation between power supply and inputs	None			
Isolation between inputs	None			
Protection against polarity inversions	Yes			
Status indicator	No		On LCD screen	
Cable length	≤ 100 m			
Input used as high speed digital input				
Maximum counting frequency	3 channels encoder (I1, I2, I3): 5 kHz* 2 independent counters (I1, I2) (I3, I4) (Cumul, IND, DIR): 2 channels: 10 kHz*, 4 channels: 5 kHz*, 2 independent counters (I1, I2) (I3, I4) (PH, PH2): 2/4 channels: 5 kHz* 4 independent counters (I1, I2, I3, I4) (Up/Down) : 1 channel: 15 kHz*, 2 channels: 10 kHz*, > 2 channels: 5 kHz* * with a time cycle ≤ 10 ms and a ton / toff = 50% ± 5%, level 0 < 2V and level 1 > 20,4V			
Other functions	4 tachometers (I1, I2, I3, I4)			
Cable length	≤ 3 m with shielded twisted cable			
Digital 24 VDC and analog inputs 12 bits / 28.8 V - potentiometer - 8 inputs from I5 to IC				
Input used as digital input				
Input voltage	24 VDC (-15% / +20%)			
Input current	1.8 mA @ 20.4 V 2.1 mA @ 24 V 2.5 mA @ 28.8 V			
Input impedance	11.6 kΩ			
Logic 1 voltage threshold	≥ 11 VDC			
Making current at logic state 1	≥ 1 mA			
Logic 0 voltage threshold	≤ 9 VDC			
Release current at logic state 0	≤ 0.7 mA			
Response time	1 to 2 cycle times			
Sensor type	Contact or 3-wire PNP			
Conforming to IEC/EN 61131-2	Type 1			
Input type	Resistive			
Isolation between power supply and inputs	None			
Isolation between inputs	None			
Protection against polarity inversions	Yes			

	XBP24	XBP24-E	XDP24	XDP24-E
Status indicator	No		On LCD screen	
Cable length	≤ 30 m			
Input used as analog input				
Measuring range	0 → 10 V, 0 → V power supply or Voltmeter			
Input impedance	11.6 kΩ			
Maximum value without destruction	28.8 VDC max			
Input type	Common mode			
Resolution	12 bit at maximum input voltage (10 bit at 10V)			
Value of LSB	7.03 mV			
Conversion time	Controller cycle time			
Maximum error in 0-10V mode	± 3.5 % of full scale at 25°C (77°F) ± 5 % of full scale at 55°C (131°F)			
Maximum error in 0-V power supply mode	± 5 % of full scale at 25°C (77°F) ± 6.2 % of full scale at 55°C (131°F)			
Repeat accuracy at 55°C (131°F)	± 2 %			
Voltmeter	From 0 to 30.5 V, 5%			
Isolation between analogue channel and power supply	None			
Protection against polarity inversions	Yes			
Potentiometer control	2.2 kΩ / 0.5 W (recommended), 10 KΩ max.			
Cable length	≤ 10 m with shielded twisted cable (sensor not isolated)			
Digital 24 VDC - 4 inputs from ID to IG				
Input voltage	24 VDC (-15% / +20%)			
Input current	1.5 mA @ 20.4 V 1.7 mA @ 24 V 2.1 mA @ 28.8 V			
Input impedance	13.9 kΩ			
Logic 1 voltage threshold	≥ 11 VDC			
Making current at logic state 1	≥ 0.8 mA			
Logic 0 voltage threshold	≤ 8 VDC			
Release current at logic state 0	≤ 0.5 mA			
Response time	1 to 2 cycle times			
Sensor type	Contact or 3-wire PNP			
Conforming to IEC/EN 61131-2	Type 1			
Input type	Resistive			
Isolation between power supply and inputs	None			
Isolation between inputs	None			
Protection against polarity inversions	No			
Status indicator	No		On LCD screen	
Cable length	≤ 30 m			
Outputs				
6 A relay output - 2 outputs from O1 to O2				
Breaking voltage	250 VAC max			
Breaking current	6 A Derating: UL: ≥ 45°C (113°F): 4A max			
Maximum breaking current in the common	IEC @ 25°C (77 °F): 12 A IEC @ 60°C (140 °F) or UL: 10 A			
Mechanical life	5 000 000 operations (cycles)			

	XBP24	XBP24-E	XDP24	XDP24-E
Electrical durability for 50 000 operating cycles	24 VDC tau = 0 ms: 6 A, tau = 7 ms: 3 A, tau = 15 ms: 1.8 A Usage category DC-12: 24 V, 6 A Usage category DC-14: 24 V, 1.8 A 250 VAC cos phi = 1: 6 A, cos phi = 0.7: 5 A, cos phi = 0.4: 2.5 A Usage category AC-12: 250 V, 6 A Usage category AC-13: 250 V, 5 A Usage category AC-15: 250 V, 2 A			
Minimum switching capacity	100 mA (at minimum voltage of 12V)			
Maximum operating rate	Off load: 10 Hz At operating current: 0.1 Hz			
Voltage for withstanding shocks	In accordance with IEC/EN 60947-1 and IEC/EN 60664-1: 4 kV			
Response time	Make = 1 cycle time + 8 ms typical Release = 1 cycle time + 4 ms typical			
Built-in protections	Against short-circuits: None Against over voltages and overload: None			
Status indicator	No		On LCD screen	
Cable length	≤ 30 m			

8 A relay output - 6 outputs from O3 to O8

Breaking voltage	250 VAC max	
Breaking current	8 A Derating: CEI ≥ 55°C (131°F) or UL: ≥ 45°C (113°F): 6A max	
Maximum breaking current in the common	IEC @ 25°C (77°F): C3, C6: 8A ; C4, C5: 16 A IEC @ 60°C (140 °F) or UL: C3, C6: 8 A ; C4, C5: 10 A	
Mechanical life	20 000 000 operations (cycles)	
Electrical durability for 50 000 operating cycles	24 VDC tau = 0 ms: 8 A, tau = 7 ms: 3 A, tau = 15 ms: 1.5 A Usage category DC-12: 24 V, 8 A Usage category DC-14: 24 V, 1.5 A 250 VAC cos phi = 1: 8 A, cos phi = 0.7: 4.75 A, cos phi = 0.4: 3 A Usage category AC-12: 250 V, 8 A Usage category AC-13: 250 V, 4.3 A Usage category AC-15: 250 V, 1.5 A	
Minimum switching capacity	100 mA (at minimum voltage of 12V)	
Maximum operating rate	Off load: 10 Hz At operating current: 0.1 Hz	
Voltage for withstanding shocks	In accordance with IEC/EN 60947-1 and IEC/EN 60664-1: 4 kV	
Response time	Make = 1 cycle time + 10 ms typical Release = 1 cycle time + 5 ms typical	
Built-in protections	Against short-circuits: None Against over voltages and overload: None	
Status indicator	No	On LCD screen
Cable length	≤ 30 m	



Ethernet network

Programming / exploitation	-	USB & Ethernet port / Ethernet port	-	USB & Ethernet port / Ethernet port
Ethernet connection	-	Type RJ45, 10/100 Mbit/s, MDI/MDIX	-	Type RJ45, 10/100 Mbit/s, MDI/MDIX
Adressage	-	Static or dynamic (DHCP server / Auto IP)	-	Static or dynamic (DHCP server / Auto IP)
Protocols	-	Modbus TCP (client / server), Discovery, UDP, TCP, SMTP, SSL (workshop communication via Ethernet)	-	Modbus TCP (client / server), Discovery, UDP, TCP, SMTP, SSL (workshop communication via Ethernet)
Cable length	-	Maximun length between 2 devices: 100 m / 3937 inch	-	Maximun length between 2 devices: 100 m / 3937 inch

	XBP24	XBP24-E	XDP24	XDP24-E
Ethernet earthing	-	Yes, refer to the quick reference guide supplied with the product	-	Yes, refer to the quick reference guide supplied with the product

Technical sketches


Dimensions (mm)

Version	XBP24	XBP24-E	XDP24	XDP24-E
				


Connections

INPUTS


I1 ... IG 0/1




PNP




I5 ... IC U




30 V, NTC, LDR, R




I1 ... I4




Hz




I1 ... I4




Hz





I1 ... I4



Hz, Rpm



OUTPUTS



Warning:

The product information contained in this catalogue is given purely as information and does not constitute a representation, warranty or any form of contractual commitment. Crouzet Automatismes SAS and its subsidiaries reserve the right to modify their products without notice. It is imperative that we should be consulted over any particular use or application of our products and it is the responsibility of the buyer to establish, particularly through all the appropriate tests, that the product is suitable for the use or application. Under no circumstances will our warranty apply, nor shall we be held responsible for any application (such as any modification, addition, deletion, use in conjunction with other electrical or electronic components, circuits or assemblies, or any other unsuitable material or substance) which has not been expressly agreed by us prior to the sale of our products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Crouzet:

[88975001](#) [88975101](#) [88975011](#) [88975111](#) [88975901](#) [88975911](#)