

MICROSWITCHES - SEALED, POSITIVE BREAK

PBX - 8324

- › Double-break snap-action mechanism with electrically separated circuits (form Zb)
- › Positive opening action according to IEC 60947-5-1 Annex K
- › Long overtravel, also after the positive opening position
- › Protection of mechanism: IP67/IP65, or IP40 with sealed plunger
- › Operating temperature -50 °C to +85 °C
- › Ratings from 1 mA 4 V_{DC} to 6 A 250 V_{AC} - Rating codes: A300, Q150
- › Very long mechanical life
- › Choice of connections
- › Mounting plates and roller lever (pre-assembled or retrofittable)
- › cURus and CCC approved - Meet applicable railway standards



Main specifications

		Standard 83240	High force 83242	Dual-current 83244	Dual-current High force 83245
Degree of protection	Connections				
IP40	W3 (QC 6.3x0.8)	83240000	83242000	83244000	83245000
IP40	W3/90B (QC 6.3x0.8, folded)	83240010	83242010	●	●
IP40	W5 (screw + clamp)	83240020	83242020	83244020	83245020
IP40	W5/IP20 (screw + clamp, protected)	83240030	83242030	83244030	83245030
IP67	W3 (QC 6.3x0.8)	83240200	83242200	83244200	83245200
IP67	W3/90B (QC 6.3x0.8, folded)	83240210	●	83244210	●
IP67	W5 (screw + clamp)	83240220	83242220	83244220	83245220
IP67	W5/IP20 (screw + clamp, protected)	83240230	83242230	83244230	83245230
Electrical characteristics					
Positive opening action		➔	➔	➔	➔
Rating nominal / 250 V _{AC} (A)		6	6	6*	6*
Rating nominal / 250 V _{DC} (A)		0.6	0.6	0.6*	0.6*
Rating thermal (A)		10	10	10	10
Mechanical characteristics					
Maximum operating force (N)		4.5	6.5	4.5	6.5
Minimum release force (N)		0.6	2.5	0.6	2.5
Minimum positive opening force (N)		28	28	28	28
Maximum rest position (mm)		8.9	8.9	8.9	8.9
Operating position (mm)		6.6 ±0.25	6.6 ±0.25	6.6 ±0.25	6.6 ±0.25
Positive opening position (mm)		4.4	4.4	4.4	4.4
Maximum total travel position (mm)		3.4	3.4	3.4	3.4
Differential travel (mm)		1 ±0.3	1 ±0.3	1 ±0.3	1 ±0.3
Operating temperature (°C)		-50 → +85	-50 → +85	-50 → +85	-50 → +85
Mechanical life - IP40 versions (operations)		10 ⁷	10 ⁷	10 ⁷	10 ⁷
Mechanical life - IP67 versions (operations)		4x10 ⁶	4 x 10 ⁶	4 x 10 ⁶	4 x 10 ⁶
Contact gap (mm)		2 x 1	2 x 1	2 x 1	2 x 1
Weight, terminal versions (g)		22	22	22	22

Additional specifications

- Case: PC GF (UL 94-V0 / GWFI 960 °C / GWIT 775 °C)
- Button: PBT GF (UL 94-V0 / GWFI 960 °C)
- Membrane: silicone rubber
- Contacts: silver alloy, micro-profile
gold alloy on silver alloy, micro-profile (dual-current)
- Terminals: brass (silver-plated brass : on request)
- Screws: stainless steel
- Levers: stainless steel, polyamide roller
- Degree of protection: IP65/IP67 or IP40 (mechanism)
- Recommended min actuating speed: 0.1 mm/s
- Rated insulation voltage U_i: 400 V
- Impulse withstand voltage U_{imp}: 4 kV
- Pollution degree: 3
- Protection against electric shock: Button and actuators of IP67 versions have reinforced insulation
- Dimensional conformity: DIN 41636 F
- Fire/smoke resistance: EN 45545
- Certification marks: (A300, Q150) /

Product adaptations



- › Special connections: W3 QC with specific folding, double QC tabs, W1 screw + washer, W5 without screw, ...
- › Integral wire lead or cable outputs, EN 50306 halogen-free versions
- › Special levers: special shapes and lengths
- › AgPd contacts for infrequent switching in corrosive atmospheres up to 1A (83241/83243)
- › Maintained action variant (bistable reset switch), with plunger or lever
- › Two-pole DPDT assemblies with common lever
- › IP40 protective cover/housing on connections

Standard product

Product made to order




Contact us

Principles

Double break snap-action switch with electrically separated circuits and with positive opening action on NC contacts (21-22) according to IEC 60947-5-1 Annex K


Changeover - SPDT (form Zb)



Both circuits can be used at opposite polarities

Curves

Operating curve for category AC15 Operating curve for category DC13




** For IP67 versions used in 125 V DC, please consult us.

* Models 83244 and 83245 are designed to operate equally well on low-current (1 mA 4 V minimum recommended) or medium to high current circuits. However, a given product should only be used to switch one type of circuit during its working life.

Dimensions

Product

8324




- 1 Fixing screw threaded length
- 2 Fixing nuts 2 x M3


Max. tightening torque of fixing screws: 1.3 N.m on $\varnothing 4.1$ holes
0.9 N.m on M3 nuts

Connections


W3 quick-connect 6.3 x 0.8



W3/90B quick-connect 6.3x0.8, 90° downward folding




W5 screw with clamp W1 screw with washer




4 x M3 screws - PZ1 type

W5/IP20 screw with clamp and IP20 protection




Mounting accessories

PT mounting plates with holes 79552459




Thickness: 1 mm

PE mounting plates with notches 79552460



Thickness: 1 mm

IP20 screw connection cover 79552328




Snap-on mounting
2 pieces are needed

Actuators

LG roller lever 79552456

LG PT roller lever + plates with holes 79552457

LG PE roller lever + plates with notches 79552458



Mechanical characteristics on roller

	83240/83244	83242/83245
Maximum operating force (N)	3	4
Minimum release force (N)	0.3	1.3
Min. positive opening force (N)	19	19
Maximum rest position (mm)	21	21
Operating position (mm)	16,6±0,5	16,6±0,5
Positive opening position (mm)	13,2	13,2
Maximum total travel position (mm)	12	12
Differential travel (mm)	1,8±0,55	1,8±0,55

Actuators and mounting accessories

PBX 8324 with referenced accessories

Roller lever Mounting plates Accessory kit			LG	LG	LG	-	-
			-	PT	PE	PT	PE
			79552456	79552457	79552458	79552459	79552460
83240	IP40	W3	83240003	83240004	83240005	•	•
		W3/90B	83240013	83240014	83240015	•	•
		W5	83240023	83240024	•	83240021	•
		W5/IP20	83240033	83240034	•	•	•
	IP67	W3	83240203	•	•	•	•
		W3/90B	83240213	83240214	•	•	•
		W5	83240223	83240224	83240225	83240221	•
		W5/IP20	•	•	•	•	•
	IP40	W3	83242003	83242004	83242005	•	•
		W3/90B	•	83242014	•	83242011	•
		W5	83242023	83242024	•	83242021	•
		W5/IP20	•	•	•	•	•
	IP67	W3	•	•	•	•	•
		W3/90B	•	•	•	•	•
		W5	83242223	83242224	•	•	•
		W5/IP20	•	•	•	•	•
83244	IP40	W3	83244003	83244004	•	•	•
		W3/90B	83244013	83244014	•	•	•
		W5	83244023	83244024	•	•	•
		W5/IP20	83244033	83244034	•	•	•
	IP67	W3	83244203	•	•	•	•
		W3/90B	83244213	•	•	•	•
		W5	83244223	83244224	•	•	•
		W5/IP20	•	•	•	•	•

Installation recommendations

See "Basic technical concepts".

To observe the required clearances and creepage distances in the connection area :

- above 100 V: an insulating plate is needed when the switch is mounted on an uninsulated surface.
- above 250 V: insulating plates are needed between switches when ganging.

How to order


Use the 8 digit part numbers when they are defined

Other cases, precise: Type of microswitch - Degree of protection - Connection - Actuator* - Mounting accessories* - Adaptation*


* if needed

Example: 83240 IP67 W3/90B LG PE


Examples of special adaptations



Two-pole DPDT assembly with linked levers



Short roller lever



Mixed connections: NO quick-connect 6.3 x 0.8 / NC screw with clamp



Mixed connections: NO screw with clamp / NC quick-connect 6.3 x 0.8, 90° downward folding



In-line quick-connect terminals



Economic version (839930): SPDT form Za without positive opening, Ø 3.2 mounting holes on top face, screw terminals

Warning:

The product information contained in this catalogue is given purely as information and does not constitute a representation, warranty or any form of contractual commitment. Crouzet and its subsidiaries reserve the right to modify their products without notice. It is imperative that we should be consulted over any particular use or application of our products and it is the responsibility of the buyer to establish, particularly through all the appropriate tests, that the product is suitable for the use or application. Under no circumstances will our warranty apply, nor shall we be held responsible for any application (such as any modification, addition, deletion, use in conjunction with other electrical or electronic components, circuits or assemblies, or any other unsuitable material or substance) which has not been expressly agreed by us prior to the sale of our products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Crouzet:

[83242003](#) [83240023](#) [83242030](#) [83240030](#) [83240005](#) [83240203](#) [83242024](#) [83240020](#) [83242023](#) [83242004](#)
[83240003](#) [83240220](#) [83242005](#) [83242000](#) [83242224](#) [83240223](#) [83242020](#) [83240213](#) [83242220](#) [83242200](#)
[83240224](#) [83242230](#) [83240040](#) [83240043](#) [83240230](#)