

Starting/running torque 2.5 mNm 0.16 watts Part number 82340195


- Constant speed dependent on supply frequency
- Direction of rotation controlled by long-life mechanical anti-return
- Permanent magnet rotor with 5 pole pairs
- Toughened shaft turning on two moulded polyamide bearings
- UL, CSA (class B)

Part numbers


Type	Type	Direction of rotation	Voltages/Frequencies
82 340 195	0.16 watts	82 340 0	Anti-clockwise 230 V 50 hz

Specifications
General characteristics

Base speed of motor (rpm)	600
Absorbed power (W)	3
Usable Power (W)	0,16
Starting/running torque (mNm)	2,5
Stall torque (mNm)	3,3
Temperature rise (°C)	55
Ambient temperature (°C)	-5 → +60
Maximum inertial load that can be moved (g.cm²)	4,6
Number of offload starts 10⁶	10
Max. reverse rotation angle (°)	360
Insulation resistance (MΩ)	75 x 10³
Breakdown voltage (V-50 Hz)	1800 - 1 s
Weight (g)	110
Wires length mm (approximately)	250
Protection rating	IP30

Dimensions (mm)

82 340 0



Nº	Legend
1	3 fixing holes ØM2 at 120 ° on r=19.5 max. depth 2.4 mm

Product adaptations



- Different voltages available
- Pinion on output shaft
- Special cable lengths
- Special connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Crouzet:](#)

[82340195](#)