


MIL-STD-1553 TRANSFORMERS

Dual Ratio SMT QPL Pulse Transformers
Ruggedized



Summary Performance Specifications

Droop	20% MAX
Overshoot	±1V MAX
Common Mode Rejection (CMR)	45dB MIN
Frequency Range (no load)	75kHz - 1MHz
Operating Temperature Range	-55°C to +130°C
Weight	5 grams MAX
Insulation Resistance (MIN)	10K MΩ @ 250Vdc
Dielectric Withstanding Voltage	100Vrms

- ⊗ Qualified QPL MIL-STD-1553 applications
- ⊗ Dual ratio in a single package
- ⊗ Designed, built and tested to MIL-PRF-21038
- ⊗ Product Levels:
 - ⊗ Level C: for high reliability commercial/industrial applications
 - ⊗ Level M: for general purpose military applications
 - ⊗ Level T: for high reliability critical military applications
- ⊗ Two Packages Available:
 - ⊗ Package B: Gull-wing Leads
 - ⊗ Package F: Flat Pack
- ⊗ Moisture Sensitivity Level: 3
- ⊗ Applicable Specifications:
 - ⊗ MIL-STD-1553B
 - ⊗ MIL-STD-202
 - ⊗ MIL-PRF-21038
 - ⊗ ISO 9001

Characteristics

Part Number	Line	Level	Military Designation No.	Package	Height MAX	Terminals	Ratio (±3%)	RDC MAX (Ω)	Impedance MIN (Ω)
					IN. [mm]				
SMQC1553-6	1	C	M21038/27-11C	B	0.250 [6.35]	1-3:4-8 1-3:5-7	1CT:1CT 1CT:0.707CT	1-3 = 3.0 4-8 = 3.0	(1-3) 4,000
SMQ1553-6	2	M	M21038/27-11						
SMQT1553-6	3	T	M21038/27-11T						
SMQC1553-7	4	C	M21038/27-12C	B	0.250 [6.35]	1-3:4-8 1-3:5-7	1.40CT:1CT 2CT:1CT	1-3 = 3.5 4-8 = 3.0	(1-3) 7,200
SMQ1553-7	5	M	M21038/27-12						
SMQT1553-7	6	T	M21038/27-12T						
SMQC1553-8	7	C	M21038/27-13C	B	0.250 [6.35]	1-3:4-8 1-3:5-7	1.25CT:1CT 1.66CT:1CT	1-3 = 3.2 4-8 = 3.0	(1-3) 4,000
SMQ1553-8	8	M	M21038/27-13						
SMQT1553-8	9	T	M21038/27-13T						
SMQC1553-10*	10	C	M21038/27-15C	B	0.250 [6.35]	1-3:4-8 1-3:5-7	1CT:2.12CT 1CT:1.50CT	1-3 = 1.0 4-8 = 3.5	(4-8) 4,000
SMQ1553-10*	11	M	M21038/27-15						
SMQT1553-10*	12	T	M21038/27-15T						
FPQC1553-6	13	C	M21038/27-16C	F	0.250 [6.35]	1-3:4-8 1-3:5-7	1CT:1CT 1CT:0.707CT	1-3 = 3.0 4-8 = 3.0	(1-3) 4,000
FPQ1553-6	14	M	M21038/27-16						
FPQT1553-6	15	T	M21038/27-16T						
FPQC1553-7	16	C	M21038/27-17C	F	0.250 [6.35]	1-3:4-8 1-3:5-7	1.40CT:1CT 2CT:1CT	1-3 = 3.5 4-8 = 3.0	(1-3) 7,200
FPQ1553-7	17	M	M21038/27-17						
FPQT1553-7	18	T	M21038/27-17T						
FPQC1553-8	19	C	M21038/27-18C	F	0.250 [6.35]	1-3:4-8 1-3:5-7	1.25CT:1CT 1.66CT:1CT	1-3 = 3.2 4-8 = 3.0	(1-3) 4,000
FPQ1553-8	20	M	M21038/27-18						
FPQT1553-8	21	T	M21038/27-18T						
FPQC1553-10*	22	C	M21038/27-20C	F	0.250 [6.35]	1-3:4-8 1-3:5-7	1CT:2.12CT 1CT:1.50CT	1-3 = 1.0 4-8 = 3.5	(4-8) 4,000
FPQ1553-10*	23	M	M21038/27-20						
FPQT1553-10*	24	T	M21038/27-20T						
SMQC1553-45*	25	C	M21038/27-27C	B	0.250 [6.35]	1-3:4-8 1-3:5-7	1CT:2.50CT 1CT:1.79CT	1-3 = 1.0 4-8 = 3.5	(4-8) 4,000
SMQ1553-45*	26	M	M21038/27-27						
SMQT1553-45*	27	T	M21038/27-27T						
FPQC1553-45*	28	C	M21038/27-31C	F	0.250 [6.35]	1-3:4-8 1-3:5-7	1CT:2.50CT 1CT:1.79CT	1-3 = 1.0 4-8 = 3.5	(4-8) 4,000
FPQ1553-45*	29	M	M21038/27-31						
FPQT1553-45*	30	T	M21038/27-31T						

*Designed for transceivers utilizing a single supply voltage (+5V).



Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2020. iNRCORE, LLC. All rights reserved.

M225.E (11/21)

MIL-STD-1553 TRANSFORMERS


Dual Ratio SMT QPL Pulse Transformers
Ruggedized





Mechanicals

Electrical Schematics

Package B




Dimensions: inch [mm]
Tolerance (unless otherwise specified): ± 0.010 [0.25]





Mechanicals

Electrical Schematics

Package F



Dimensions: inch [mm]
Tolerance (unless otherwise specified): ± 0.010 [0.25]



Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2020. iNRCORE, LLC. All rights reserved.

M225.E (11/21)

MIL-PRF-21038/27 Inspection, Sampling, Testing

Table 1 - Group A Inspection

Level "C" **		Level "M"		Level "T"	
Tests	Sampling Plan	Tests	Sampling Plan	Tests	Sampling Plan
N/A	N/A	Electrical Characteristics per MIL-PRF-21038/27	Sample per Table 3	Thermal Shock	100%
N/A	N/A	Visual & Mechanical Inspection	Sample per Table 3	Winding Continuity	100%
N/A	N/A	N/A	N/A	Electrical Characteristics per MIL-PRF-21038/27	100%
N/A	N/A	N/A	N/A	Impedance	Sample per Table 3
N/A	N/A	N/A	N/A	Visual & Mechanical Inspection	Sample per Table 3

Table 2 - Group B Inspection

Level "C" **		Level "M"		Level "T"	
Tests	Sampling Plan	Tests	Sampling Plan	Tests	Sampling Plan
N/A	N/A	Dielectric Withstanding Voltage	Sample per Table 3	Dielectric Withstanding Voltage	Sample per Table 3
N/A	N/A	Insulation Resistance	Sample per Table 3	Insulation Resistance	Sample per Table 3


Table 3 - Sampling Plans for Group A and Group B Inspections

Lot Size	Group A, Group II Inspections	Group B
1 to 5	All	All
6 to 13	All	5
14 to 50	13	5
51 to 90	13	7
91 to 150	13	11
151 to 280	20	13
281 to 500	29	16
501 to 1,200	34	19
1,201 to 3,200	42	23
3,201 to 10,000	50	29

** Parts ordered to Level C are certified to comply with MIL-PRF-21038 Level C, however testing is performed per manufacturer's internal requirements and sampling rates.



Tin/Lead Recommended Reflow Profile (Based on J-STD-020D)



T_{smin} (°C)	T_{smax} (°C)	T_l (°C)	T_p (°C MAX)	t_s (s)	t_L (s)	t_p (s MAX)	Ramp-up rate (T_l to T_p)	Ramp-down rate (T_p to T_l)	Time 25°C to peak temperature (s MAX)
100	150	183	225	60 - 120	60 - 150	20	3°C/s MAX	6°C/s MAX	360

- NOTES:
1. All temperatures measured on the package leads.
 2. Maximum times of reflow cycle: 2



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[iNRCORE:](#)

[SMQC1553-6](#) [SMQ1553-45](#) [SMQC1553-45](#) [FPQT1553-45](#) [SMQC1553-7](#) [SMQT1553-45](#) [SMQT1553-7](#)
[SMQC1553-10](#) [SMQ1553-7](#)