

1000BASE-T SINGLE PORT TRANSFORMER MODULES

Industrial grade



- Compliant with IEEE 802.3 standards
- 350pH OCL with 8mA DC bias at 100KHz 100mV
- Lead finish: Pure tin
- Moisture Sensitivity Level: 1





Electrical Specifications @ 25 °C – Operating Temperature – 40 °C to +85

Part Number	Insertion Loss (dB MAX)	Return Loss (dB MIN)					Crosstalk (dB MIN)			Differential to Common Mode Rejection (dB MIN)			Dielectric Withstanding Voltage @60s (Vrms MIN)
	0.1-100 MHz	5 MHz	30 MHz	60 MHz	80 MHz	100 MHz	30 MHz	60 MHz	100 MHz	30 MHz	60 MHz	100 MHz	
R5033NL	-1.2	-18	-18	-14	-12	-10	-33	-30	-25	-43	-37	-33	1500

Notes: 1. Add suffix to part number for Tape & Reel package (ie: **R5033NLT**).

Mechanical

R5033NL




DIMENSIONS: $\frac{\text{INCHES}}{\text{MM}}$
UNLESS OTHERWISE SPECIFIED,
ALL TOLERANCES ARE $\pm \frac{.010}{0.25}$

WEIGHT.....APPROX 2.2GRAMS
TAPE & REEL.....250PCS/REEL
TUBE.....30PCS/TUBE




Electrical Schematic

R5033NL



LEGEND




ALL CHANNELS ARE
IN-PHASE BETWEEN
INPUT AND OUTPUT

1000BASE-T SINGLE PORT TRANSFORMER MODULES

Industrial grade



Non-Lead Recommended Reflow Profile (Based on J-STD-020D)



T_{SMIN} (°C)	T_{SMAX} (°C)	T_L (°C)	T_P (°C MAX)	t_s (s)	t_L (s)	t_p (s MAX)	Ramp-up rate (T_L to T_P)	Ramp-down rate (T_P to T_L)	Time 25°C to peak temperature (s MAX)
150	200	217	245	60-120	60-150	30	3°C/s MAX	6°C/s MAX	480

Notes:

1. All temperatures measured on the package leads.
2. Maximum times of reflow cycle: 2.

For More Information

iNRCORE, LLC

311 Sinclair Road Bristol,
PA 19007-6812 U.S.A
Tel: +1.215.781.6400
Fax: +1.215.781.6430

Dongguan iNRCORE Co. Ltd

No.7, An Li Road, Changan Town,
Dongguan City, China
Tel: +0769 8165 9962

Global Sales Representatives and Locations:

<http://www.inrcore.com>

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2020. iNRCORE, LLC. All rights reserved.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[iNRCORE:](#)

[R5033NL](#) [R5033NLT](#)